

PHILIPS

Meson Recessed Light

Recessed Lights

6500/2700/4000K

White

SceneSwitch



8720169356207



Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution

Safety

- No harmful UV radiation

Mounting

- Integrated driver with connector for easy installation.

Durability

- Long life span up to 15,000 hours

Highlights

Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

Integrated driver with connector for easy installation.

Allows for safe and easy installation with no knowledge or wiring required.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Number of switch cycles: 7,500

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: SceneSwitch

Other characteristics

- Lamp current: 70 mA

Power consumption

- Power factor: 0.5
- Wattage: 9 W

Product dimensions and weight

- Net weight: 0.07 kg
- Cut out length: 10.5 cm
- Cut out width: 10.5 cm
- Height: 5 cm
- Recessed distance: 11 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 120 mm
- Total lumen output fixture: 2700K : 6304000K : 7506500K : 680
- Light color: 6500/2700/4000
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- IP code: IP20

- Class of protection: Class II
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC - product: 8720169356207
- Net weight: 0.03 kg
- Gross weight: 0.06 kg
- Height: 12.2 cm
- Length: 5.4 cm
- Width: 12.1 cm



Issue date: 2024-11-21
Version: 0.54

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.