

# PHILIPS

Linear fluorescent  
tube

TL-D Standard colours

30 W

G13

Cool daylight

928025405482



## Reliable, functional lighting

Philips TL/TLDs produce light efficiently, resulting in fewer replacements. They provide functional lighting that gives sufficient light levels for common areas.

### Gives you bright light

- Standard colors with moderate color rendering
- High initial light output

# Highlights

**Standard colors****High initial light output**

High Light output provides better light quality with more brightness and

allows more vibrance in home application.

# Specifications

**Bulb characteristics**

- Socket: GU10
- Dimmable: No

**Durability**

- Nominal lifetime: 13,000 hour(s)

**Light characteristics**

- Color rendering index (CRI): 72
- Light Color Category: Cool Daylight
- Correlated Color Temperature (Nom): 6200
- Luminous Flux: 1,825 lm

**Power consumption**

- Wattage: 30 W
- Power Consumption: 30.0 W

**Technical specifications**

- Light output: 1,825 lm
- Shape: Linear fluorescent tube
- Dimmable: Yes
- Cap-Base: G13 | Medium Bi-Pin Fluorescent

**Packaging dimensions and weight**

- EAN/UPC - product: 8711500722638
- Net weight: 0.13 kg
- Gross weight: 0.15 kg
- Height: 2.7 cm
- Length: 91.8 cm
- Width: 2.7 cm



Issue date: 2025-03-18  
Version: 0.528

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)