

PHILIPS

Candle & Lustre

LED

2.7W-25W

B22

White

8718696459836



Frosted LED candle bulbs for decorative fixtures

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

High quality light

- Long life bulb - Lasts up to 10 years

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- A simple LED for everyday use
- Instant on

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Instant on

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: C37
- Socket: E14
- Dimmable: No

Bulb dimensions

- Height: 11 cm
- Width: 3.8 cm

Durability

- Number of switch cycles: 5,000
- Nominal lifetime: 10,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 92.6 lm/W

Packaging information

- Product family: LED
- EAN: 8718696459836
- EOC: 871869645983600
- Product title: Ace Saver Candle WW 2.7W E14

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 2.7 W
- Wattage equivalent: 25 W

Product dimensions and weight

- Length: 11 cm

8718696459836

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718696459836
- Net weight: 0.05 kg
- Gross weight: 0.06 kg
- Height: 10 cm
- Length: 5 cm
- Width: 5 cm
- Material number (12NC):
929001141723



Issue date: 2024-06-19
Version: 0.150

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com