

PHILIPS

Downlight

Functional

UltraGlow

White

8718696584972



High quality LED light designed to last for years

Philips LED luminaires provide light that is designed for the comfort of your eyes.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution

Premium quality

- EyeComfort - light that's easy on the eyes

Durability

- Long life span up to 25,000 hours

Highlights

Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 10,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Functional
- EyeComfort: Yes

Other characteristics

- Lamp current: 80 mA
- Efficacy: 75 lm/W

Power consumption

- Power factor: 0.9
- Voltage: 220–240 V

Product dimensions and weight

- Net weight: 0.265 kg
- Cut out length: 18.8 cm
- Cut out width: 18.8 cm
- Height: 2.2 cm
- Length: 22.5 cm
- Width: 22.5 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Diameter: 225 mm
- Total lumen output fixture: 2200
- Light color: 4000
- Mains power: 220–240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 22
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718696584972
- Net weight: 0.28 kg
- Gross weight: 0.39 kg
- Height: 23.5 cm
- Length: 25 cm
- Width: 4 cm
- Material number (12NC):
929002629601



Issue date: 2024-09-07
Version: 0.55

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com