

PHILIPS

Recessed spot light

Functional

Surface COB

Black



8719514260863



High quality LED light designed to last for years

Surface mounted COB light to highlight the objects in the places where there is no false ceiling like corridors, shops etc.

Match your interior

- Decorative metallic finishing

Easy to experience

- Easy installation

Light effect

- Durable synthetic diffuser for uniform light and reduced glare

Premium quality

- Durable and impact resistant die-cast aluminum housing

Mounting

- Closed mounting for prevention of bugs and dirt ingress

Durability

- Long life span up to 30,000 hours

Highlights

Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Closed mounting for prevention of bugs and dirt ingress

Prevents damage cause by bugs, dust or other foreign objects.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Design and finishing

- Color: Black
- Material: Metal

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 36 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.19 kg
- Cut out length: 0 cm
- Cut out width: 0 cm
- Height: 9 cm
- Length: 5 cm
- Width: 5 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 35,000 hour(s)
- Diameter: 50 mm
- Total lumen output fixture: 595
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 7
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8719514260863
- Net weight: 0.19 kg
- Gross weight: 0.24 kg
- Height: 13.5 cm
- Length: 9 cm
- Width: 9 cm
- Material number (12NC): 929001951950



Issue date: 2024-09-17
Version: 0.240

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com