

PHILIPS

Fan Regulator

Switches & Sockets

Durro

White

1 Module

913713989801



Durability with style

Enhance your home décor with smooth, curved & highly durable switches & accessories, from Philips Durro range.

Easy to use

- Front insertion & front removal
- Glossy finish

Safe to use

- FR Grade Polycarbonate Material
- Safe to use even with wet hands

Choose for a sustainable solution

- RoHS compliant

Durability

- 360° smooth rotation
- Air vents

Long lasting marking

- Laser marking for step indication

Convenience

- 5 step fan regulator
- Choose between 1 module or 2 module

Highlights

Front insertion & front removal

Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

Glossy finish

Glossy external finish for easy to clean and long lasting finish.

FR Grade Polycarbonate Material

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

Safe to use even with wet hands

No seepage of water due to precision & covered design.

RoHS compliant

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

360° smooth rotation

Smooth continuous rotation to prevent accidental breakage even after 360° movement.

Air vents

Designed with Air vents for better air circulation which helps in keeping the product cools and improves the life.

Laser marking for step indication

Step indication with permanent laser marking which stays forever.

5 step fan regulator

5 step fan regulator for maintaining variable speed.

Choose between 1 module or 2 module

Available in 1Module and 2 Module so that you can choose as per the design and décor.

Specifications

Design and finishing

- Color: White
- Material: PC
- Module/Gang: 1 Module
- Product Range: Durro
- Minimum Installation Box Depth: 5 cm

Durability

- Number of Operation Cycles: 5,000

Other characteristics

- Installation Type: Fast Installation

Power consumption

- Voltage: 240 V
- Wattage: 100 W

Product dimensions and weight

- Length: 5.5 cm
- Width: 2.4 cm
- Depth: 5.63 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699684761
- Net weight: 0.03 kg
- Gross weight: 0.03 kg
- Height: 5.6 cm
- Length: 5.5 cm
- Width: 2.4 cm
- Material number (12NC): 913713989801



Issue date: 2024-09-17
Version: 0.278

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com