

PHILIPS

Wall light

Led outdoor

12 W

Aluminium

Grey

IP 65

919215850755



Specially designed for your outdoors

80 % Energy saving. Outdoor ambient light. Protection against dust & water from any direction

Easy installation

- Easy installation

Light effect

- Provides a bright white light

Beacon of trust

- You can trust what the Philips packaging is saying

Premium quality

- Die-casted aluminum for a premium look and feel

Specially designed for your outdoors

- Resistant to all weather conditions

Highlights

Easy installation



No more hassle in installation. Just fix or hang securely on the wall and plug in, now this luminaire is ready to light on.

Superior light quality

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Premium materials



Resistant to all weather



This Philips Hue outdoor sensor is specially designed for use in outdoor environments and has undergone rigorous tests to ensure its performance. This lamp is designed with IP54: it is protected against water splashed from any direction. The product will withstand heavy rainfall and other weather conditions.

Specifications

Bulb characteristics

- Intended use: Outdoor

Design and finishing

- Color: Grey
- Material: Aluminium

Extra feature/accessory incl.

- Adjustable height: Yes
- Adjustable spot head: Yes
- Anti rust anti dust: Yes
- Clamp included: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Made for LED only: Yes
- Perfectly suited for ambiance creation: Yes
- Photometric data available: Yes
- Premium quality material: Yes
- Resistant high quality material: Yes
- Rotates freely in any direction: Yes
- Warm White Light: Yes
- Waterproof: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Functional
- Type: Other

Product dimensions and weight

- Net weight: 0.38 kg
- Height: 3.34 inch
- Length: 4.8 inch
- Width: 3.34 inch

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 625
- Bulb technology: LED
- Light color: 4000K
- Mains power: Range 220 V - 240 V
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 12W
- IP code: IP65
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 8718696767658
- Net weight: 0.3 kg
- Gross weight: 0.3 kg
- Height: 17 cm
- Length: 16.5 cm
- Width: 7.8 cm
- Material number (12NC):
919215850755



Issue date: 2024-07-25
Version: 0.366

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com