

# PHILIPS

IP44 dust and water-resistant step light

myGarden

Long life LED source;

Bright warm white light;

Expressive style;

High-quality polycarbonate

919215851047



## Express your style with light!


The neatly designed modern and minimal step light melts into the background settings and provides just the right ambient illumination to create an interesting setting

### Designed for your bathroom

- IP44, perfectly suited for your bathroom

# Highlights

## IP44 - bathroom safe



This Philips bathroom light is especially designed for humid environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This bathroom light is designed with IP44: it is protected against splashing water,

this product is most common and ideal for bathroom use.

# Specifications

## Bulb characteristics

- Intended use: Indoor/Outdoor

## Design and finishing

- Color: Anthracite Grey
- Material: Polycarbonate

## Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: No
- Adjustable spot head: No
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: No
- Choose your color: No
- Clamp included: Yes
- Color changing (LED): No
- Day-and-night sensor: No
- Defined light beams: No
- Fully weatherproof: No
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: Yes
- Premium quality material: Yes

## Light characteristics

- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Bathroom

## Product dimensions and weight

- Net weight: 0.107 kg
- Height: 5.2 cm
- Height maximum: 5.2 cm
- Length: 10.8 cm
- Width: 10.8 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lamp lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 80
- Bulb technology: LED
- Light color: warm white
- Mains power: 220-240 V
- LED: Yes
- Built in LED: Yes
- Energy class included light source: built in LED + bulb of class A+
- IP code: IP44

## Packaging dimensions and weight

- EAN/UPC - product: 8719514491953
- Net weight: 0.11 kg
- Gross weight: 0.13 kg
- Height: 9.7 cm
- Length: 9.7 cm
- Width: 4.8 cm
- Material number (12NC): 919215851047



Issue date: 2024-09-17  
Version: 0.105

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)