

PHILIPS

Tunable white IP44
bathroom wall light

myBathroom

5W; 260 lumen; In-built LED;

IP44 rating ensures protection
from dust and moisture;

Perfect chrome finish;

Toggle from warm white to
natural white to cool white via
wall switch

919215851095



The epitome of elegance and luxury

Aesthetically designed with symmetrical light distribution for enduring appeal and endless versatility. These wall lights are a perfect mix of contemporary and antique designs that can instantly take your home décor up a notch.

Light modes

- Tunable warm to cool white and preset modes

Highlights

Tunable warm to cool white and preset modes

Choose from a wide range of energizing cool white to soft warm

white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Specifications

Bulb characteristics

- Intended use: Indoor

Bulb dimensions

- Height: 19.5 cm

Design and finishing

- Color: Chrome
- Material: Metal

Durability

- Nominal lifetime: 20,000 hour(s)

Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: No
- Adjustable spot head: No
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: No
- Choose your color: No
- Clamp included: Yes
- Color changing (LED): Yes
- Day-and-night sensor: No
- Defined light beams: No
- Fully weatherproof: No
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: Yes
- Perfectly suited for ambience creation: Yes
- Premium quality material: Yes
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bathroom
- Style: Contemporary
- Type: Ceiling Lights

Product dimensions and weight

- Net weight: 0.522 kg
- Height: 19.5 cm
- Length: 15 cm
- Width: 19.5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lamp lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 260
- Bulb technology: LED
- Light color: 3000-6500
- Mains power: 220-240 V
- Energy class included light source: built in LED + bulb of class A+
- IP code: IP44

Packaging dimensions and weight

- EAN/UPC – product: 8720169211339
- Net weight: 0.98 kg
- Gross weight: 0.98 kg
- Height: 22.7 cm
- Length: 20.7 cm
- Width: 16.5 cm



Issue date: 2025-06-06
Version: 0.29

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com