

# PHILIPS

Tunable white IP44  
bathroom wall light

myBathroom

5W; 370 lumen; In-built LED;

IP44 rating ensures protection  
from dust and moisture;

Perfect chrome finish;

Toggle from warm white to  
natural white to cool white via  
wall switch

919215851097



## Bathroom adoration with minimal efforts

These wall lights create ambient light to give a warm and diffused glow in the room. It can light up specific bathroom areas making your bathroom chores smooth like shaving and applying makeup. Now give your bathroom a feel of luxury with these decorative wall lights!

### Light modes

- Tunable warm to cool white and preset modes

# Highlights

## Tunable warm to cool white and preset modes

Choose from a wide range of energizing cool white to soft warm

white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Chrome
- Material: Metal

## Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: No
- Adjustable spot head: Yes
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: No
- Choose your color: No
- Clamp included: Yes
- Color changing (LED): Yes
- Day-and-night sensor: No
- Defined light beams: No
- Fully weatherproof: No
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: Yes
- Perfectly suited for ambience creation: Yes
- Premium quality material: Yes
- Centerpiece: Yes

## Light characteristics

- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Bathroom
- Style: Contemporary

## Product dimensions and weight

- Net weight: 0.365 kg
- Height: 8.5 cm
- Height maximum: 8.5 cm
- Length: 12 cm
- Width: 12 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 20,000 hour(s)
- Lamp lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 370
- Bulb technology: LED
- Light color: 3000-6500
- Mains power: 220-240 V
- LED: Yes
- Built in LED: Yes
- Energy class included light source: built in LED + bulb of class A+
- IP code: IP44

## Packaging dimensions and weight

- EAN/UPC - product: 8720169211377
- Net weight: 0.37 kg
- Gross weight: 0.64 kg
- Height: 9.2 cm
- Length: 15.3 cm
- Width: 14.7 cm



Issue date: 2024-11-21  
Version: 0.50

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)