



CoreLine Trunking gen2 – Innovative LED light lines have never been so simple

CoreLine Trunking gen2

CoreLine Trunking gen2 is a light-line system that is designed for simplicity. It comes in a choice of lengths, flux packages and beam shapes to suit every project and application. Easy to use and integrate with spots and sensors, CoreLine Trunking gen2 provides consistent, high-quality lighting with added protection against accidental water ingress. The innovative system is also easy to assemble and install for faster retrofits and refurbishments.

Benefits

- Optimized, efficient design and light effect
- Consistent, high-quality light - no Color over Angle or striping artefacts
- Improved light continuity
- Easy to order, assemble and install
- InterAct ready for enhanced use in Retail and Industry applications

Features




- Intuitive, single layer architecture – only 2 12NCs needed to create a line
- Choice of 3 lengths, each with 3 flux packages
- 8 different optics with consistent light quality
- Dedicated sensor units to upgrade to InterAct system propositions
- Lumen maintenance @ 50,000 hours - L80
- Available as trunking and standalone versions

CoreLine Trunking gen2

Application

- Food and Large Retailers
- Warehouses
- Manufacturing

Dimensional drawing



Product details



CoreLine Trunking Gen2 Half Blind



Product Detail Photo Coreline

CoreLine Trunking gen2

Product details

Product Detail Photo Coreline



Product Detail Photo Coreline



General Information

Driver included	Yes
Light source replaceable	No
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20

Approval and Application

Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC plus mark
Flammability mark	-
Glow-wire test	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code	Number of gear units
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	-	1 unit
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	-	1 unit
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	-	1 unit
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	-	1 unit
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	-	1 unit
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	-	1 unit
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	-	1 unit
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	-	1 unit
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	-	1 unit
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	-	1 unit
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	-	1 unit
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	-	1 unit
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	120S	1 unit
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	120S	1 unit
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	120S	1 unit
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	120S	1 unit
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	80S	1 unit
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	80S	1 unit
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	80S	1 unit
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	80S	1 unit
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	80S	1 unit
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	80S	1 unit
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	80S	1 unit
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	160S	2 units
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	160S	2 units
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	160S	2 units
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	160S	2 units
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	160S	2 units
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	240S	2 units
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	240S	2 units
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	240S	2 units
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	240S	2 units
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	240S	2 units
910925867552	LL234X 160S/840 2x PSD O 7x2.5	160S	2 units
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	160S	2 units
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	160S	2 units
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	160S	2 units

Order Code	Full Product Name	Lamp family code	Number of gear units
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	160S	2 units
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	160S	2 units
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	80S	1 unit
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	90S	2 units
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	-	1 unit
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	-	2 units
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	-	1 unit
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	-	2 units
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	-	1 unit
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	-	1 unit
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	-	1 unit
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	-	1 unit
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	-	1 unit
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	-	1 unit
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	-	1 unit
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	-	1 unit
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	-	1 unit
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	-	1 unit
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	-	1 unit
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	-	1 unit
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	-	1 unit
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	-	1 unit
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	-	1 unit
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	-	1 unit
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	-	1 unit
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	-	1 unit
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	-	1 unit
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	-	1 unit
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	-	1 unit
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	-	1 unit
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	-	1 unit
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	-	1 unit
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	-	1 unit
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	-	1 unit
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	-	2 units
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	-	2 units
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	-	2 units
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	-	2 units
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	-	2 units
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	-	2 units
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	-	1 unit
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	-	1 unit
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	-	1 unit
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	-	1 unit
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	-	1 unit
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	-	1 unit
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	-	1 unit
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	-	1 unit
910925867498	LL217X 80S/840 1x PSD BV WB	-	1 unit
910925867525	LL217X 120S/840 1x PSU BV WB HE	120S	1 unit
910925867539	LL234X 240S/840 2x PSD BV WB HE	240S	2 units
910925867550	LL234X 160S/840 2x PSU BV WB	160S	2 units

CoreLine Trunking gen2

Order Code	Full Product Name	Lamp family code	Number of gear units
910925867698	LL217X 80S/840 1X PSU BV WB TW3	-	1 unit
910925867699	LL234X 160S/840 1X PSU BV WB TW3	-	1 unit
910925867701	LL234X 160S/840 2X PSU BV WB TW3	-	2 units
910925868236	LL217X 45S/840 1x PSU BV WB	-	1 unit
910925868237	LL217X 45S/840 1x PSD BV WB	-	1 unit
910925868238	LL217X 45S/840 1x PSU BV O	-	1 unit
910925868239	LL217X 45S/840 1x PSD BV O	-	1 unit
910925868240	LL217X 80S/840 1x PSU BV WB	-	1 unit
910925868241	LL217X 80S/840 1x PSU BV O	-	1 unit
910925868242	LL217X 80S/840 1x PSD BV O	-	1 unit
910925868391	LL217X 120S/840 1x PSU BV WB TW3	-	1 unit
910925868392	LL217X 120S/840 1x PSU BV MB TW3	-	1 unit
910925868393	LL217X 120S/840 1x PSU BV NB TW3	-	1 unit
910925868394	LL217X 80S/840 1x PSU BV MB TW3	-	1 unit
910925868395	LL217X 80S/840 1x PSU BV NB TW3	-	1 unit
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	80S	1 unit
910925867535	LL217X 80S/840 1x PSD O 7x2.5	80S	1 unit
910925867551	LL234X 160S/840 2x PSD O 7x1.5	160S	2 units
910925867556	LL234X 160S/840 2x PSU O 5x1.5	160S	2 units
910925867557	LL234X 160S/840 2x PSU O 5x2.5	160S	2 units

Light Technical

Order Code	Full Product Name	Luminous		Optic type	Order Code	Full Product Name	Luminous		Optic type
		Efficacy (rated) (Nom)	Luminous Flux				Efficacy (rated) (Nom)	Luminous Flux	
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	161 lm/W	4,500 lm	Wide beam	910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	152 lm/W	12,000 lm	Wide beam
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	160 lm/W	8,000 lm	Wide beam	910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	152 lm/W	12,000 lm	Wide beam
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	161 lm/W	4,500 lm	Narrow beam	910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	150 lm/W	12,000 lm	Wide beam
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	160 lm/W	8,000 lm	Narrow beam	910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	165 lm/W	8,000 lm	Wide beam
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	161 lm/W	5,300 lm	Wide beam	910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	165 lm/W	8,000 lm	Wide beam
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	156 lm/W	5,300 lm	Wide beam	910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	163 lm/W	8,000 lm	Wide beam
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	161 lm/W	5,300 lm	Wide beam	910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	163 lm/W	8,000 lm	Wide beam
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	161 lm/W	5,300 lm	Wide beam	910925867536	LL217X 80S/840 1x PSD WB 7x2.5	160 lm/W	8,000 lm	Wide beam
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	161 lm/W	5,300 lm	Wide beam	910925867537	LL217X 80S/840 1x PSU WB 5x1.5	157 lm/W	8,000 lm	Wide beam
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	150 lm/W	12,000 lm	Wide beam	910925867538	LL217X 80S/840 1x PSU WB 5x2.5	157 lm/W	8,000 lm	Wide beam
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	160 lm/W	8,000 lm	Wide beam	910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	165 lm/W	16,000 lm	Wide beam
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	160 lm/W	8,000 lm	Wide beam	910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	165 lm/W	16,000 lm	Wide beam
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	152 lm/W	12,000 lm	Wide beam	910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	165 lm/W	16,000 lm	Wide beam

CoreLine Trunking gen2

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	165 lm/W	16,000 lm	Wide beam
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	165 lm/W	16,000 lm	Wide beam
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	152 lm/W	24,000 lm	Wide beam
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	152 lm/W	24,000 lm	Wide beam
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	152 lm/W	24,000 lm	Wide beam
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	150 lm/W	24,000 lm	Wide beam
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	150 lm/W	24,000 lm	Wide beam
910925867552	LL234X 160S/840 2x PSD O 7x2.5	150 lm/W	15,000 lm	Symmetrical
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	160 lm/W	16,000 lm	Wide beam
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	160 lm/W	16,000 lm	Wide beam
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	160 lm/W	16,000 lm	Wide beam
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	157 lm/W	16,000 lm	Wide beam
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	157 lm/W	16,000 lm	Wide beam
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	165 lm/W	8,000 lm	Wide beam
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	161 lm/W	9,000 lm	Wide beam
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	160 lm/W	16,000 lm	Wide beam
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	157 lm/W	16,000 lm	Narrow beam
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	157 lm/W	8,000 lm	Narrow beam
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	161 lm/W	9,000 lm	Wide beam
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	158 lm/W	9,000 lm	Wide beam
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	161 lm/W	4,500 lm	Wide beam
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	164 lm/W	4,500 lm	Wide beam
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	161 lm/W	4,500 lm	Wide beam
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	150 lm/W	4,500 lm	Wide beam
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	157 lm/W	8,000 lm	Wide beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	160 lm/W	8,000 lm	Wide beam
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	161 lm/W	4,500 lm	Narrow beam
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	150 lm/W	4,500 lm	Narrow beam
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	157 lm/W	8,000 lm	Narrow beam
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	160 lm/W	8,000 lm	Narrow beam
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	158 lm/W	9,000 lm	Narrow beam
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	160 lm/W	16,000 lm	Narrow beam
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	160 lm/W	8,000 lm	Narrow beam
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	161 lm/W	3,000 lm	Medium beam
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	161 lm/W	3,000 lm	Narrow beam
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	160 lm/W	5,300 lm	Medium beam
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	160 lm/W	5,300 lm	Narrow beam
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	163 lm/W	8,000 lm	Medium beam
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	163 lm/W	8,000 lm	Narrow beam
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	161 lm/W	4,500 lm	Medium beam
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	161 lm/W	4,500 lm	Narrow beam
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	157 lm/W	8,000 lm	Medium beam
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	157 lm/W	8,000 lm	Narrow beam
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	150 lm/W	12,000 lm	Medium beam
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	150 lm/W	12,000 lm	Narrow beam
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	161 lm/W	9,000 lm	Medium beam
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	161 lm/W	9,000 lm	Narrow beam
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	157 lm/W	16,000 lm	Medium beam
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	157 lm/W	16,000 lm	Narrow beam
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	150 lm/W	24,000 lm	Medium beam

CoreLine Trunking gen2

Order Code	Full Product Name	Luminous		Optic type
		Efficacy (rated) (Nom)	Luminous Flux	
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	150 lm/W	24,000 lm	Narrow beam
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	158 lm/W	9,000 lm	Wide beam
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	160 lm/W	16,000 lm	Wide beam
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	158 lm/W	9,000 lm	Narrow beam
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	160 lm/W	16,000 lm	Narrow beam
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	161 lm/W	4,500 lm	Wide beam
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	160 lm/W	8,000 lm	Wide beam
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	161 lm/W	4,500 lm	Narrow beam
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	160 lm/W	8,000 lm	Narrow beam
910925867498	LL217X 80S/840 1x PSD BV WB	160 lm/W	8,000 lm	Wide beam
910925867525	LL217X 120S/840 1x PSU BV WB HE	150 lm/W	12,000 lm	Wide beam
910925867539	LL234X 240S/840 2x PSD BV WB HE	152 lm/W	24,000 lm	Wide beam
910925867550	LL234X 160S/840 2x PSU BV WB	157 lm/W	16,000 lm	Wide beam
910925867698	LL217X 80S/840 1x PSU BV WB TW3	157 lm/W	8,000 lm	Wide beam
910925867699	LL234X 160S/840 1x PSU BV WB TW3	157 lm/W	16,000 lm	Wide beam
910925867701	LL234X 160S/840 2x PSU BV WB TW3	157 lm/W	16,000 lm	Wide beam
910925868236	LL217X 45S/840 1x PSU BV WB	161 lm/W	4,500 lm	Wide beam

Order Code	Full Product Name	Luminous		Optic type
		Efficacy (rated) (Nom)	Luminous Flux	
910925868237	LL217X 45S/840 1x PSD BV WB	164 lm/W	4,500 lm	Wide beam
910925868238	LL217X 45S/840 1x PSU BV O	150 lm/W	4,200 lm	Symmetrical
910925868239	LL217X 45S/840 1x PSD BV O	150 lm/W	4,200 lm	Symmetrical
910925868240	LL217X 80S/840 1x PSU BV WB	157 lm/W	8,000 lm	Wide beam
910925868241	LL217X 80S/840 1x PSU BV O	148 lm/W	7,400 lm	Symmetrical
910925868242	LL217X 80S/840 1x PSD BV O	148 lm/W	7,400 lm	Symmetrical
910925868391	LL217X 120S/840 1x PSU BV WB TW3	139 lm/W	12,000 lm	Wide beam
910925868392	LL217X 120S/840 1x PSU BV MB TW3	139 lm/W	12,000 lm	Medium beam
910925868393	LL217X 120S/840 1x PSU BV NB TW3	139 lm/W	12,000 lm	Narrow beam
910925868394	LL217X 80S/840 1x PSU BV MB TW3	160 lm/W	8,000 lm	Medium beam
910925868395	LL217X 80S/840 1x PSU BV NB TW3	160 lm/W	8,000 lm	Narrow beam
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	148 lm/W	7,400 lm	Symmetrical
910925867535	LL217X 80S/840 1x PSD O 7x2.5	148 lm/W	7,400 lm	Symmetrical
910925867551	LL234X 160S/840 2x PSD O 7x1.5	150 lm/W	15,000 lm	Symmetrical
910925867556	LL234X 160S/840 2x PSU O 5x1.5	150 lm/W	15,000 lm	Symmetrical
910925867557	LL234X 160S/840 2x PSU O 5x2.5	150 lm/W	15,000 lm	Symmetrical

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	27.5 W	Yes (relates to presence/ movement

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	33 W	Yes
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	34 W	Yes (relates to presence/ movement

CoreLine Trunking gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching
			detection and daylight harvesting)
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	33 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	33 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	33 W	Yes
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	80 W	Yes
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	79 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	79 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	79 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	80 W	Yes
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	48.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	48 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	49 W	Yes
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	49 W	Yes
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	50 W	Yes (relates to presence/ movement

Order Code	Full Product Name	Power Consumption	Suitable for random switching
			detection and daylight harvesting)
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	51 W	Yes
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	51 W	Yes
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	97 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	97 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	96 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	98 W	Yes
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	98 W	Yes
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	158 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	158 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	158 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	160 W	Yes
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	160 W	Yes
910925867552	LL234X 160S/840 2x PSD O 7x2.5	100 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	100 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	100 W	Yes (relates to presence/ movement detection and daylight harvesting)

CoreLine Trunking gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	100 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	102 W	Yes
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	102 W	Yes
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	48.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	55 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	98 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	102 W	Yes
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	51 W	Yes
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	56 W	Yes
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	57 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	28 W	Yes
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	28 W	Yes
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	51 W	Yes
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	28 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	51 W	Yes
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	57 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	98 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	19 W	Yes
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	19 W	Yes
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	33 W	Yes
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	33 W	Yes
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	49 W	Yes
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	49 W	Yes
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	28 W	Yes
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	28 W	Yes
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	50 W	Yes
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	50 W	Yes
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	79 W	Yes
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	79 W	Yes
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	56 W	Yes
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	56 W	Yes

CoreLine Trunking gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	102 W	Yes
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	102 W	Yes
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	158 W	Yes
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	158 W	Yes
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	57 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	100 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	57 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	100 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867498	LL217X 80S/840 1x PSD BV WB	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867525	LL217X 120S/840 1x PSU BV WB HE	80 W	Yes
910925867539	LL234X 240S/840 2x PSD BV WB HE	158 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867550	LL234X 160S/840 2x PSU BV WB	102 W	Yes

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867698	LL217X 80S/840 1x PSU BV WB TW3	51 W	Yes
910925867699	LL234X 160S/840 1x PSU BV WB TW3	102 W	Yes
910925867701	LL234X 160S/840 2X PSU BV WB TW3	102 W	Yes
910925868236	LL217X 45S/840 1x PSU BV WB	28 W	Yes
910925868237	LL217X 45S/840 1x PSD BV WB	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868238	LL217X 45S/840 1x PSU BV O	28 W	Yes
910925868239	LL217X 45S/840 1x PSD BV O	27.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868240	LL217X 80S/840 1x PSU BV WB	51 W	Yes
910925868241	LL217X 80S/840 1x PSU BV O	51 W	Yes
910925868242	LL217X 80S/840 1x PSD BV O	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925868391	LL217X 120S/840 1x PSU BV WB TW3	80 W	Yes
910925868392	LL217X 120S/840 1x PSU BV MB TW3	80 W	Yes
910925868393	LL217X 120S/840 1x PSU BV NB TW3	80 W	Yes
910925868394	LL217X 80S/840 1x PSU BV MB TW3	50 W	Yes
910925868395	LL217X 80S/840 1x PSU BV NB TW3	50 W	Yes
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	48.5 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867535	LL217X 80S/840 1x PSD O 7x2.5	50 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867551	LL234X 160S/840 2x PSD O 7x1.5	100 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867556	LL234X 160S/840 2x PSU O 5x1.5	102 W	Yes

CoreLine Trunking gen2

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910925867557	LL234X 160S/840 2x PSU O 5x2.5	102 W	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	Yes	-	1%
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	Yes	-	1%
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	Yes	-	1%
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	Yes	-	1%
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	No	-	Not applicable
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	Yes	-	1%
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	Yes	-	1%
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	Yes	-	1%
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	No	-	Not applicable
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	No	-	Not applicable
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	Yes	-	1%
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	Yes	-	1%
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	Yes	-	1%
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	Yes	-	1%
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	Yes	Visible light communication	1%
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	No	-	Not applicable
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	Yes	-	1%
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	Yes	Visible light communication	1%
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	No	-	Not applicable
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	No	-	Not applicable
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	Yes	-	1%
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	No	-	Not applicable
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	Yes	-	1%
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	Yes	-	1%
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	Yes	Visible light communication	1%
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	No	-	Not applicable
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	No	-	Not applicable
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	Yes	-	1%
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	Yes	-	1%
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	Yes	Visible light communication	1%
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	No	-	Not applicable
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	No	-	Not applicable
910925867552	LL234X 160S/840 2x PSD O 7x2.5	Yes	-	1%
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	Yes	-	1%
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	Yes	-	1%
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	Yes	Visible light communication	1%
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	No	-	Not applicable
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	No	-	Not applicable
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	Yes	-	1%
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	Yes	-	1%
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	Yes	-	1%
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	No	-	Not applicable
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	No	-	Not applicable

CoreLine Trunking gen2

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	No	-	Not applicable
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	Yes	-	1%
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	No	-	Not applicable
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	Yes	-	1%
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	No	-	Not applicable
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	Yes	-	1%
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	No	-	Not applicable
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	Yes	-	1%
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	No	-	Not applicable
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	Yes	-	1%
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	No	-	Not applicable
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	Yes	-	1%
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	Yes	-	1%
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	Yes	-	1%
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	Yes	-	1%
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	No	-	Not applicable
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	No	-	Not applicable
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	No	-	Not applicable
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	No	-	Not applicable
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	No	-	Not applicable
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	No	-	Not applicable
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	No	-	Not applicable
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	No	-	Not applicable
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	No	-	Not applicable
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	No	-	Not applicable
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	No	-	Not applicable
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	No	-	Not applicable
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	No	-	Not applicable
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	No	-	Not applicable
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	No	-	Not applicable
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	No	-	Not applicable
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	No	-	Not applicable
910925868899	LL234X 90S/840 1x SIA WB 7x1.5	Yes	-	1%
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	Yes	-	1%
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	Yes	-	1%
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	Yes	-	1%
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	Yes	-	1%
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	Yes	-	1%
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	Yes	-	1%
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	Yes	-	1%
910925867498	LL217X 80S/840 1x PSD BV WB	Yes	-	1%
910925867525	LL217X 120S/840 1x PSU BV WB HE	No	-	Not applicable
910925867539	LL234X 240S/840 2x PSD BV WB HE	Yes	-	1%
910925867550	LL234X 160S/840 2x PSU BV WB	No	-	Not applicable
910925867698	LL217X 80S/840 1x PSU BV WB TW3	No	-	Not applicable
910925867699	LL234X 160S/840 1x PSU BV WB TW3	No	-	Not applicable
910925867701	LL234X 160S/840 2x PSU BV WB TW3	No	-	Not applicable
910925868236	LL217X 45S/840 1x PSU BV WB	No	-	Not applicable
910925868237	LL217X 45S/840 1x PSD BV WB	Yes	-	1%

CoreLine Trunking gen2

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925868238	LL217X 45S/840 1x PSU BV O	No	-	Not applicable
910925868239	LL217X 45S/840 1x PSD BV O	Yes	-	1%
910925868240	LL217X 80S/840 1x PSU BV WB	No	-	Not applicable
910925868241	LL217X 80S/840 1x PSU BV O	No	-	Not applicable
910925868242	LL217X 80S/840 1x PSD BV O	Yes	-	1%
910925868391	LL217X 120S/840 1x PSU BV WB TW3	No	-	Not applicable
910925868392	LL217X 120S/840 1x PSU BV MB TW3	No	-	Not applicable
910925868393	LL217X 120S/840 1x PSU BV NB TW3	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910925868394	LL217X 80S/840 1x PSU BV MB TW3	No	-	Not applicable
910925868395	LL217X 80S/840 1x PSU BV NB TW3	No	-	Not applicable
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	Yes	-	1%
910925867535	LL217X 80S/840 1x PSD O 7x2.5	Yes	-	1%
910925867551	LL234X 160S/840 2x PSD O 7x1.5	Yes	-	1%
910925867556	LL234X 160S/840 2x PSU O 5x1.5	No	-	Not applicable
910925867557	LL234X 160S/840 2x PSU O 5x2.5	No	-	Not applicable

Product Data

Order Code	Full Product Name	Product family code
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	LL234X
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	LL234X
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	LL234X
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	LL234X
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	LL212X
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	LL212X
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	LL212X
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	LL212X
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	LL212X
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	LL217X
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	LL217X
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	LL217X
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	LL217X
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	LL217X
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	LL217X
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	LL217X
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	LL217X
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	LL217X
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	LL217X
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	LL217X
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	LL217X
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	LL217X
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	LL217X
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	LL234X
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	LL234X
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	LL234X
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	LL234X
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	LL234X
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	LL234X
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	LL234X
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	LL234X


Order Code	Full Product Name	Product family code
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	LL234X
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	LL234X
910925867552	LL234X 160S/840 2x PSD O 7x2.5	LL234X
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	LL234X
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	LL234X
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	LL234X
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	LL234X
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	LL234X
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	LL217X
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	LL234X
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	LL234X
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	LL234X
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	LL217X
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	LL234X
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	LL234X
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	LL217X
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	LL217X
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	LL234X
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	LL234X
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	LL234X
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	LL234X
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	LL234X
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	LL234X
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	LL234X
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	LL234X
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	LL234X
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	LL234X
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	LL217X
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	LL212X
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	LL212X
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	LL212X

CoreLine Trunking gen2


Order Code	Full Product Name	Product family code
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	LL212X
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	LL212X
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	LL212X
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	LL217X
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	LL217X
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	LL217X
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	LL217X
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	LL217X
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	LL217X
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	LL234X
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	LL234X
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	LL234X
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	LL234X
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	LL234X
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	LL234X
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	LL234X
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	LL234X
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	LL234X
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	LL234X
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	LL217X
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	LL217X
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	LL217X
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	LL217X
910925867498	LL217X 80S/840 1x PSD BV WB	LL217X

Order Code	Full Product Name	Product family code
910925867525	LL217X 120S/840 1x PSU BV WB HE	LL217X
910925867539	LL234X 240S/840 2x PSD BV WB HE	LL234X
910925867550	LL234X 160S/840 2x PSU BV WB	LL234X
910925867698	LL217X 80S/840 1x PSU BV WB TW3	LL217X
910925867699	LL234X 160S/840 1x PSU BV WB TW3	LL234X
910925867701	LL234X 160S/840 2x PSU BV WB TW3	LL234X
910925868236	LL217X 45S/840 1x PSU BV WB	LL217X
910925868237	LL217X 45S/840 1x PSD BV WB	LL217X
910925868238	LL217X 45S/840 1x PSU BV O	LL217X
910925868239	LL217X 45S/840 1x PSD BV O	LL217X
910925868240	LL217X 80S/840 1x PSU BV WB	LL217X
910925868241	LL217X 80S/840 1x PSU BV O	LL217X
910925868242	LL217X 80S/840 1x PSD BV O	LL217X
910925868391	LL217X 120S/840 1x PSU BV WB TW3	LL217X
910925868392	LL217X 120S/840 1x PSU BV MB TW3	LL217X
910925868393	LL217X 120S/840 1x PSU BV NB TW3	LL217X
910925868394	LL217X 80S/840 1x PSU BV MB TW3	LL217X
910925868395	LL217X 80S/840 1x PSU BV NB TW3	LL217X
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	LL217X
910925867535	LL217X 80S/840 1x PSD O 7x2.5	LL217X
910925867551	LL234X 160S/840 2x PSD O 7x1.5	LL234X
910925867556	LL234X 160S/840 2x PSU O 5x1.5	LL234X
910925867557	LL234X 160S/840 2x PSU O 5x2.5	LL234X


Polar Wide Diagrams



Polar Normal (separate) - LL200XI -
910925868236




Polar Normal (separate) - LL200XI -
910925868217




Polar Normal (separate) - LL200XI -
910925868826

CoreLine Trunking gen2


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925868830




Polar Normal (separate) - LL200XI - 910925868218




Polar Normal (separate) - LL200XI - 910925868821




Polar Normal (separate) - LL200XI - 910925868820




Polar Normal (separate) - LL200XI - 910925868841




Polar Normal (separate) - LL200XI - 910925868850



Polar Normal (separate) - LL200XI - 910925868823




Polar Normal (separate) - LL200XI - 910925868825




Polar Normal (separate) - LL200XI - 910925868840


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925868843




Polar Normal (separate) - LL200XI - 910925868846




Polar Normal (separate) - LL200XI - 910925868842




Polar Normal (separate) - LL200XI - 910925868849




Polar Normal (separate) - LL200XI - 910925868828




Polar Normal (separate) - LL200XI - 910925868839



Polar Normal (separate) - LL200XI - 910925868835




Polar Normal (separate) - LL200XI - 910925868836




Polar Normal (separate) - LL200XI - 910925868852


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925868848




Polar Normal (separate) - LL200XI - 910925868851




Polar Normal (separate) - LL200XI - 910925868845




Polar Normal (separate) - LL200XI - 910925868844




Polar Normal (separate) - LL200XI - 910925868824




Polar Normal (separate) - LL200XI - 910925868994



Polar Normal (separate) - LL200XI - 910925867515




Polar Normal (separate) - LL200XI - 910925867525




Polar Normal (separate) - LL200XI - 910925867535

CoreLine Trunking gen2


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925867561




Polar Normal (separate) - LL200XI - 910925867526




Polar Normal (separate) - LL200XI - 910925867532




Polar Normal (separate) - LL200XI - 910925867533




Polar Normal (separate) - LL200XI - 910925867545




Polar Normal (separate) - LL200XI - 910925867560



Polar Normal (separate) - LL200XI - 910925867498




Polar Normal (separate) - LL200XI - 910925867523




Polar Normal (separate) - LL200XI - 910925867528


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925867530




Polar Normal (separate) - LL200XI - 910925867534




Polar Normal (separate) - LL200XI - 910925867540




Polar Normal (separate) - LL200XI - 910925867541




Polar Normal (separate) - LL200XI - 910925867542




Polar Normal (separate) - LL200XI - 910925867506



Polar Normal (separate) - LL200XI - 910925867524




Polar Normal (separate) - LL200XI - 910925867543




Polar Normal (separate) - LL200XI - 910925867549


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925867544




Polar Normal (separate) - LL200XI - 910925867554




Polar Normal (separate) - LL200XI - 910925867555




Polar Normal (separate) - LL200XI - 910925867527




Polar Normal (separate) - LL200XI - 910925867531




Polar Normal (separate) - LL200XI - 910925867536



Polar Normal (separate) - LL200XI - 910925867527




Polar Normal (separate) - LL200XI - 910925867539




Polar Normal (separate) - LL200XI - 910925867546


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925867551




Polar Normal (separate) - LL200XI - 910925867552




Polar Normal (separate) - LL200XI - 910925867556




Polar Normal (separate) - LL200XI - 910925867538




Polar Normal (separate) - LL200XI - 910925867550




Polar Normal (separate) - LL200XI - 910925867547



Polar Normal (separate) - LL200XI - 910925867557




Polar Normal (separate) - LL200XI - 910925867559




Polar Normal (separate) - LL200XI - 910925868234

CoreLine Trunking gen2


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925868235




Polar Normal (separate) - LL200XI - 910925868205




Polar Normal (separate) - LL200XI - 910925868232




Polar Normal (separate) - LL200XI - 910925868242




Polar Normal (separate) - LL200XI - 910925868233




Polar Normal (separate) - LL200XI - 910925868239



Polar Normal (separate) - LL200XI - 910925868240




Polar Normal (separate) - LL200XI - 910925868241




Polar Normal (separate) - LL200XI - 910925868238


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925867495




Polar Normal (separate) - LL200XI - 910925867509




Polar Normal (separate) - LL200XI - 910925867518




Polar Normal (separate) - LL200XI - 910925867522




Polar Normal (separate) - LL200XI - 910925867529




Polar Normal (separate) - LL200XI - 910925867548



Polar Normal (separate) - LL200XI - 910925867553




Polar Normal (separate) - LL200XI - 910925867558




Polar Normal (separate) - LL200XI - 910925868237

CoreLine Trunking gen2


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925868819




Polar Normal (separate) - LL200XI - 910925868822




Polar Normal (separate) - LL200XI - 910925868834




Polar Normal (separate) - LL200XI - 910925868837




Polar Normal (separate) - LL200XI - 910925868838




Polar Normal (separate) - LL200XI - 910925868847



Polar Normal (separate) - LL200XI - 910925868992




Polar Normal (separate) - LL200XI - 910925868991




Polar Normal (separate) - LL200XI - 910925868993

CoreLine Trunking gen2


Polar Wide Diagrams




Polar Normal (separate) - LL200XI - 910925868996




Polar Normal (separate) - LL200XI - 910925868995




Polar Normal (separate) - LL200XI - 910925868997




Polar Normal (separate) - LL200XI - 910925868998




Polar Normal (separate) - LL200XI - 910925869001



Polar Normal (separate) - LL200XI - 910925868999



Polar Normal (separate) - LL200XI - 910925868990



Polar Normal (separate) - LL200XI - 910925868989

CoreLine Trunking gen2

