



Easily upgrade your city's lighting for future-proof energy savings

AluRoad gen2

The AluRoad gen2 family is available in 2 versions, standard AluRoad gen2 and AluRoad gen2 Pro. These are available in 2 sizes, Mini and Medium. Standard AluRoad gen2 as BGPO20 Mini and BGPO25 Medium, AluRoad gen2 Pro as BGPO21 Mini and BGPO26 Medium. Standard AluRoad gen2 features a fixed spigot for both post top 0 degrees tilt and side entry with limited negative tilt. AluRoad gen2 Pro is equipped with an adjustable spigot allowing tilt settings in both post top and side entry, positive and negative. AluRoad gen2 enables you to easily upgrade your city's lighting and enjoy the benefits of LED technology, designated to further minimize Total Cost of Investment and Ownership. The family is ideally suited for both new build areas and streets as well as renovation of existing installations. This affordable family not only offers a clean and timeless design to blend in with the environment, but also brings high quality lighting and future proof solutions with significant energy and maintenance savings over a long operational life.

Benefits

- Easy to install in both post top and side entry application.
- Interesting total cost of ownership.
- Limited initial investment.
- Considerable reduction in energy usage and carbon footprint; further energy savings achievable when using CLO or stand alone dimming such as Dynadim.
- Signify Service tag (unique QR identification) for maintenance, installation, and spare part information.

AluRoad gen2

Features

- Easy to install in both post top and side entry application.
- Interesting total cost of ownership through future proof energy savings.
- Limited initial investment.
- Considerable reduction in energy usage and carbon footprint; further energy savings achievable when using CLO or standalone dimming such as Dynadim. Certainly, when using the Ultra Efficient versions available within the family.
- Signify Service tag (unique QR identification) for maintenance, installation, and spare part information.

Application

- Road and Street
- Residential
- Walkways
- Industrial area

Versions

AluRoad gen2 Pro Mini side entry




AluRoad gen2 Medium Pro product picture





AluRoad gen2 Pro Medium post top




Dimensional drawing



Luminaire	Dimensions (mm)								
	A	B	C	D	D'	E	F	G	H
Mini BGPO21 szajgot Ø48-60	428	405	74	102		336	230	115	
Mini BGPO21 szajgot Ø60-76	480	405	74		152	336	230	115	102
Medium BGPO25 szajgot Ø48-60	573	550	74	102		482	230	115	
Medium BGPO25 szajgot Ø60-76	625	550	74		152	482	230	115	102



Luminaire	Dimensions (mm)						
	A	B	C	D	E	F	G
Mini BGPO20	447	70	112	111	334	230	88
Medium BGPO25	592	70	112	111	481	230	88



AluRoad gen2

Product details

AluRoad gen2 Pro Mini top view



AluRoad gen2 Pro Medium bottom view



AluRoad gen2 Pro Mini with Zhaga socket



AluRoad gen2 Pro Mini with OLC



AluRoad gen2 Pro Mini bottom view



AluRoad gen2 Pro tilt indicator



AluRoad gen2 Pro family top view



AluRoad gen2 Pro family top view



AluRoad gen2 Pro interior



AluRoad gen2 Pro family bottom view



AluRoad gen2

Product details



AluRoad gen2 Pro family bottom view



AluRoad gen2 Pro 76mm spigot and tilt indicator



AluRoad gen2 Pro Medium with Zhaga socket



AluRoad gen2 Pro Medium with OLC



AluRoad gen2 Pro toolless opening option



AluRoad gen2 Pro Medium top view

General Information

Driver included	Yes
Number of gear units	1 unit
Service tag	Yes

Light Technical

Color rendering index (CRI)	70
Upward light output ratio	0

Mechanical and Housing

Optical cover type	Flat glass
Housing Color	Gray
Ingress protection code	IP66
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°

Approval and Application

CE mark	Yes
Flammability mark	-

General Information

Order Code	Full Product Name	Lamp family code
910925870303	BGP021 LED34/740 II DM GR 48/60A	LED34
910925870304	BGP021 LED51/740 II DM GR SRT 48/60A	LED51
910925870305	BGP021 LED69/740 DM GR SRG10 48/60A	LED69
910925870309	BGP021 LED34/740 DW GR SRT 48/60A	LED34
910925870310	BGP021 LED51/740 II DW GR SDM10E 48/60A	LED51
910925870311	BGP021 LED69/740 II DW GR SRT 48/60A	LED69
910925870314	BGP021 LED69/730 II DW GR 48/60A	LED69
910925870317	BGP021 LED34/730 DN GR 48/60A	LED34
910925870318	BGP021 LED51/730 II DN GR 48/60A	LED51
910925870319	BGP021 LED69/730 II DN GR SRT 48/60A	LED69
910925870392	BGP021 LED35/740 DM10 GR 48/60A	LED35
910925870393	BGP021 LED56/740 DM10 GR 48/60A	LED56
910925870394	BGP021 LED70/740 DM10 GR 48/60A	LED70
910925870396	BGP021 LED35/730 DM10 GR 48/60A	LED35
910925869084	BGP020 LED34/740 II DM CLO-DDF2	LED34
910925869085	BGP020 LED51/740 II DM CLO-DDF2	LED51

Order Code	Full Product Name	Lamp family code
910925869086	BGP020 LED69/740 II DM CLO-DDF2	LED69
910925869090	BGP020 LED34/740 II DW CLO-DDF2	LED34
910925869091	BGP020 LED51/740 II DW CLO-DDF2	LED51
910925869092	BGP020 LED69/740 II DW CLO-DDF2	LED69
910925869096	BGP020 LED34/740 II DN CLO-DDF2	LED34
910925869097	BGP020 LED51/740 II DN CLO-DDF2	LED51
910925869098	BGP020 LED69/740 II DN CLO-DDF2	LED69
910925869103	BGP020 LED34/730 II DM CLO-DDF2	LED34
910925869104	BGP020 LED51/730 II DM CLO-DDF2	LED51
910925869105	BGP020 LED69/730 II DM CLO-DDF2	LED69
910925869109	BGP020 LED34/730 II DW CLO-DDF2	LED34
910925869110	BGP020 LED51/730 II DW CLO-DDF2	LED51
910925869111	BGP020 LED69/730 II DW CLO-DDF2	LED69
910925869115	BGP020 LED34/730 II DN CLO-DDF2	LED34
910925869116	BGP020 LED51/730 II DN CLO-DDF2	LED51
910925869117	BGP020 LED69/730 II DN CLO-DDF2	LED69
910925869652	BGP020 LED51/740 II DM CLO-DDF243	LED51
910925869653	BGP020 LED69/740 II DM CLO-DDF243	LED69
910925869657	BGP020 LED34/740 II DN CLO-DDF243	LED34
910925869658	BGP020 LED51/740 II DN CLO-DDF243	LED51
910925869659	BGP020 LED69/740 II DN CLO-DDF243	LED69
910925869663	BGP020 LED34/740 II DW CLO-DDF243	LED34
910925869664	BGP020 LED51/740 II DW CLO-DDF243	LED51
910925869665	BGP020 LED69/740 II DW CLO-DDF243	LED69
910925870306	BGP026 LED91/740 II DM GR SRT 48/60A	LED91
910925870307	BGP026 LED113/740 II DM GR 48/60A	LED113
910925870308	BGP026 LED147/740 II DM GR SDM10E 48/60A	LED147
910925870312	BGP026 LED91/740 II DW GR 48/60A	LED91
910925870313	BGP026 LED113/740 II DW GR SRT 48/60A	LED113
910925870315	BGP026 LED113/730 DW GR SRG10 48/60A	LED113
910925870316	BGP026 LED147/730 II DW GR 48/60A	LED147
910925870320	BGP026 LED113/730 II DN GR 48/60A	LED113
910925870321	BGP026 LED147/730 II DN GR 48/60A	LED147
910925870389	BGP021 LED30/740 II DM GR CLO-DDF2A D18	LED30
910925870390	BGP021 LED50/740 II DM GR CLO-DDF2A D18	LED50
910925870395	BGP026 LED120/740 DM10 GR 48/60A	LED120
910925869087	BGP025 LED91/740 II DM CLO-DDF2	LED91
910925869088	BGP025 LED113/740 II DM CLO-DDF2	LED113
910925869089	BGP025 LED147/740 II DM CLO-DDF2	LED147
910925869093	BGP025 LED91/740 II DW CLO-DDF2	LED91
910925869094	BGP025 LED113/740 II DW CLO-DDF2	LED113
910925869095	BGP025 LED147/740 II DW CLO-DDF2	LED147
910925869099	BGP025 LED91/740 II DN CLO-DDF2	LED91
910925869101	BGP025 LED113/740 II DN CLO-DDF2	LED113
910925869102	BGP025 LED147/740 II DN CLO-DDF2	LED147
910925869106	BGP025 LED91/730 II DM CLO-DDF2	LED91
910925869107	BGP025 LED113/730 II DM CLO-DDF2	LED113
910925869108	BGP025 LED147/730 II DM CLO-DDF2	LED147
910925869112	BGP025 LED91/730 II DW CLO-DDF2	LED91
910925869113	BGP025 LED113/730 II DW CLO-DDF2	LED113
910925869114	BGP025 LED147/730 II DW CLO-DDF2	LED147
910925869118	BGP025 LED91/730 II DN CLO-DDF2	LED91

Order Code	Full Product Name	Lamp family code
910925869119	BGP025 LED113/730 II DN CLO-DDF2	LED113
910925869120	BGP025 LED147/730 II DN CLO-DDF2	LED147
910925869654	BGP025 LED91/740 II DM CLO-DDF243	LED91
910925869655	BGP025 LED113/740 II DM CLO-DDF243	LED113
910925869656	BGP025 LED147/740 II DM CLO-DDF243	LED147
910925869660	BGP025 LED91/740 II DN CLO-DDF243	LED91
910925869661	BGP025 LED113/740 II DN CLO-DDF243	LED113
910925869662	BGP025 LED147/740 II DN CLO-DDF243	LED147
910925869666	BGP025 LED91/740 II DW CLO-DDF243	LED91
910925869667	BGP025 LED113/740 II DW CLO-DDF243	LED113
910925869668	BGP025 LED147/740 II DW CLO-DDF243	LED147
910925870391	BGP026 LED147/740 II DW GR CLO-DDF2A D18	LED147

Light Technical (1/2)

Order Code	Full Product Name	Luminaire		Correlated		Luminaire	Correlated	Luminaire	Correlated		
		light beam spread	Light source color	Color Temperature (Nom)	Luminc Flux					light beam spread	Light source color
910925870303	BGP021 LED34/740 II DM GR 48/60A	5° x 55° x 150°	740 neutral white	4000 K	2,992 lm	910925870393	BGP021 LED56/740 DM10 GR 48/60A	5° x 55° x 150°	740 neutral white	4000 K	4,760 lm
910925870304	BGP021 LED51/740 II DM GR SRT 48/60A	5° x 55° x 150°	740 neutral white	4000 K	4,350 lm	910925870394	BGP021 LED70/740 DM10 GR 48/60A	5° x 55° x 150°	740 neutral white	4000 K	5,880 lm
910925870305	BGP021 LED69/740 DM GR SRG10 48/60A	5° x 55° x 150°	740 neutral white	4000 K	5,848 lm	910925870396	BGP021 LED35/730 DM10 GR 48/60A	5° x 55° x 150°	730 warm white	3000 K	3,010 lm
910925870309	BGP021 LED34/740 DW GR SRT 48/60A	23° x 59° x 148°	740 neutral white	4000 K	2,992 lm	910925869084	BGP020 LED34/740 II DM CLO-DDF2	5° x 55° x 150°	740 neutral white	4000 K	2,937 lm
910925870310	BGP021 LED51/740 II DW GR SDM10E 48/60A	23° x 59° x 148°	740 neutral white	4000 K	4,350 lm	910925869085	BGP020 LED51/740 II DM CLO-DDF2	5° x 55° x 150°	740 neutral white	4000 K	4,312 lm
910925870311	BGP021 LED69/740 II DW GR SRT 48/60A	23° x 59° x 148°	740 neutral white	4000 K	5,848 lm	910925869086	BGP020 LED69/740 II DM CLO-DDF2	5° x 55° x 150°	740 neutral white	4000 K	5,742 lm
910925870314	BGP021 LED69/730 II DW GR 48/60A	23° x 59° x 148°	730 warm white	3000 K	5,848 lm	910925869090	BGP020 LED34/740 II DW CLO-DDF2	23° x 59° x 148°	740 neutral white	4000 K	2,904 lm
910925870317	BGP021 LED34/730 DN GR 48/60A	23° x 44° x 152°	730 warm white	3000 K	3,026 lm	910925869091	BGP020 LED51/740 II DW CLO-DDF2	23° x 59° x 148°	740 neutral white	4000 K	4,263 lm
910925870318	BGP021 LED51/730 II DN GR 48/60A	23° x 44° x 152°	730 warm white	3000 K	4,400 lm	910925869092	BGP020 LED69/740 II DW CLO-DDF2	23° x 59° x 148°	740 neutral white	4000 K	5,742 lm
910925870319	BGP021 LED69/730 II DN GR SRT 48/60A	23° x 44° x 152°	730 warm white	3000 K	5,916 lm	910925869096	BGP020 LED34/740 II DN CLO-DDF2	23° x 44° x 152°	740 neutral white	4000 K	2,937 lm
910925870392	BGP021 LED35/740 DM10 GR 48/60A	5° x 55° x 150°	740 neutral white	4000 K	3,010 lm	910925869097	BGP020 LED51/740 II DN CLO-DDF2	23° x 44° x 152°	740 neutral white	4000 K	4,312 lm

AluRoad gen2

Order Code	Full Product Name	Luminaire		Correlated			Order Code	Full Product Name	Luminaire		Correlated	
		light beam spread	Light source color	Color Temperature (Nom)	Luminc Flux	light beam spread			Light source color	Color Temperature (Nom)	Luminous Flux	
910925869098	BGP020 LED69/740 II DN CLO- DDF2	23° x 44° x 152°	740 neutral white	4000 K	5,742 lm	910925869664	BGP020 LED51/740 II DW CLO- DDF243	23° x 59° x 148°	740 neutral white	4000 K	4,263 lm	
910925869103	BGP020 LED34/730 II DM CLO- DDF2	5° x 55° x 150°	730 warm white	3000 K	2,937 lm	910925869665	BGP020 LED69/740 II DW CLO- DDF243	23° x 59° x 148°	740 neutral white	4000 K	5,742 lm	
910925869104	BGP020 LED51/730 II DM CLO- DDF2	5° x 55° x 150°	730 warm white	3000 K	4,312 lm	910925870306	BGP026 LED91/740 II DM GR SRT 48/60A	5° x 55° x 150°	740 neutral white	4000 K	7,740 lm	
910925869105	BGP020 LED69/730 II DM CLO- DDF2	5° x 55° x 150°	730 warm white	3000 K	5,568 lm	910925870307	BGP026 LED113/740 II DM GR 48/60A	5° x 55° x 150°	740 neutral white	4000 K	9,775 lm	
910925869109	BGP020 LED34/730 II DW CLO- DDF2	23° x 59° x 148°	730 warm white	3000 K	2,904 lm	910925870308	BGP026 LED147/740 II DM GR SDM10E 48/60A	5° x 55° x 150°	740 neutral white	4000 K	12,325 lm	
910925869110	BGP020 LED51/730 II DW CLO- DDF2	23° x 59° x 148°	730 warm white	3000 K	4,263 lm	910925870312	BGP026 LED91/740 II DW GR 48/60A	23° x 59° x 148°	740 neutral white	4000 K	7,740 lm	
910925869111	BGP020 LED69/730 II DW CLO- DDF2	23° x 59° x 148°	730 warm white	3000 K	5,568 lm	910925870313	BGP026 LED113/740 II DW GR SRT 48/60A	23° x 59° x 148°	740 neutral white	4000 K	9,890 lm	
910925869115	BGP020 LED34/730 II DN CLO- DDF2	23° x 44° x 152°	730 warm white	3000 K	2,937 lm	910925870315	BGP026 LED113/730 DW GR SRG10 48/60A	23° x 59° x 148°	730 warm white	3000 K	9,890 lm	
910925869116	BGP020 LED51/730 II DN CLO- DDF2	23° x 44° x 152°	730 warm white	3000 K	4,312 lm	910925870316	BGP026 LED147/730 II DW GR 48/60A	23° x 59° x 148°	730 warm white	3000 K	12,325 lm	
910925869117	BGP020 LED69/730 II DN CLO- DDF2	23° x 44° x 152°	730 warm white	3000 K	5,568 lm	910925870320	BGP026 LED113/730 II DN GR 48/60A	23° x 44° x 152°	730 warm white	3000 K	9,890 lm	
910925869652	BGP020 LED51/740 II DM CLO- DDF243	5° x 55° x 150°	740 neutral white	4000 K	4,312 lm	910925870321	BGP026 LED147/730 II DN GR 48/60A	23° x 44° x 152°	730 warm white	3000 K	12,325 lm	
910925869653	BGP020 LED69/740 II DM CLO- DDF243	5° x 55° x 150°	740 neutral white	4000 K	5,742 lm	910925870389	BGP021 LED30/740 II DM GR CLO-DDF2A D18	5° x 55° x 150°	740 neutral white	4000 K	2,552 lm	
910925869657	BGP020 LED34/740 II DN CLO- DDF243	23° x 44° x 152°	740 neutral white	4000 K	2,937 lm	910925870390	BGP021 LED50/740 II DM GR CLO-DDF2A D18	5° x 55° x 150°	740 neutral white	4000 K	4,176 lm	
910925869658	BGP020 LED51/740 II DN CLO- DDF243	23° x 44° x 152°	740 neutral white	4000 K	4,312 lm	910925870395	BGP026 LED120/740 DM10 GR 48/60A	5° x 55° x 150°	740 neutral white	4000 K	10,320 lm	
910925869659	BGP020 LED69/740 II DN CLO- DDF243	23° x 44° x 152°	740 neutral white	4000 K	5,742 lm	910925869087	BGP025 LED91/740 II DM CLO- DDF2	5° x 55° x 150°	740 neutral white	4000 K	7,482 lm	
910925869663	BGP020 LED34/740 II DW CLO- DDF243	23° x 59° x 148°	740 neutral white	4000 K	2,904 lm	910925869088	BGP025 LED113/740 II DM CLO- DDF2	5° x 55° x 150°	740 neutral white	4000 K	9,030 lm	

AluRoad gen2

Order Code	Full Product Name	Luminaire	Correlated			Luminaire	Correlated				
		light beam spread	Light source color	Color Temperature (Nom)	Luminc Flux		light beam spread	Light source color	Color Temperature (Nom)	Luminous Flux	
910925869089	BGP025 LED147/740 II DM CLO- DDF2	5° x 55° x 150°	740 neutral white	4000 K	11,475 lm	910925869118	BGP025 LED91/730 II DN CLO- DDF2	23° x 44° x 152°	730 warm white	3000 K	7,568 lm
910925869093	BGP025 LED91/740 II DW CLO- DDF2	23° x 59° x 148°	740 neutral white	4000 K	7,482 lm	910925869119	BGP025 LED113/730 II DN CLO- DDF2	23° x 44° x 152°	730 warm white	3000 K	9,135 lm
910925869094	BGP025 LED113/740 II DW CLO- DDF2	23° x 59° x 148°	740 neutral white	4000 K	9,030 lm	910925869120	BGP025 LED147/730 II DN CLO- DDF2	23° x 44° x 152°	730 warm white	3000 K	11,610 lm
910925869095	BGP025 LED147/740 II DW CLO- DDF2	23° x 59° x 148°	740 neutral white	4000 K	11,475 lm	910925869654	BGP025 LED91/740 II DM CLO- DDF243	5° x 55° x 150°	740 neutral white	4000 K	7,482 lm
910925869099	BGP025 LED91/740 II DN CLO- DDF2	23° x 44° x 152°	740 neutral white	4000 K	7,568 lm	910925869655	BGP025 LED113/740 II DM CLO- DDF243	5° x 55° x 150°	740 neutral white	4000 K	9,030 lm
910925869101	BGP025 LED113/740 II DN CLO- DDF2	23° x 44° x 152°	740 neutral white	4000 K	9,135 lm	910925869656	BGP025 LED147/740 II DM CLO- DDF243	5° x 55° x 150°	740 neutral white	4000 K	11,475 lm
910925869102	BGP025 LED147/740 II DN CLO- DDF2	23° x 44° x 152°	740 neutral white	4000 K	11,610 lm	910925869660	BGP025 LED91/740 II DN CLO- DDF243	23° x 44° x 152°	740 neutral white	4000 K	7,568 lm
910925869106	BGP025 LED91/730 II DM CLO- DDF2	5° x 55° x 150°	730 warm white	3000 K	7,482 lm	910925869661	BGP025 LED113/740 II DN CLO- DDF243	23° x 44° x 152°	740 neutral white	4000 K	9,135 lm
910925869107	BGP025 LED113/730 II DM CLO- DDF2	5° x 55° x 150°	730 warm white	3000 K	9,030 lm	910925869662	BGP025 LED147/740 II DN CLO- DDF243	23° x 44° x 152°	740 neutral white	4000 K	11,610 lm
910925869108	BGP025 LED147/730 II DM CLO- DDF2	5° x 55° x 150°	730 warm white	3000 K	11,475 lm	910925869666	BGP025 LED91/740 II DW CLO- DDF243	23° x 59° x 148°	740 neutral white	4000 K	7,482 lm
910925869112	BGP025 LED91/730 II DW CLO- DDF2	23° x 59° x 148°	730 warm white	3000 K	7,482 lm	910925869667	BGP025 LED113/740 II DW CLO- DDF243	23° x 59° x 148°	740 neutral white	4000 K	9,030 lm
910925869113	BGP025 LED113/730 II DW CLO- DDF2	23° x 59° x 148°	730 warm white	3000 K	9,030 lm	910925869668	BGP025 LED147/740 II DW CLO-DDF243	23° x 59° x 148°	740 neutral white	4000 K	11,475 lm
910925869114	BGP025 LED147/730 II DW CLO- DDF2	23° x 59° x 148°	730 warm white	3000 K	11,475 lm	910925870391	BGP026 LED147/740 II DW GR CLO-DDF2A D18	23° x 59° x 148°	740 neutral white	4000 K	12,325 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type outdoor	Order Code	Full Product Name	Optic type outdoor
910925870303	BGP021 LED34/740 II DM GR 48/60A	Distribution medium	910925870314	BGP021 LED69/730 II DW GR 48/60A	Distribution wide
910925870304	BGP021 LED51/740 II DM GR SRT 48/60A	Distribution medium	910925870317	BGP021 LED34/730 DN GR 48/60A	Distribution narrow
910925870305	BGP021 LED69/740 DM GR SRG10 48/60A	Distribution medium	910925870318	BGP021 LED51/730 II DN GR 48/60A	Distribution narrow
910925870309	BGP021 LED34/740 DW GR SRT 48/60A	Distribution wide	910925870319	BGP021 LED69/730 II DN GR SRT 48/60A	Distribution narrow
910925870310	BGP021 LED51/740 II DW GR SDM10E 48/60A	Distribution wide	910925870392	BGP021 LED35/740 DM10 GR 48/60A	Distribution wide
910925870311	BGP021 LED69/740 II DW GR SRT 48/60A	Distribution wide	910925870393	BGP021 LED56/740 DM10 GR 48/60A	Distribution wide

Order Code	Full Product Name	Optic type outdoor
910925870394	BGP021 LED70/740 DM10 GR 48/60A	Distribution wide
910925870396	BGP021 LED35/730 DM10 GR 48/60A	Distribution wide
910925869084	BGP020 LED34/740 II DM CLO-DDF2	Distribution medium
910925869085	BGP020 LED51/740 II DM CLO-DDF2	Distribution medium
910925869086	BGP020 LED69/740 II DM CLO-DDF2	Distribution medium
910925869090	BGP020 LED34/740 II DW CLO-DDF2	Distribution wide
910925869091	BGP020 LED51/740 II DW CLO-DDF2	Distribution wide
910925869092	BGP020 LED69/740 II DW CLO-DDF2	Distribution wide
910925869096	BGP020 LED34/740 II DN CLO-DDF2	Distribution narrow
910925869097	BGP020 LED51/740 II DN CLO-DDF2	Distribution narrow
910925869098	BGP020 LED69/740 II DN CLO-DDF2	Distribution narrow
910925869103	BGP020 LED34/730 II DM CLO-DDF2	Distribution medium
910925869104	BGP020 LED51/730 II DM CLO-DDF2	Distribution medium
910925869105	BGP020 LED69/730 II DM CLO-DDF2	Distribution medium
910925869109	BGP020 LED34/730 II DW CLO-DDF2	Distribution wide
910925869110	BGP020 LED51/730 II DW CLO-DDF2	Distribution wide
910925869111	BGP020 LED69/730 II DW CLO-DDF2	Distribution wide
910925869115	BGP020 LED34/730 II DN CLO-DDF2	Distribution narrow
910925869116	BGP020 LED51/730 II DN CLO-DDF2	Distribution narrow
910925869117	BGP020 LED69/730 II DN CLO-DDF2	Distribution narrow
910925869652	BGP020 LED51/740 II DM CLO-DDF243	Distribution medium
910925869653	BGP020 LED69/740 II DM CLO-DDF243	Distribution medium
910925869657	BGP020 LED34/740 II DN CLO-DDF243	Distribution narrow
910925869658	BGP020 LED51/740 II DN CLO-DDF243	Distribution narrow
910925869659	BGP020 LED69/740 II DN CLO-DDF243	Distribution narrow
910925869663	BGP020 LED34/740 II DW CLO-DDF243	Distribution wide
910925869664	BGP020 LED51/740 II DW CLO-DDF243	Distribution wide
910925869665	BGP020 LED69/740 II DW CLO-DDF243	Distribution wide
910925870306	BGP026 LED91/740 II DM GR SRT 48/60A	Distribution medium
910925870307	BGP026 LED113/740 II DM GR 48/60A	Distribution medium
910925870308	BGP026 LED147/740 II DM GR SDM10E 48/60A	Distribution medium
910925870312	BGP026 LED91/740 II DW GR 48/60A	Distribution wide
910925870313	BGP026 LED113/740 II DW GR SRT 48/60A	Distribution wide
910925870315	BGP026 LED113/730 DW GR SRG10 48/60A	Distribution wide

Order Code	Full Product Name	Optic type outdoor
910925870316	BGP026 LED147/730 II DW GR 48/60A	Distribution wide
910925870320	BGP026 LED113/730 II DN GR 48/60A	Distribution narrow
910925870321	BGP026 LED147/730 II DN GR 48/60A	Distribution narrow
910925870389	BGP021 LED30/740 II DM GR CLO-DDF2A D18	Distribution wide
910925870390	BGP021 LED50/740 II DM GR CLO-DDF2A D18	Distribution wide
910925870395	BGP026 LED120/740 DM10 GR 48/60A	Distribution wide
910925869087	BGP025 LED91/740 II DM CLO-DDF2	Distribution medium
910925869088	BGP025 LED113/740 II DM CLO-DDF2	Distribution medium
910925869089	BGP025 LED147/740 II DM CLO-DDF2	Distribution medium
910925869093	BGP025 LED91/740 II DW CLO-DDF2	Distribution wide
910925869094	BGP025 LED113/740 II DW CLO-DDF2	Distribution wide
910925869095	BGP025 LED147/740 II DW CLO-DDF2	Distribution wide
910925869099	BGP025 LED91/740 II DN CLO-DDF2	Distribution narrow
910925869101	BGP025 LED113/740 II DN CLO-DDF2	Distribution narrow
910925869102	BGP025 LED147/740 II DN CLO-DDF2	Distribution narrow
910925869106	BGP025 LED91/730 II DM CLO-DDF2	Distribution medium
910925869107	BGP025 LED113/730 II DM CLO-DDF2	Distribution medium
910925869108	BGP025 LED147/730 II DM CLO-DDF2	Distribution medium
910925869112	BGP025 LED91/730 II DW CLO-DDF2	Distribution wide
910925869113	BGP025 LED113/730 II DW CLO-DDF2	Distribution wide
910925869114	BGP025 LED147/730 II DW CLO-DDF2	Distribution wide
910925869118	BGP025 LED91/730 II DN CLO-DDF2	Distribution narrow
910925869119	BGP025 LED113/730 II DN CLO-DDF2	Distribution narrow
910925869120	BGP025 LED147/730 II DN CLO-DDF2	Distribution narrow
910925869654	BGP025 LED91/740 II DM CLO-DDF243	Distribution medium
910925869655	BGP025 LED113/740 II DM CLO-DDF243	Distribution medium
910925869656	BGP025 LED147/740 II DM CLO-DDF243	Distribution medium
910925869660	BGP025 LED91/740 II DN CLO-DDF243	Distribution narrow
910925869661	BGP025 LED113/740 II DN CLO-DDF243	Distribution narrow
910925869662	BGP025 LED147/740 II DN CLO-DDF243	Distribution narrow
910925869666	BGP025 LED91/740 II DW CLO-DDF243	Distribution wide
910925869667	BGP025 LED113/740 II DW CLO-DDF243	Distribution wide
910925869668	BGP025 LED147/740 II DW CLO-DDF243	Distribution wide
910925870391	BGP026 LED147/740 II DW GR CLO-DDF2A D18	Distribution wide

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925870303	BGP021 LED34/740 II DM GR 48/60A	19.4 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870304	BGP021 LED51/740 II DM GR SRT 48/60A	28 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925870305	BGP021 LED69/740 DM GR SRG10 48/60A	39 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925870309	BGP021 LED34/740 DW GR SRT 48/60A	19 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925870310	BGP021 LED51/740 II DW GR SDM10E 48/60A	28 W	Luminaire surge protection level until 6 kV differential mode and 10 kV common mode
910925870311	BGP021 LED69/740 II DW GR SRT 48/60A	38.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870314	BGP021 LED69/730 II DW GR 48/60A	41 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870317	BGP021 LED34/730 DN GR 48/60A	20.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870318	BGP021 LED51/730 II DN GR 48/60A	29.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870319	BGP021 LED69/730 II DN GR SRT 48/60A	40.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870392	BGP021 LED35/740 DM10 GR 48/60A	19.6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870393	BGP021 LED56/740 DM10 GR 48/60A	31 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870394	BGP021 LED70/740 DM10 GR 48/60A	39.5 W	Luminaire surge protection level

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925870396	BGP021 LED35/730 DM10 GR 48/60A	20.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869084	BGP020 LED34/740 II DM CLO- DDF2	19 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869085	BGP020 LED51/740 II DM CLO- DDF2	28.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869086	BGP020 LED69/740 II DM CLO- DDF2	39 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869090	BGP020 LED34/740 II DW CLO- DDF2	19 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869091	BGP020 LED51/740 II DW CLO- DDF2	28.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869092	BGP020 LED69/740 II DW CLO- DDF2	39 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869096	BGP020 LED34/740 II DN CLO- DDF2	19 W	Luminaire surge protection level until 6 kV differential mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
			and 8 kV common mode
910925869097	BGP020 LED51/740 II DN CLO- DDF2	28.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869098	BGP020 LED69/740 II DN CLO- DDF2	39 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869103	BGP020 LED34/730 II DM CLO- DDF2	20 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869104	BGP020 LED51/730 II DM CLO- DDF2	30 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869105	BGP020 LED69/730 II DM CLO- DDF2	41 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869109	BGP020 LED34/730 II DW CLO- DDF2	20 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869110	BGP020 LED51/730 II DW CLO- DDF2	30 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869111	BGP020 LED69/730 II DW CLO- DDF2	41 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925869115	BGP020 LED34/730 II DN CLO- DDF2	20 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869116	BGP020 LED51/730 II DN CLO- DDF2	30 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869117	BGP020 LED69/730 II DN CLO- DDF2	41 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869652	BGP020 LED51/740 II DM CLO- DDF243	28.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869653	BGP020 LED69/740 II DM CLO- DDF243	39 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869657	BGP020 LED34/740 II DN CLO- DDF243	19 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869658	BGP020 LED51/740 II DN CLO- DDF243	28.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869659	BGP020 LED69/740 II DN CLO- DDF243	39 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869663	BGP020 LED34/740 II DW CLO- DDF243	19 W	Luminaire surge protection level

AluRoad gen2

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
			until 6 kV differential mode and 8 kV common mode
910925869664	BGP020 LED51/740 II DW CLO- DDF243	28.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869665	BGP020 LED69/740 II DW CLO- DDF243	39 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870306	BGP026 LED91/740 II DM GR SRT 48/60A	49.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870307	BGP026 LED113/740 II DM GR 48/60A	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870308	BGP026 LED147/740 II DM GR SDM10E 48/60A	81 W	Luminaire surge protection level until 6 kV differential mode and 10 kV common mode
910925870312	BGP026 LED91/740 II DW GR 48/60A	49 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870313	BGP026 LED113/740 II DW GR SRT 48/60A	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870315	BGP026 LED113/730 DW GR SRG10 48/60A	64 W	Luminaire surge protection level until 10 kV differential mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
			and 10 kV common mode
910925870316	BGP026 LED147/730 II DW GR 48/60A	85 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870320	BGP026 LED113/730 II DN GR 48/60A	64 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870321	BGP026 LED147/730 II DN GR 48/60A	85 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870389	BGP021 LED30/740 II DM GR CLO-DDF2A D18	17.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870390	BGP021 LED50/740 II DM GR CLO-DDF2A D18	27.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870395	BGP026 LED120/740 DM10 GR 48/60A	65 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869087	BGP025 LED91/740 II DM CLO- DDF2	49.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869088	BGP025 LED113/740 II DM CLO- DDF2	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925869089	BGP025 LED147/740 II DM CLO- DDF2	81 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869093	BGP025 LED91/740 II DW CLO- DDF2	49.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869094	BGP025 LED113/740 II DW CLO- DDF2	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869095	BGP025 LED147/740 II DW CLO- DDF2	81 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869099	BGP025 LED91/740 II DN CLO- DDF2	49.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869101	BGP025 LED113/740 II DN CLO- DDF2	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869102	BGP025 LED147/740 II DN CLO- DDF2	81 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869106	BGP025 LED91/730 II DM CLO- DDF2	52 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869107	BGP025 LED113/730 II DM CLO- DDF2	64 W	Luminaire surge protection level

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925869108	BGP025 LED147/730 II DM CLO- DDF2	85 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869112	BGP025 LED91/730 II DW CLO- DDF2	52 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869113	BGP025 LED113/730 II DW CLO- DDF2	64 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869114	BGP025 LED147/730 II DW CLO- DDF2	85 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869118	BGP025 LED91/730 II DN CLO- DDF2	52 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869119	BGP025 LED113/730 II DN CLO- DDF2	64 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869120	BGP025 LED147/730 II DN CLO- DDF2	85 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869654	BGP025 LED91/740 II DM CLO- DDF243	49.5 W	Luminaire surge protection level until 6 kV differential mode

AluRoad gen2

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
			and 8 kV common mode
910925869655	BGP025 LED113/740 II DM CLO- DDF243	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869656	BGP025 LED147/740 II DM CLO- DDF243	81 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869660	BGP025 LED91/740 II DN CLO- DDF243	49.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869661	BGP025 LED113/740 II DN CLO- DDF243	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869662	BGP025 LED147/740 II DN CLO- DDF243	81 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925869666	BGP025 LED91/740 II DW CLO- DDF243	49.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869667	BGP025 LED113/740 II DW CLO- DDF243	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869668	BGP025 LED147/740 II DW CLO- DDF243	81 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870391	BGP026 LED147/740 II DW GR CLO-DDF2A D18	81 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925870303	BGP021 LED34/740 II DM GR 48/60A	No
910925870304	BGP021 LED51/740 II DM GR SRT 48/60A	Yes
910925870305	BGP021 LED69/740 DM GR SRG10 48/60A	No
910925870309	BGP021 LED34/740 DW GR SRT 48/60A	Yes
910925870310	BGP021 LED51/740 II DW GR SDM10E 48/60A	No
910925870311	BGP021 LED69/740 II DW GR SRT 48/60A	Yes
910925870314	BGP021 LED69/730 II DW GR 48/60A	No
910925870317	BGP021 LED34/730 DN GR 48/60A	No
910925870318	BGP021 LED51/730 II DN GR 48/60A	No
910925870319	BGP021 LED69/730 II DN GR SRT 48/60A	Yes
910925870392	BGP021 LED35/740 DM10 GR 48/60A	Yes
910925870393	BGP021 LED56/740 DM10 GR 48/60A	Yes
910925870394	BGP021 LED70/740 DM10 GR 48/60A	Yes
910925870396	BGP021 LED35/730 DM10 GR 48/60A	Yes

Order Code	Full Product Name	Dimmable
910925869084	BGP020 LED34/740 II DM CLO-DDF2	Yes
910925869085	BGP020 LED51/740 II DM CLO-DDF2	Yes
910925869086	BGP020 LED69/740 II DM CLO-DDF2	Yes
910925869090	BGP020 LED34/740 II DW CLO-DDF2	Yes
910925869091	BGP020 LED51/740 II DW CLO-DDF2	Yes
910925869092	BGP020 LED69/740 II DW CLO-DDF2	Yes
910925869096	BGP020 LED34/740 II DN CLO-DDF2	Yes
910925869097	BGP020 LED51/740 II DN CLO-DDF2	Yes
910925869098	BGP020 LED69/740 II DN CLO-DDF2	Yes
910925869103	BGP020 LED34/730 II DM CLO-DDF2	Yes
910925869104	BGP020 LED51/730 II DM CLO-DDF2	Yes
910925869105	BGP020 LED69/730 II DM CLO-DDF2	Yes
910925869109	BGP020 LED34/730 II DW CLO-DDF2	Yes
910925869110	BGP020 LED51/730 II DW CLO-DDF2	Yes

Order Code	Full Product Name	Dimmable
910925869111	BGP020 LED69/730 II DW CLO-DDF2	Yes
910925869115	BGP020 LED34/730 II DN CLO-DDF2	Yes
910925869116	BGP020 LED51/730 II DN CLO-DDF2	Yes
910925869117	BGP020 LED69/730 II DN CLO-DDF2	Yes
910925869652	BGP020 LED51/740 II DM CLO-DDF243	Yes
910925869653	BGP020 LED69/740 II DM CLO-DDF243	Yes
910925869657	BGP020 LED34/740 II DN CLO-DDF243	Yes
910925869658	BGP020 LED51/740 II DN CLO-DDF243	Yes
910925869659	BGP020 LED69/740 II DN CLO-DDF243	Yes
910925869663	BGP020 LED34/740 II DW CLO-DDF243	Yes
910925869664	BGP020 LED51/740 II DW CLO-DDF243	Yes
910925869665	BGP020 LED69/740 II DW CLO-DDF243	Yes
910925870306	BGP026 LED91/740 II DM GR SRT 48/60A	Yes
910925870307	BGP026 LED113/740 II DM GR 48/60A	No
910925870308	BGP026 LED147/740 II DM GR SDM10E 48/60A	No
910925870312	BGP026 LED91/740 II DW GR 48/60A	No
910925870313	BGP026 LED113/740 II DW GR SRT 48/60A	Yes
910925870315	BGP026 LED113/730 DW GR SRG10 48/60A	No
910925870316	BGP026 LED147/730 II DW GR 48/60A	No
910925870320	BGP026 LED113/730 II DN GR 48/60A	No
910925870321	BGP026 LED147/730 II DN GR 48/60A	No
910925870389	BGP021 LED30/740 II DM GR CLO-DDF2A D18	No
910925870390	BGP021 LED50/740 II DM GR CLO-DDF2A D18	No
910925870395	BGP026 LED120/740 DM10 GR 48/60A	Yes
910925869087	BGP025 LED91/740 II DM CLO-DDF2	Yes
910925869088	BGP025 LED113/740 II DM CLO-DDF2	Yes

Order Code	Full Product Name	Dimmable
910925869089	BGP025 LED147/740 II DM CLO-DDF2	Yes
910925869093	BGP025 LED91/740 II DW CLO-DDF2	Yes
910925869094	BGP025 LED113/740 II DW CLO-DDF2	Yes
910925869095	BGP025 LED147/740 II DW CLO-DDF2	Yes
910925869099	BGP025 LED91/740 II DN CLO-DDF2	Yes
910925869101	BGP025 LED113/740 II DN CLO-DDF2	Yes
910925869102	BGP025 LED147/740 II DN CLO-DDF2	Yes
910925869106	BGP025 LED91/730 II DM CLO-DDF2	Yes
910925869107	BGP025 LED113/730 II DM CLO-DDF2	Yes
910925869108	BGP025 LED147/730 II DM CLO-DDF2	Yes
910925869112	BGP025 LED91/730 II DW CLO-DDF2	Yes
910925869113	BGP025 LED113/730 II DW CLO-DDF2	Yes
910925869114	BGP025 LED147/730 II DW CLO-DDF2	Yes
910925869118	BGP025 LED91/730 II DN CLO-DDF2	Yes
910925869119	BGP025 LED113/730 II DN CLO-DDF2	Yes
910925869120	BGP025 LED147/730 II DN CLO-DDF2	Yes
910925869654	BGP025 LED91/740 II DM CLO-DDF243	Yes
910925869655	BGP025 LED113/740 II DM CLO-DDF243	Yes
910925869656	BGP025 LED147/740 II DM CLO-DDF243	Yes
910925869660	BGP025 LED91/740 II DN CLO-DDF243	Yes
910925869661	BGP025 LED113/740 II DN CLO-DDF243	Yes
910925869662	BGP025 LED147/740 II DN CLO-DDF243	Yes
910925869666	BGP025 LED91/740 II DW CLO-DDF243	Yes
910925869667	BGP025 LED113/740 II DW CLO-DDF243	Yes
910925869668	BGP025 LED147/740 II DW CLO-DDF243	Yes
910925870391	BGP026 LED147/740 II DW GR CLO-DDF2A D18	No

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code
910925870303	BGP021 LED34/740 II DM GR 48/60A	IK09
910925870304	BGP021 LED51/740 II DM GR SRT 48/60A	IK09
910925870305	BGP021 LED69/740 DM GR SRG10 48/60A	IK09
910925870309	BGP021 LED34/740 DW GR SRT 48/60A	IK09
910925870310	BGP021 LED51/740 II DW GR SDM10E 48/60A	IK09
910925870311	BGP021 LED69/740 II DW GR SRT 48/60A	IK09
910925870314	BGP021 LED69/730 II DW GR 48/60A	IK09
910925870317	BGP021 LED34/730 DN GR 48/60A	IK09
910925870318	BGP021 LED51/730 II DN GR 48/60A	IK09
910925870319	BGP021 LED69/730 II DN GR SRT 48/60A	IK09
910925870392	BGP021 LED35/740 DM10 GR 48/60A	IK09
910925870393	BGP021 LED56/740 DM10 GR 48/60A	IK09
910925870394	BGP021 LED70/740 DM10 GR 48/60A	IK09
910925870396	BGP021 LED35/730 DM10 GR 48/60A	IK09
910925869084	BGP020 LED34/740 II DM CLO-DDF2	IK08
910925869085	BGP020 LED51/740 II DM CLO-DDF2	IK08
910925869086	BGP020 LED69/740 II DM CLO-DDF2	IK08
910925869090	BGP020 LED34/740 II DW CLO-DDF2	IK08
910925869091	BGP020 LED51/740 II DW CLO-DDF2	IK08
910925869092	BGP020 LED69/740 II DW CLO-DDF2	IK08
910925869096	BGP020 LED34/740 II DN CLO-DDF2	IK08

Order Code	Full Product Name	Mech. impact protection code
910925869097	BGP020 LED51/740 II DN CLO-DDF2	IK08
910925869098	BGP020 LED69/740 II DN CLO-DDF2	IK08
910925869103	BGP020 LED34/730 II DM CLO-DDF2	IK08
910925869104	BGP020 LED51/730 II DM CLO-DDF2	IK08
910925869105	BGP020 LED69/730 II DM CLO-DDF2	IK08
910925869109	BGP020 LED34/730 II DW CLO-DDF2	IK08
910925869110	BGP020 LED51/730 II DW CLO-DDF2	IK08
910925869111	BGP020 LED69/730 II DW CLO-DDF2	IK08
910925869115	BGP020 LED34/730 II DN CLO-DDF2	IK08
910925869116	BGP020 LED51/730 II DN CLO-DDF2	IK08
910925869117	BGP020 LED69/730 II DN CLO-DDF2	IK08
910925869652	BGP020 LED51/740 II DM CLO-DDF243	IK08
910925869653	BGP020 LED69/740 II DM CLO-DDF243	IK08
910925869657	BGP020 LED34/740 II DN CLO-DDF243	IK08
910925869658	BGP020 LED51/740 II DN CLO-DDF243	IK08
910925869659	BGP020 LED69/740 II DN CLO-DDF243	IK08
910925869663	BGP020 LED34/740 II DW CLO-DDF243	IK08
910925869664	BGP020 LED51/740 II DW CLO-DDF243	IK08
910925869665	BGP020 LED69/740 II DW CLO-DDF243	IK08
910925870306	BGP026 LED91/740 II DM GR SRT 48/60A	IK09
910925870307	BGP026 LED113/740 II DM GR 48/60A	IK09

Order Code	Full Product Name	Mech. impact protection code
910925870308	BGP026 LED147/740 II DM GR SDM10E 48/60A	IK09
910925870312	BGP026 LED91/740 II DW GR 48/60A	IK09
910925870313	BGP026 LED113/740 II DW GR SRT 48/60A	IK09
910925870315	BGP026 LED113/730 DW GR SRG10 48/60A	IK09
910925870316	BGP026 LED147/730 II DW GR 48/60A	IK09
910925870320	BGP026 LED113/730 II DN GR 48/60A	IK09
910925870321	BGP026 LED147/730 II DN GR 48/60A	IK09
910925870389	BGP021 LED30/740 II DM GR CLO-DDF2A D18	IK09
910925870390	BGP021 LED50/740 II DM GR CLO-DDF2A D18	IK09
910925870395	BGP026 LED120/740 DM10 GR 48/60A	IK09
910925869087	BGP025 LED91/740 II DM CLO-DDF2	IK08
910925869088	BGP025 LED113/740 II DM CLO-DDF2	IK08
910925869089	BGP025 LED147/740 II DM CLO-DDF2	IK08
910925869093	BGP025 LED91/740 II DW CLO-DDF2	IK08
910925869094	BGP025 LED113/740 II DW CLO-DDF2	IK08
910925869095	BGP025 LED147/740 II DW CLO-DDF2	IK08
910925869099	BGP025 LED91/740 II DN CLO-DDF2	IK08
910925869101	BGP025 LED113/740 II DN CLO-DDF2	IK08
910925869102	BGP025 LED147/740 II DN CLO-DDF2	IK08

Order Code	Full Product Name	Mech. impact protection code
910925869106	BGP025 LED91/730 II DM CLO-DDF2	IK08
910925869107	BGP025 LED113/730 II DM CLO-DDF2	IK08
910925869108	BGP025 LED147/730 II DM CLO-DDF2	IK08
910925869112	BGP025 LED91/730 II DW CLO-DDF2	IK08
910925869113	BGP025 LED113/730 II DW CLO-DDF2	IK08
910925869114	BGP025 LED147/730 II DW CLO-DDF2	IK08
910925869118	BGP025 LED91/730 II DN CLO-DDF2	IK08
910925869119	BGP025 LED113/730 II DN CLO-DDF2	IK08
910925869120	BGP025 LED147/730 II DN CLO-DDF2	IK08
910925869654	BGP025 LED91/740 II DM CLO-DDF243	IK08
910925869655	BGP025 LED113/740 II DM CLO-DDF243	IK08
910925869656	BGP025 LED147/740 II DM CLO-DDF243	IK08
910925869660	BGP025 LED91/740 II DN CLO-DDF243	IK08
910925869661	BGP025 LED113/740 II DN CLO-DDF243	IK08
910925869662	BGP025 LED147/740 II DN CLO-DDF243	IK08
910925869666	BGP025 LED91/740 II DW CLO-DDF243	IK08
910925869667	BGP025 LED113/740 II DW CLO-DDF243	IK08
910925869668	BGP025 LED147/740 II DW CLO-DDF243	IK08
910925870391	BGP026 LED147/740 II DW GR CLO-DDF2A D18	IK09

Product Data

Order Code	Full Product Name	Product family code
910925870303	BGP021 LED34/740 II DM GR 48/60A	BGP021
910925870304	BGP021 LED51/740 II DM GR SRT 48/60A	BGP021
910925870305	BGP021 LED69/740 DM GR SRG10 48/60A	BGP021
910925870309	BGP021 LED34/740 DW GR SRT 48/60A	BGP021
910925870310	BGP021 LED51/740 II DW GR SDM10E 48/60A	BGP021
910925870311	BGP021 LED69/740 II DW GR SRT 48/60A	BGP021
910925870314	BGP021 LED69/730 II DW GR 48/60A	BGP021
910925870317	BGP021 LED34/730 DN GR 48/60A	BGP021
910925870318	BGP021 LED51/730 II DN GR 48/60A	BGP021
910925870319	BGP021 LED69/730 II DN GR SRT 48/60A	BGP021
910925870392	BGP021 LED35/740 DM10 GR 48/60A	BGP021
910925870393	BGP021 LED56/740 DM10 GR 48/60A	BGP021
910925870394	BGP021 LED70/740 DM10 GR 48/60A	BGP021
910925870396	BGP021 LED35/730 DM10 GR 48/60A	BGP021
910925869084	BGP020 LED34/740 II DM CLO-DDF2	BGP020
910925869085	BGP020 LED51/740 II DM CLO-DDF2	BGP020
910925869086	BGP020 LED69/740 II DM CLO-DDF2	BGP020
910925869090	BGP020 LED34/740 II DW CLO-DDF2	BGP020
910925869091	BGP020 LED51/740 II DW CLO-DDF2	BGP020
910925869092	BGP020 LED69/740 II DW CLO-DDF2	BGP020
910925869096	BGP020 LED34/740 II DN CLO-DDF2	BGP020
910925869097	BGP020 LED51/740 II DN CLO-DDF2	BGP020
910925869098	BGP020 LED69/740 II DN CLO-DDF2	BGP020
910925869103	BGP020 LED34/730 II DM CLO-DDF2	BGP020
910925869104	BGP020 LED51/730 II DM CLO-DDF2	BGP020
910925869105	BGP020 LED69/730 II DM CLO-DDF2	BGP020
910925869109	BGP020 LED34/730 II DW CLO-DDF2	BGP020
910925869110	BGP020 LED51/730 II DW CLO-DDF2	BGP020

Order Code	Full Product Name	Product family code
910925869111	BGP020 LED69/730 II DW CLO-DDF2	BGP020
910925869115	BGP020 LED34/730 II DN CLO-DDF2	BGP020
910925869116	BGP020 LED51/730 II DN CLO-DDF2	BGP020
910925869117	BGP020 LED69/730 II DN CLO-DDF2	BGP020
910925869652	BGP020 LED51/740 II DM CLO-DDF243	BGP020
910925869653	BGP020 LED69/740 II DM CLO-DDF243	BGP020
910925869657	BGP020 LED34/740 II DN CLO-DDF243	BGP020
910925869658	BGP020 LED51/740 II DN CLO-DDF243	BGP020
910925869659	BGP020 LED69/740 II DN CLO-DDF243	BGP020
910925869663	BGP020 LED34/740 II DW CLO-DDF243	BGP020
910925869664	BGP020 LED51/740 II DW CLO-DDF243	BGP020
910925869665	BGP020 LED69/740 II DW CLO-DDF243	BGP020
910925870306	BGP026 LED91/740 II DM GR SRT 48/60A	BGP026
910925870307	BGP026 LED113/740 II DM GR 48/60A	BGP026
910925870308	BGP026 LED147/740 II DM GR SDM10E 48/60A	BGP026
910925870312	BGP026 LED91/740 II DW GR 48/60A	BGP026
910925870313	BGP026 LED113/740 II DW GR SRT 48/60A	BGP026
910925870315	BGP026 LED113/730 DW GR SRG10 48/60A	BGP026
910925870316	BGP026 LED147/730 II DW GR 48/60A	BGP026
910925870320	BGP026 LED113/730 II DN GR 48/60A	BGP026
910925870321	BGP026 LED147/730 II DN GR 48/60A	BGP026
910925870389	BGP021 LED30/740 II DM GR CLO-DDF2A D18	BGP021
910925870390	BGP021 LED50/740 II DM GR CLO-DDF2A D18	BGP021
910925870395	BGP026 LED120/740 DM10 GR 48/60A	BGP026
910925869087	BGP025 LED91/740 II DM CLO-DDF2	BGP025
910925869088	BGP025 LED113/740 II DM CLO-DDF2	BGP025
910925869089	BGP025 LED147/740 II DM CLO-DDF2	BGP025
910925869093	BGP025 LED91/740 II DW CLO-DDF2	BGP025

AluRoad gen2

Order Code	Full Product Name	Product family code
910925869094	BGP025 LED113/740 II DW CLO-DDF2	BGP025
910925869095	BGP025 LED147/740 II DW CLO-DDF2	BGP025
910925869099	BGP025 LED91/740 II DN CLO-DDF2	BGP025
910925869101	BGP025 LED113/740 II DN CLO-DDF2	BGP025
910925869102	BGP025 LED147/740 II DN CLO-DDF2	BGP025
910925869106	BGP025 LED91/730 II DM CLO-DDF2	BGP025
910925869107	BGP025 LED113/730 II DM CLO-DDF2	BGP025
910925869108	BGP025 LED147/730 II DM CLO-DDF2	BGP025
910925869112	BGP025 LED91/730 II DW CLO-DDF2	BGP025
910925869113	BGP025 LED113/730 II DW CLO-DDF2	BGP025
910925869114	BGP025 LED147/730 II DW CLO-DDF2	-
910925869118	BGP025 LED91/730 II DN CLO-DDF2	BGP025

Order Code	Full Product Name	Product family code
910925869119	BGP025 LED113/730 II DN CLO-DDF2	BGP025
910925869120	BGP025 LED147/730 II DN CLO-DDF2	BGP025
910925869654	BGP025 LED91/740 II DM CLO-DDF243	BGP025
910925869655	BGP025 LED113/740 II DM CLO-DDF243	BGP025
910925869656	BGP025 LED147/740 II DM CLO-DDF243	BGP025
910925869660	BGP025 LED91/740 II DN CLO-DDF243	BGP025
910925869661	BGP025 LED113/740 II DN CLO-DDF243	BGP025
910925869662	BGP025 LED147/740 II DN CLO-DDF243	BGP025
910925869666	BGP025 LED91/740 II DW CLO-DDF243	BGP025
910925869667	BGP025 LED113/740 II DW CLO-DDF243	BGP025
910925869668	BGP025 LED147/740 II DW CLO-DDF243	BGP025
910925870391	BGP026 LED147/740 II DW GR CLO-DDF2A D18	BGP026

