



Time to upgrade your conventional lighting to LumiStreet gen2

LumiStreet gen2

Increasing numbers of municipalities are having to upgrade large-scale conventional street lighting installations with energy efficient LED technology. But they are having to do this with smaller and smaller budgets. That's why the new generation of LumiStreet has been upgraded and designed to provide a solution to this challenge, it is the ideal solution for performing point-to-point replacement of conventional lighting. LumiStreet gen2 achieves this by offering high efficiency, low Total Cost of Ownership, and ease of installation and maintenance. The ease of installation and maintenance is enabled by the Philips Service tag. Moreover, the Philips SR (System Ready) socket makes it future-ready and you can pair this luminaire with lighting control and software applications such as Interact City.

Benefits

- Economical LED alternative to conventional street lights
- Offers high efficiency and energy savings
- Made of high-quality materials for longer lifetime and minimized maintenance

Features

- Good application coverage thanks to wide range of optics, tunable flux and tiltable spigot
- Easy luminaire identification due to the Philips Service tag
- Future-ready thanks to the SR (System Ready) socket
- High system efficiency with good application coverage
- Luminaire is also equipped with dedicated light recipes that help with: 1) maintaining an optimal ecosystems for bats or 2) preserving a dark night sky and reduce light pollution

LumiStreet gen2

Application

- Roads and streets
- Residential streets

Versions





UniStreet gen2 Medium Solar



UniStreet LumiStreet gen2 Nano with Zhaga sockets



Dimensional drawing



LumiStreet gen2

Product details

UniStreet LumiStreet gen2 Nano
top side view with Zhaga sockets



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2

UniStreet LumiStreet gen2 Nano
profile view



UniStreet gen2 spigot regulation

UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2

UniStreet LumiStreet gen2 Nano
gear compartment



UniStreet_LumiStreet_gen2

UniStreet_LumiStreet_gen2



LumiStreet gen2

Product details



UniStreet_LumiStreet_gen2

UniStreet_LumiStreet_gen2



UniStreet LumiStreet gen2 Nano
spigot view

Bottom view for spigot regulation
and screw



UniStreet LumiStreet gen2 Nano
spigot view

UniStreet LumiStreet gen2 Nano
profile view with Zhaga sockets



UniStreet_LumiStreet_gen2

UniStreet LumiStreet gen2 Nano
top view



LumiStreet gen2

Product details



UniStreet LumiStreet gen2 Nano
bottom view



UniStreet_LumiStreet_gen2



UniStreet LumiStreet gen2 Nano
bottom view with louvre



UniStreet LumiStreet gen2 Nano
gear compartment



UniStreet LumiStreet gen2 Nano
gear compartment

UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



General Information

Driver included	Yes
-----------------	-----

Light Technical

Upward light output ratio	0
---------------------------	---

Mechanical and Housing

Optical cover type	Flat glass
--------------------	------------

Ingress protection code	IP66
-------------------------	------

Standard tilt angle side entry	0°
--------------------------------	----

Standard tilt angle posttop	0°
-----------------------------	----

Approval and Application

CE mark	Yes
---------	-----

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

General Information

Order Code	Full Product Name	Lamp family code	Light source replaceable	Number of gear units	Service tag
910925868721	BGP290 LED50-1F/740 I DM10 48/60S	LED50	Yes	1 unit	Yes
910925868722	BGP390 LED50-1F/740 I DM10 48/60S	LED50	Yes	1 unit	Yes
910925868724	BGP290 LED50-1F/740 II DM10 48/60S	LED50	Yes	1 unit	Yes
910925868725	BGP390 LED50-1F/740 II DM10 48/60S	LED50	Yes	1 unit	Yes
910925869152	BGP290 LED20-1F/730 II DM50 D9 48/60S	LED20	Yes	1 unit	Yes
910925869153	BGP290 LED40-1F/730 II DM50 D9 48/60S	LED40	Yes	1 unit	Yes
910925869154	BGP290 LED50-1F/730 II DM50 D9 48/60S	LED50	Yes	1 unit	Yes
910925869155	BGP290 LED60-1F/730 II DM50 D9 48/60S	LED60	Yes	1 unit	Yes
910925869156	BGP290 LED50-1F/730 II DM12 SRTB 48/60S	LED50	Yes	1 unit	Yes
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	LED49	Yes	1 unit	Yes
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	LED39	Yes	1 unit	Yes
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	LED99	Yes	1 unit	Yes
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	LED14	Yes	1 unit	Yes
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	LED120	Yes	1 unit	Yes
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	LED18	Yes	1 unit	Yes
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	LED22	Yes	1 unit	Yes
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	LED34	Yes	1 unit	Yes
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	LED60	Yes	1 unit	Yes
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	LED80	Yes	1 unit	Yes
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	LED100	Yes	1 unit	Yes
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	LED120	Yes	1 unit	Yes
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	LED120	Yes	1 unit	Yes
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	LED85	Yes	1 unit	Yes
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	LED85	Yes	1 unit	Yes
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	LED120	Yes	1 unit	Yes
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	LED75	Yes	1 unit	Yes
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	LED49	Yes	1 unit	Yes
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	LED27	Yes	1 unit	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Number of gear units	Service tag
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	LED99	Yes	1 unit	Yes
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	LED34	Yes	1 unit	Yes
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	LED22	Yes	1 unit	Yes
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	LED75	Yes	1 unit	Yes
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	LED18	Yes	1 unit	Yes
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	LED27	Yes	1 unit	Yes
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	LED85	Yes	1 unit	Yes
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	LED49	Yes	1 unit	Yes
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05ZIZI-	LED74	Yes	1 unit	Yes
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	LED34	Yes	1 unit	Yes
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	LED94	Yes	1 unit	Yes
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	LED22	Yes	1 unit	Yes
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	LED109	Yes	1 unit	Yes
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05ZIZI	LED120	Yes	1 unit	Yes
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	LED22	Yes	1 unit	Yes
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	LED51	Yes	1 unit	Yes
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	LED39	Yes	1 unit	Yes
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	LED99	Yes	1 unit	Yes
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	LED75	Yes	1 unit	Yes
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	LED39	Yes	1 unit	Yes
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	LED51	Yes	1 unit	Yes
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	LED18	Yes	1 unit	Yes
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	LED39	Yes	1 unit	Yes
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	LED75	Yes	1 unit	Yes
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	LED65	Yes	1 unit	Yes
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	LED119	Yes	1 unit	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Number of gear units	Service tag
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	LED39	Yes	1 unit	Yes
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	LED74	Yes	1 unit	Yes
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	LED94	Yes	1 unit	Yes
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZI-	LED54	Yes	1 unit	Yes
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZI-	LED64	Yes	1 unit	Yes
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZI-	LED45	Yes	1 unit	Yes
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	LED49	Yes	1 unit	Yes
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	LED39	Yes	1 unit	Yes
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	LED49	Yes	1 unit	Yes
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZI-	LED45	Yes	1 unit	Yes
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZI-	LED35	Yes	1 unit	Yes
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	LED49	Yes	1 unit	Yes
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZI-	LED35	Yes	1 unit	Yes
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	LED70	Yes	1 unit	Yes
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	LED80	Yes	1 unit	Yes
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	LED70	Yes	1 unit	Yes
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	LED120	Yes	1 unit	Yes
910925868082	BGP292 LED35-4S/740 II DM11 CLO- DDF1 D18	LED35	Yes	1 unit	Yes
910925868083	BGP292 LED35-4S/830 II DM11 CLO- DDF1 D18	LED35	Yes	1 unit	Yes
910925868084	BGP292 LED45-4S/740 II DM11 CLO- DDF1 D18	LED45	Yes	1 unit	Yes
910925868085	BGP292 LED45-4S/830 II DM11 CLO- DDF1 D18	LED45	Yes	1 unit	Yes
910925868086	BGP292 LED54-4S/740 II DM11 CLO- DDF1 D18	LED54	Yes	1 unit	Yes
910925868087	BGP292 LED64-4S/740 II DM11 CLO- DDF1 D18	LED64	Yes	1 unit	Yes
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	LED100	Yes	1 unit	Yes
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	LED100	Yes	1 unit	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Number of gear units	Service tag
910925868938	BGP292 LED149-4S/730 II DM32 GR-10714 MS	LED149	Yes	1 unit	Yes
910925869852	BGP292 LED120-1P/740 UE II DM24P D9 48/6	LED240	-	1 unit	Yes
910925870249	BGP392 LED120-1P/740 II DM65P FS 32/76P	LED120	-	1 unit	-
910925870251	BGP392 LED113-1P/730 II DM65P FS 32/76P	LED113	-	1 unit	-
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	LED149	Yes	1 unit	Yes
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	LED120	Yes	1 unit	Yes
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	LED240	Yes	1 unit	Yes
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	LED240	Yes	1 unit	Yes
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	LED100	Yes	1 unit	Yes
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	LED139	Yes	1 unit	Yes
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	LED180	Yes	1 unit	Yes
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	LED240	Yes	1 unit	Yes
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	LED170	Yes	1 unit	Yes
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	LED240	Yes	1 unit	Yes
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	LED149	Yes	1 unit	Yes
910925866755	BGP293 LED149-4S/740 I DX10 76S	LED149	Yes	1 unit	Yes
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	LED139	Yes	1 unit	Yes
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	LED139	Yes	1 unit	Yes
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	LED149	Yes	1 unit	Yes
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	LED149	Yes	1 unit	Yes
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	LED149	Yes	1 unit	Yes
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	LED84	Yes	1 unit	Yes
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	LED139	Yes	1 unit	Yes
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	LED84	Yes	1 unit	Yes
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	LED149	Yes	1 unit	Yes
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	LED109	Yes	1 unit	Yes
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	LED64	Yes	1 unit	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Number of gear units	Service tag
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05ZIZ1-	LED80	Yes	1 unit	Yes
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05ZIZ1	LED100	Yes	1 unit	Yes
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05ZIZ1	LED120	Yes	1 unit	Yes
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05ZIZ1	LED149	Yes	1 unit	Yes
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	LED80	Yes	1 unit	Yes
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	LED80	Yes	1 unit	Yes
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	LED100	Yes	1 unit	Yes
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	LED120	Yes	1 unit	Yes
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	LED84	Yes	1 unit	Yes
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	LED80	Yes	1 unit	Yes
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	LED100	Yes	1 unit	Yes
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	LED120	Yes	1 unit	Yes
910925868939	BGP293 LED220-4S/730 II DM32 GR-10714 MS	LED220	Yes	1 unit	Yes
910925869853	BGP293 LED240-1P/740 UE II DM24P D9 48/6	LED240	-	1 unit	Yes
910925868727	BGP290 LED50-1F/740 I DM10 SRG10 SRT SRB	LED50	Yes	1 unit	Yes
910925868728	BGP390 LED50-1F/740 I DM10 SRG10 SRT SRB	LED50	Yes	1 unit	Yes
910925869157	BGP290 LED50-1F/730 II DM32 MSP SRTB48/6	LED50	Yes	1 unit	Yes
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	LED340	Yes	2 units	Yes
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	LED180	Yes	2 units	Yes
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	LED240	Yes	2 units	Yes
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	LED240	Yes	2 units	Yes
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	LED340	Yes	2 units	Yes
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	LED240	Yes	2 units	Yes
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	LED140	Yes	2 units	Yes
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	LED240	Yes	2 units	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Number of gear units	Service tag
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05ZIZ1	LED400	Yes	2 units	Yes
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	LED140	Yes	2 units	Yes
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	LED240	Yes	2 units	Yes
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	LED150	Yes	2 units	Yes
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	LED340	Yes	2 units	Yes
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05ZIZ1	LED300	Yes	2 units	Yes
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05ZIZ1	LED150	Yes	2 units	Yes
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05ZIZ1	LED300	Yes	2 units	Yes
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05ZIZ1	LED400	Yes	2 units	Yes
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	LED150	Yes	2 units	Yes
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	LED300	Yes	2 units	Yes
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	LED400	Yes	2 units	Yes
910925868940	BGP294 LED380-4S/730 II DM32 GR-10714 MS	LED380	Yes	2 units	Yes
910925869854	BGP294 LED340-1P/740 UE II DM24P D9 48/6	LED240	-	1 unit	Yes
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	LED39	Yes	1 unit	Yes
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	LED50	Yes	1 unit	Yes
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	LED50	Yes	1 unit	Yes
910925866610	BGP291 LED8-4S/740 II DM50 D9 48/60S	LED8	Yes	1 unit	Yes
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	LED20	Yes	1 unit	Yes
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	LED40	Yes	1 unit	Yes
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	LED50	Yes	1 unit	Yes
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	LED64	Yes	1 unit	Yes
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	LED45	Yes	1 unit	Yes
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	LED64	Yes	1 unit	Yes
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	LED44	Yes	1 unit	Yes
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	LED34	Yes	1 unit	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Number of gear units	Service tag
910925866857	BGP291 LED34-4S/740 II DM11 CLO- DDF1 D18	LED34	Yes	1 unit	Yes
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	LED34	Yes	1 unit	Yes
910925866859	BGP291 LED34-4S/830 II DM11 CLO- DDF1 D18	LED34	Yes	1 unit	Yes
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	LED44	Yes	1 unit	Yes
910925866861	BGP291 LED44-4S/740 II DM11 CLO- DDF1 D18	LED44	Yes	1 unit	Yes
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	LED44	Yes	1 unit	Yes
910925866863	BGP291 LED44-4S/830 II DM11 CLO- DDF1 D18	LED44	Yes	1 unit	Yes
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	LED51	Yes	1 unit	Yes
910925866865	BGP291 LED51-4S/740 II DM11 CLO- DDF1 D18	LED51	Yes	1 unit	Yes
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	LED34	Yes	1 unit	Yes
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05ZIZI-	LED20	Yes	1 unit	Yes
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	LED30	Yes	1 unit	Yes
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05ZIZI-	LED25	Yes	1 unit	Yes
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05ZIZI-	LED35	Yes	1 unit	Yes
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05ZIZI-	LED45	Yes	1 unit	Yes
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	LED22	Yes	1 unit	Yes
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	LED45	Yes	1 unit	Yes
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	LED54	Yes	1 unit	Yes
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05ZIZI-	LED20	Yes	1 unit	Yes
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05ZIZI-	LED25	Yes	1 unit	Yes
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05ZIZI-	LED35	Yes	1 unit	Yes
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05ZIZI-	LED45	Yes	1 unit	Yes
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	LED22	Yes	1 unit	Yes
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	LED34	Yes	1 unit	Yes
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	LED45	Yes	1 unit	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable	Number of gear units	Service tag
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	LED60	Yes	1 unit	Yes
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	LED25	Yes	1 unit	Yes
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	LED35	Yes	1 unit	Yes
910925868074	BGP291 LED20-4S/740 II DM11 CLO- DDF1 D18	LED20	Yes	1 unit	Yes
910925868075	BGP291 LED20-4S/830 II DM11 CLO- DDF1 D18	LED20	Yes	1 unit	Yes
910925868076	BGP291 LED25-4S/740 II DM11 CLO- DDF1 D18	LED25	Yes	1 unit	Yes
910925868077	BGP291 LED25-4S/830 II DM11 CLO- DDF1 D18	LED25	Yes	1 unit	Yes
910925868078	BGP291 LED35-4S/740 II DM11 CLO- DDF1 D18	LED35	Yes	1 unit	Yes
910925868079	BGP291 LED35-4S/830 II DM11 CLO- DDF1 D18	LED35	Yes	1 unit	Yes
91092586808	BGP291 LED45-4S/740 II DM11 CLO- DDF1 D18	LED45	Yes	1 unit	Yes
910925868081	BGP291 LED45-4S/830 II DM11 CLO- DDF1 D18	LED45	Yes	1 unit	Yes
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	LED51	Yes	1 unit	Yes
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	LED51	Yes	1 unit	Yes
910925868932	BGP291 LED49-4S/730 II DM32 MSP SRG10 HO	LED49	Yes	1 unit	Yes
910925868937	BGP291 LED49-4S/730 II DM32 GR-10714 MSP	LED49	Yes	1 unit	Yes
910925869851	BGP291 LED50-1P/740 UE II DM24P D9 48/60	LED240	-	1 unit	Yes
910925870248	BGP391 LED82-1P/740 II DM65P FS 32/76P	LED82	-	1 unit	-
910925870250	BGP391 LED78-1P/730 II DM65P FS 32/76P	LED79	-	1 unit	-

Light Technical (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925868721	BGP290	157° - 33° x	740	4000 K	70	910925868724	BGP290	157° - 33° x	740	4000 K	70
	LED50-1F/740 I DM10 48/60S	55°	neutral white				LED50-1F/740 II DM10 48/60S	55°	neutral white		
910925868722	BGP390	157° - 33° x	740	4000 K	70	910925868725	BGP390	157° - 33° x	740	4000 K	70
	LED50-1F/740 I DM10 48/60S	55°	neutral white				LED50-1F/740 II DM10 48/60S	55°	neutral white		

LumiStreet gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	Color
				Color Temperature (Nom)	rendering index (CRI)
910925869152	BGP290 LED20-1F/730 II DM50 D9 48/60S	154° - 31° x 54°	730 warm white	3000 K	70
910925869153	BGP290 LED40-1F/730 II DM50 D9 48/60S	154° - 31° x 54°	730 warm white	3000 K	70
910925869154	BGP290 LED50-1F/730 II DM50 D9 48/60S	154° - 31° x 54°	730 warm white	3000 K	70
910925869155	BGP290 LED60-1F/730 II DM50 D9 48/60S	154° - 31° x 54°	730 warm white	3000 K	70
910925869156	BGP290 LED50-1F/730 II DM12 SRTB 48/60S	53° x 71°	730 warm white	3000 K	70
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	150° - 43° x 67°	740 neutral white	4000 K	70
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	4000 K	70
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	150° - 43° x 67°	740 neutral white	4000 K	70
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	4000 K	70
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	Color
				Color Temperature (Nom)	rendering index (CRI)
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	150° - 43° x 67°	740 neutral white	4000 K	70
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	150° - 43° x 67°	740 neutral white	4000 K	70
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	4000 K	70
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	150° - 43° x 67°	740 neutral white	4000 K	70
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	4000 K	70
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	4000 K	70
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	150° - 43° x 67°	740 neutral white	4000 K	70
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	4000 K	70
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	4000 K	70
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	157° - 33° x 55°	740 neutral white	4000 K	70
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05ZIZ1-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	4000 K	70
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	160° - 42° x 54°	740 neutral white	4000 K	70
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	4000 K	70
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	157° - 33° x 55°	740 neutral white	4000 K	70
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05ZIZ1	160° - 42° x 54°	740 neutral white	4000 K	70
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	4000 K	70
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	150° - 43° x 67°	740 neutral white	4000 K	70
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	4000 K	70
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	150° - 43° x 67°	740 neutral white	4000 K	70
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	150° - 43° x 67°	740 neutral white	4000 K	70
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	4000 K	70
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	150° - 43° x 67°	740 neutral white	4000 K	70
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	4000 K	70
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	61° x 150°	740 neutral white	4000 K	70
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	150° - 43° x 67°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	157° - 33° x 55°	740 neutral white	4000 K	70
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZ1-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZ1-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZ1-	160° - 42° x 54°	830 warm white	3000 K	80
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTH	149° - 10° x 57°	740 neutral white	4000 K	70
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	157° - 33° x 55°	830 warm white	3000 K	80
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	157° - 33° x 55°	740 neutral white	4000 K	70
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZ1-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZ1-	160° - 42° x 54°	830 warm white	3000 K	80
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	157° - 33° x 55°	830 warm white	3000 K	80
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZ1-	160° - 42° x 54°	740 neutral white	4000 K	70
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	150° - 43° x 67°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	Color
				Color Temperature (Nom)	rendering index (CRI)
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	150° - 43° x 67°	740 neutral white	4000 K	70
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	160° - 42° x 54°	740 neutral white	4000 K	70
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	160° - 42° x 54°	740 neutral white	4000 K	70
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	154° - 31° x 54°	730 warm white	3000 K	70
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	154° - 31° x 54°	730 warm white	3000 K	70
910925868938	BGP292 LED149-4S/730 II DM32 GR-10714 MS	149° - 10° x 57°	730 warm white	3000 K	70
910925869852	BGP292 LED120-1P/74 0 UE II DM24P D9 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925870249	BGP392 LED120-1P/740 II DM65P FS 32/76P	160° - 42° x 54°	740 neutral white	4000 K	70
910925870251	BGP392 LED113-1P/730 II DM65P FS 32/76P	160° - 42° x 54°	730 warm white	3000 K	70
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	53° x 71°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	Color
				Color Temperature (Nom)	rendering index (CRI)
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	150° - 43° x 67°	740 neutral white	4000 K	70
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	160° - 42° x 54°	740 neutral white	4000 K	70
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866755	BGP293 LED149-4S/740 I DX10 76S	150° - 43° x 67°	740 neutral white	4000 K	70
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	61° x 150°	740 neutral white	4000 K	70
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	150° - 43° x 67°	740 neutral white	4000 K	70
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	150° - 43° x 67°	740 neutral white	4000 K	70
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	61° x 150°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	Color
				Color Temperature (Nom)	rendering index (CRI)
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	157° - 33° x 55°	740 neutral white	4000 K	70
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	-	830 warm white	3000 K	80
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05ZIZI	160° - 42° x 54°	740 neutral white	4000 K	70
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05ZIZI	160° - 42° x 54°	740 neutral white	4000 K	70
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05ZIZI	160° - 42° x 54°	740 neutral white	4000 K	70
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	-	740 neutral white	4000 K	70
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	-	830 warm white	3000 K	80
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	160° - 42° x 54°	740 neutral white	4000 K	70
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	149° - 10° x 57°	740 neutral white	4000 K	70
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	149° - 10° x 57°	740 neutral white	4000 K	70
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	Color
				Color Temperature (Nom)	rendering index (CRI)
91092586809	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868939	BGP293 LED220-4S/730 II DM32 GR-10714 MS	149° - 10° x 57°	730 warm white	3000 K	70
910925869853	BGP293 LED240-1P/740 40 UE II DM24P D9 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925868727	BGP290 LED50-1F/740 I DM10 SRG10 SRT SRB	157° - 33° x 55°	740 neutral white	4000 K	70
910925868728	BGP390 LED50-1F/740 I DM10 SRG10 SRT SRB	157° - 33° x 55°	740 neutral white	4000 K	70
910925869157	BGP290 LED50-1F/730 II DM32 MSP SRTB48/6	149° - 10° x 57°	730 warm white	3000 K	70
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	160° - 42° x 54°	740 neutral white	4000 K	70
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	154° - 31° x 54°	740 neutral white	4000 K	70
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	154° - 31° x 54°	740 neutral white	4000 K	70
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	160° - 42° x 54°	740 neutral white	4000 K	70
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	4000 K	70
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	160° - 42° x 54°	740 neutral white	4000 K	70
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	-	830 warm white	3000 K	80
91092586690	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	-	830 warm white	3000 K	80
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	-	740 neutral white	4000 K	70
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	-	740 neutral white	4000 K	70
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	149° - 10° x 57°	740 neutral white	4000 K	70
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	160° - 42° x 54°	740 neutral white	4000 K	70
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	4000 K	70
910925868940	BGP294 LED380-4S/730 II DM32 GR-10714 MS	149° - 10° x 57°	730 warm white	3000 K	70
910925869854	BGP294 LED340-1P/7 40 UE II DM24P D9 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	160° - 42° x 54°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	4000 K	70
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	152° - 24° x 66°	740 neutral white	4000 K	70
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	3000 K	80
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	3000 K	80
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	4000 K	70
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	157° - 33° x 55°	740 neutral white	4000 K	70
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	149° - 10° x 57°	740 neutral white	4000 K	70
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	3000 K	80
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	157° - 33° x 55°	830 warm white	3000 K	80
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	160° - 42° x 54°	740 neutral white	4000 K	70
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	3000 K	80
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	4000 K	70
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	3000 K	80
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	3000 K	80
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	149° - 10° x 57°	740 neutral white	4000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	157° - 33° x 55°	830 warm white	3000 K	80
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	150° - 43° x 67°	740 neutral white	4000 K	70
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	150° - 43° x 67°	740 neutral white	4000 K	70
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	160° - 42° x 54°	740 neutral white	4000 K	70
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	160° - 42° x 54°	740 neutral white	4000 K	70
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
91092586808	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
0	LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	4000 K	70
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	3000 K	80
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	154° - 31° x 54°	730 warm white	3000 K	70
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	154° - 31° x 54°	730 warm white	3000 K	70
910925868932	BGP291 LED49-4S/730 II DM32 MSP SRG10 H0	149° - 10° x 57°	730 warm white	3000 K	70

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	Color
				Color Temperature (Nom)	rendering index (CRI)
910925868937	BGP291	149° - 10° x	730	3000 K	70
	LED49-4S/730 II	57°	warm		
	DM32 GR-10714 MSP		white		
910925869851	BGP291 LED50-1P/74	160° - 42° x	740	4000 K	70
	0	54°	neutral		
	UE II DM24P D9 48/60		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Correlated	Color
				Color Temperature (Nom)	rendering index (CRI)
910925870248	BGP391 LED82-1P/740	160° - 42° x	740	4000 K	70
	II DM65P FS 32/76P	54°	neutral		
			white		
910925870250	BGP391 LED78-1P/730	160° - 42° x	730	3000 K	70
	II DM65P FS 32/76P	54°	warm		
			white		

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925868721	BGP290 LED50-1F/740 I DM10 48/60S	4,100 lm	Distribution medium 10
910925868722	BGP390 LED50-1F/740 I DM10 48/60S	4,100 lm	Distribution medium 10
910925868724	BGP290 LED50-1F/740 II DM10 48/60S	4,100 lm	Distribution medium 10
910925868725	BGP390 LED50-1F/740 II DM10 48/60S	4,100 lm	Distribution medium 10
910925869152	BGP290 LED20-1F/730 II DM50 D9 48/60S	1,700 lm	Distribution medium 50
910925869153	BGP290 LED40-1F/730 II DM50 D9 48/60S	3,320 lm	Distribution medium 50
910925869154	BGP290 LED50-1F/730 II DM50 D9 48/60S	4,000 lm	Distribution medium 50
910925869155	BGP290 LED60-1F/730 II DM50 D9 48/60S	4,620 lm	Distribution medium 50
910925869156	BGP290 LED50-1F/730 II DM12 SRTB 48/60S	4,000 lm	Distribution medium 12
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	4,263 lm	Distribution extra wide 10
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	3,306 lm	Distribution narrow 10
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	8,600 lm	Distribution extra wide 10
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	1,232 lm	Distribution medium 12
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	10,200 lm	Distribution medium 11
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	1,584 lm	Distribution medium 50
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	1,936 lm	Distribution medium 50
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	2,992 lm	Distribution medium 50
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	5,220 lm	Distribution medium 50
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	6,960 lm	Distribution medium 50

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	8,600 lm	Distribution medium 50
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	10,200 lm	Distribution medium 50
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	10,200 lm	Distribution medium 11
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	7,482 lm	Distribution medium 11
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	7,482 lm	Distribution medium 11
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	10,200 lm	Distribution medium 11
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	6,612 lm	Distribution extra wide 10
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	4,263 lm	Distribution extra wide 10
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	2,288 lm	Distribution narrow 10
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	8,600 lm	Distribution extra wide 10
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	2,904 lm	Distribution narrow 10
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	1,848 lm	Distribution medium 12
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	6,612 lm	Distribution extra wide 10
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	1,540 lm	Distribution medium 12
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	2,288 lm	Distribution narrow 10
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	7,482 lm	Distribution medium 10
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	4,263 lm	Distribution medium 50
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	6,264 lm	Distribution medium 11
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	2,904 lm	Distribution narrow 10

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	7,740 lm	Distribution medium 11
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	1,848 lm	Distribution narrow 10
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	9,460 lm	Distribution medium 10
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05ZIZ1	9,890 lm	Distribution medium 11
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	1,848 lm	Distribution medium 12
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	4,524 lm	Distribution extra wide 10
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	3,306 lm	Distribution medium 12
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	8,600 lm	Distribution extra wide 10
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	6,612 lm	Distribution extra wide 10
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	3,306 lm	Distribution narrow 10
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	4,524 lm	Distribution extra wide 10
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	1,540 lm	Distribution narrow 10
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	3,306 lm	Distribution wide 10
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	6,612 lm	Distribution extra wide 10
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	5,742 lm	Distribution medium 50
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	9,890 lm	Distribution medium 11
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	3,306 lm	Distribution medium 10
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	6,264 lm	Distribution medium 11
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	7,740 lm	Distribution medium 11
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZ1-	4,524 lm	Distribution medium 11
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZ1-	5,394 lm	Distribution medium 11
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZ1-	3,741 lm	Distribution medium 11
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	4,176 lm	Distribution medium 32
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	3,306 lm	Distribution medium 10
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	4,176 lm	Distribution medium 10

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZ1-	3,828 lm	Distribution medium 11
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZ1-	2,958 lm	Distribution medium 11
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	4,089 lm	Distribution medium 10
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZ1-	2,992 lm	Distribution medium 11
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	6,090 lm	Distribution extra wide 10
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	6,960 lm	Distribution extra wide 10
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	6,090 lm	Distribution medium 11
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	10,200 lm	Distribution medium 11
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	2,992 lm	Distribution medium 11
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	2,958 lm	Distribution medium 11
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	3,828 lm	Distribution medium 11
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	3,741 lm	Distribution medium 11
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	4,524 lm	Distribution medium 11
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	5,394 lm	Distribution medium 11
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	8,600 lm	Distribution medium 50
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	8,600 lm	Distribution medium 50
910925868938	BGP292 LED149-4S/730 II DM32 GR-10714 MS	12,180 lm	Distribution medium 32
910925869852	BGP292 LED120-1P/740 UE II DM24P D9 48/6	10,320 lm	Distribution medium 32
910925870249	BGP392 LED120-1P/740 II DM65P FS 32/76P	10,560 lm	Distribution medium version 65 Performance (for 5050)
910925870251	BGP392 LED113-1P/730 II DM65P FS 32/76P	9,280 lm	Distribution medium version 65 Performance (for 5050)
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	12,900 lm	Distribution medium 12
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	10,440 lm	Distribution extra wide 10
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	20,160 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	20,160 lm	Distribution medium 11
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	8,800 lm	Distribution medium 50
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	12,180 lm	Distribution medium 50
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	15,300 lm	Distribution medium 50
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	20,160 lm	Distribution medium 50
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	14,620 lm	Distribution medium 11
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	20,160 lm	Distribution medium 11
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	12,900 lm	Distribution medium 50
910925866755	BGP293 LED149-4S/740 I DX10 76S	12,900 lm	Distribution extra wide 10
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	11,745 lm	Distribution wide 10
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	12,180 lm	Distribution extra wide 10
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	12,900 lm	Distribution medium 50
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	12,900 lm	Distribution extra wide 10
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	12,900 lm	Distribution wide 10
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	7,392 lm	Distribution medium 50
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	12,180 lm	Distribution medium 10
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	7,392 lm	Distribution medium 50
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	12,900 lm	Distribution medium 50
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	9,680 lm	Distribution medium 50
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	5,394 lm	Distribution medium 31
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05ZIZI-	6,864 lm	Distribution medium 11
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05ZIZI	8,448 lm	Distribution medium 11
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05ZIZI	10,005 lm	Distribution medium 11
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05ZIZI	12,470 lm	Distribution medium 11
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	6,864 lm	Distribution medium 31

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	6,864 lm	Distribution medium 31
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	8,448 lm	Distribution medium 11
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	10,005 lm	Distribution medium 32
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	7,216 lm	Distribution medium 32
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	6,864 lm	Distribution medium 11
91092586809	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	8,448 lm	Distribution medium 11
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	10,005 lm	Distribution medium 11
910925868939	BGP293 LED220-4S/730 II DM32 GR-10714 MS	18,690 lm	Distribution medium 32
910925869853	BGP293 LED240-1P/740 UE II DM24P D9 48/6	20,400 lm	Distribution medium 32
910925868727	BGP290 LED50-1F/740 I DM10 SRG10 SRT SRB	4,100 lm	Distribution medium 10
910925868728	BGP390 LED50-1F/740 I DM10 SRG10 SRT SRB	4,100 lm	Distribution medium 10
910925869157	BGP290 LED50-1F/730 II DM32 MSP SRTB48/6	4,000 lm	Distribution medium 32
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	29,240 lm	Distribution medium 11
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	15,840 lm	Distribution medium 50
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	20,880 lm	Distribution medium 50
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	21,120 lm	Distribution medium 11
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	29,240 lm	Distribution medium 11
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	20,010 lm	Distribution medium 11
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	11,880 lm	Distribution medium 31
91092586690	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	19,780 lm	Distribution medium 31
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	32,300 lm	Distribution medium 11
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	12,320 lm	Distribution medium 31
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	20,010 lm	Distribution medium 31
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	12,760 lm	Distribution medium 32
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	28,380 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	24,940 lm	Distribution medium 11
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	12,760 lm	Distribution medium 11
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	24,940 lm	Distribution medium 11
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	32,300 lm	Distribution medium 11
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	12,760 lm	Distribution medium 11
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	24,940 lm	Distribution medium 11
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	32,300 lm	Distribution medium 11
910925868940	BGP294 LED380-4S/730 II DM32 GR-10714 MS	31,320 lm	Distribution medium 32
910925868954	BGP294 LED340-1P/740 UE II DM24P D9 48/6	28,560 lm	Distribution medium 32
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	3,432 lm	Distribution medium 50
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	4,350 lm	Distribution medium 11
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	4,350 lm	Distribution medium 11
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	712 lm	Distribution medium 50
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	1,760 lm	Distribution medium 50
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	3,520 lm	Distribution medium 50
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	4,350 lm	Distribution medium 50
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	5,504 lm	Distribution medium 50
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	3,960 lm	Distribution medium 11
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	5,504 lm	Distribution medium 11
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	3,784 lm	Distribution wide 50
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	2,904 lm	Distribution medium 11
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	2,904 lm	Distribution medium 11
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	2,904 lm	Distribution medium 11
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	2,904 lm	Distribution medium 11
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	3,784 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	3,784 lm	Distribution medium 11
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	3,741 lm	Distribution medium 11
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	3,741 lm	Distribution medium 11
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	4,350 lm	Distribution medium 11
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	4,350 lm	Distribution medium 11
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	2,904 lm	Distribution medium 10
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05Z1Z1-	1,716 lm	Distribution medium 11
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	2,552 lm	Distribution medium 32
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05Z1Z1-	2,112 lm	Distribution medium 11
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05Z1Z1-	2,992 lm	Distribution medium 11
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05Z1Z1-	3,872 lm	Distribution medium 11
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	1,848 lm	Distribution medium 10
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	3,872 lm	Distribution medium 11
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	4,524 lm	Distribution medium 11
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05Z1Z1-	1,716 lm	Distribution medium 11
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05Z1Z1-	2,112 lm	Distribution medium 11
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05Z1Z1-	2,992 lm	Distribution medium 11
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05Z1Z1-	3,741 lm	Distribution medium 11
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	1,848 lm	Distribution medium 32
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	2,904 lm	Distribution medium 10
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	3,960 lm	Distribution extra wide 10
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	5,220 lm	Distribution extra wide 10
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	2,200 lm	Distribution medium 32
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	3,080 lm	Distribution medium 11
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	1,716 lm	Distribution medium 11

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	1,716 lm	Distribution medium 11
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	2,112 lm	Distribution medium 11
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	2,112 lm	Distribution medium 11
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	2,992 lm	Distribution medium 11
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	2,992 lm	Distribution medium 11
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	3,872 lm	Distribution medium 11
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	3,741 lm	Distribution medium 11
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	4,524 lm	Distribution medium 50

Order Code	Full Product Name	Luminous Flux	Optic type outdoor
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	4,524 lm	Distribution medium 50
910925868932	BGP291 LED49-4S/730 II DM32 MSP SRG10 H0	4,214 lm	Distribution medium 32
910925868937	BGP291 LED49-4S/730 II DM32 GR-10714 MSP	4,320 lm	Distribution medium 32
910925869851	BGP291 LED50-1P/740 UE II DM24P D9 48/60	4,350 lm	Distribution medium 32
910925870248	BGP391 LED82-1P/740 II DM65P FS 32/76P	6,710 lm	Distribution medium version 65 Performance (for 5050)
910925870250	BGP391 LED78-1P/730 II DM65P FS 32/76P	6,210 lm	Distribution medium version 65 Performance (for 5050)

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925868721	BGP290 LED50-1F/740 I DM10 48/60S	31 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868722	BGP390 LED50-1F/740 I DM10 48/60S	31 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868724	BGP290 LED50-1F/740 II DM10 48/60S	31 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868725	BGP390 LED50-1F/740 II DM10 48/60S	31 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869152	BGP290 LED20-1F/730 II DM50 D9 48/60S	13 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869153	BGP290 LED40-1F/730 II DM50 D9 48/60S	25.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869154	BGP290 LED50-1F/730 II DM50 D9 48/60S	32.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925869155	BGP290 LED60-1F/730 II DM50 D9 48/60S	40 W	Luminaire surge protection level until 6

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925869156	BGP290 LED50-1F/730 II DM12 SRTB 48/60S	33 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	29 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	23 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	60 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	8.9 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	70 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	11.2 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

LumiStreet gen2

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	13.6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	20 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	36.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	47 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	70 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	70 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	50 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	50 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	70 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	44 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	29 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	16 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	60 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	19.8 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	13.6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	44 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	11.2 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	16 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	50 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	29 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	42.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	19.8 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	56 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	13.6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

LumiStreet gen2

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	63 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	70 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	13.6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	30.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	23 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	60 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	44 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	23 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	30.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	11.2 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	23 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	44 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	37.5 W	Luminaire surge protection level until 6

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	70 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	23 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	43 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	57 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05Z1Z1-	32 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05Z1Z1-	36.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05Z1Z1-	32 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	29.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	27.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	29.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05Z1Z1-	26.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05Z1Z1-	24.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

LumiStreet gen2

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	35 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05Z1Z1-	20.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	40.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	47 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	40.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	70 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	20.5 W	Standard surge protection level
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	24.5 W	Standard surge protection level
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	26.5 W	Standard surge protection level
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	32 W	Standard surge protection level
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	32 W	Standard surge protection level
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	36.5 W	Standard surge protection level
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868938	BGP292 LED149-4S/730 II DM32 GR-10714 MS	93 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925869852	BGP292 LED120-1P/740 UE II DM24P D9 48/6	60 W	Luminaire surge protection level until 6

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925870249	BGP392 LED120-1P/740 II DM65P FS 32/76P	61 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870251	BGP392 LED113-1P/730 II DM65P FS 32/76P	56 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	84 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	67 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	138 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	138 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	55 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	78 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	104 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	138 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	98 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	138 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

LumiStreet gen2

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	84 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866755	BGP293 LED149-4S/740 I DX10 76S	84 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	78 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	78 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	84 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	84 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	84 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	48.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	78 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	46 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	84 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	60 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	43 W	Luminaire surge protection level until 6

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05Z1Z1-	44 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05Z1Z1	55 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05Z1Z1	67 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05Z1Z1	84 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	44.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	53 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	56 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	67 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	47 W	Standard surge protection level
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	44 W	Standard surge protection level
91092586809	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	55 W	Standard surge protection level
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	67 W	Standard surge protection level
910925868939	BGP293 LED220-4S/730 II DM32 GR-10714 MS	132 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925869853	BGP293 LED240-1P/740 UE II DM24P D9 48/6	118 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925868727	BGP290 LED50-1F/740 I DM10 SRG10 SRT SRB	31.5 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925868728	BGP390 LED50-1F/740 I DM10 SRG10 SRT SRB	31.5 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925869157	BGP290 LED50-1F/730 II DM32 MSP SRTB48/6	33 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	186 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	99 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	134 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	138 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	186 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	134 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	93 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	162 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	220 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	78 W	Luminaire surge protection level until 6

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	134 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	84 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	188 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	168 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	82 W	Standard surge protection level
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	168 W	Standard surge protection level
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	220 W	Standard surge protection level
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	82 W	Standard surge protection level
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	168 W	Standard surge protection level
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	220 W	Standard surge protection level
910925868940	BGP294 LED380-4S/730 II DM32 GR-10714 MS	225 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925869854	BGP294 LED340-1P/740 UE II DM24P D9 48/6	168 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	23 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	30 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	30 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode

LumiStreet gen2

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	5,6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	13,6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	23,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	30 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	39 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	27 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	39 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	26 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	22 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	22 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	23,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	23,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	26 W	Luminaire surge protection level until 6

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	26 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	31,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	31,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	30,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	30,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	22,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05Z1Z1-	13,6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	19,6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05Z1Z1-	19 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05Z1Z1-	22,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05Z1Z1-	26,5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	16,8 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

LumiStreet gen2

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	26.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	32 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05Z1Z1-	14.8 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05Z1Z1-	15.6 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05Z1Z1-	24.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05Z1Z1-	32 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	14 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	24 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	27 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	36.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	15.8 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	22.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	13.6 W	Standard surge protection level kV differential mode and 8 kV common mode
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	14.8 W	Standard surge protection level
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	15.6 W	Standard surge protection level
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	19 W	Standard surge protection level
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	22.5 W	Standard surge protection level
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	24.5 W	Standard surge protection level
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	26.5 W	Standard surge protection level
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	32 W	Standard surge protection level
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	32.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	32.5 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868932	BGP291 LED49-4S/730 II DM32 MSP SRG10 H0	32.5 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925868937	BGP291 LED49-4S/730 II DM32 GR-10714 MSP	31.5 W	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925869851	BGP291 LED50-1P/740 UE II DM24P D9 48/60	26 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870248	BGP391 LED82-1P/740 II DM65P FS 32/76P	40 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925870250	BGP391 LED78-1P/730 II DM65P FS 32/76P	40 W	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910925868721	BGP290 LED50-1F/740 I DM10 48/60S	Yes	0% (digital)
910925868722	BGP390 LED50-1F/740 I DM10 48/60S	Yes	0% (digital)
910925868724	BGP290 LED50-1F/740 II DM10 48/60S	Yes	0% (digital)
910925868725	BGP390 LED50-1F/740 II DM10 48/60S	Yes	0% (digital)
910925869152	BGP290 LED20-1F/730 II DM50 D9 48/60S	Yes	0% (digital)
910925869153	BGP290 LED40-1F/730 II DM50 D9 48/60S	Yes	0% (digital)
910925869154	BGP290 LED50-1F/730 II DM50 D9 48/60S	Yes	0% (digital)
910925869155	BGP290 LED60-1F/730 II DM50 D9 48/60S	Yes	0% (digital)
910925869156	BGP290 LED50-1F/730 II DM12 SRTB 48/60S	No	0% (digital)
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	Yes	0% (digital)
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Yes	0% (digital)
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	Yes	0% (digital)
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	Yes	0% (digital)
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	No	0% (digital)
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	Yes	0% (digital)
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	Yes	0% (digital)
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	No	0% (digital)
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	No	0% (digital)
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	No	0% (digital)
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	Yes	0% (digital)
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	Yes	0% (digital)
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Yes	0% (digital)
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	Yes	0% (digital)
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Yes	0% (digital)
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Yes	0% (digital)
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	Yes	0% (digital)
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	Yes	0% (digital)
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Yes	0% (digital)
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	Yes	0% (digital)
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	No	0% (digital)
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Yes	0% (digital)
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	Yes	0% (digital)
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	Yes	0% (digital)
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	Yes	0% (digital)
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	No	0% (digital)
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Yes	0% (digital)
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	No	0% (digital)
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	Yes	0% (digital)
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	Yes	0% (digital)
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	No	0% (digital)
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Yes	0% (digital)
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	No	0% (digital)
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	Yes	0% (digital)
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	Yes	0% (digital)
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	No	0% (digital)
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	No	0% (digital)
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	No	0% (digital)
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	No	0% (digital)
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	No	0% (digital)
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	No	0% (digital)
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	No	0% (digital)
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	Yes	0% (digital)
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	Yes	0% (digital)
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	No	0% (digital)
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	No	0% (digital)
910925868082	BGP292 LED35-4S/740 II DM11 CLO- DDF1 D18	Yes	Programmable
910925868083	BGP292 LED35-4S/830 II DM11 CLO- DDF1 D18	Yes	Programmable
910925868084	BGP292 LED45-4S/740 II DM11 CLO- DDF1 D18	Yes	Programmable
910925868085	BGP292 LED45-4S/830 II DM11 CLO- DDF1 D18	Yes	Programmable
910925868086	BGP292 LED54-4S/740 II DM11 CLO- DDF1 D18	Yes	Programmable

Order Code	Full Product Name	Dimmable	Maximum dim level
910925868087	BGP292 LED64-4S/740 II DM11 CLO- DDF1 D18	Yes	Programmable
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	No	Programmable
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	No	Programmable
910925868938	BGP292 LED149-4S/730 II DM32 GR-10714 MS	Yes	0% (digital)
910925869852	BGP292 LED120-1P/740 UE II DM24P D9 48/6	Yes	0% (digital)
910925870249	BGP392 LED120-1P/740 II DM65P FS 32/76P	Yes	0% (digital)
910925870251	BGP392 LED113-1P/730 II DM65P FS 32/76P	Yes	0% (digital)
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	Yes	0% (digital)
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	Yes	0% (digital)
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	No	0% (digital)
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	No	0% (digital)
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	No	0% (digital)
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	Yes	0% (digital)
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866755	BGP293 LED149-4S/740 I DX10 76S	No	0% (digital)
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	No	0% (digital)
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	No	0% (digital)
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	No	0% (digital)
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	No	0% (digital)
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	Yes	0% (digital)
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	No	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	Yes	0% (digital)
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	Yes	0% (digital)
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	No	0% (digital)
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05ZIZI	No	0% (digital)
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05ZIZI	No	0% (digital)
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05ZIZI	No	0% (digital)
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	No	0% (digital)
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	No	0% (digital)
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	No	0% (digital)
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	No	0% (digital)
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	Yes	Not applicable
910925868089	BGP293 LED80-4S/740 II DM11 CLO- DDF1 D18	Yes	Programmable
91092586809	BGP293 LED100-4S/740 II DM11 CLO- DDF1 D1	Yes	Programmable
910925868091	BGP293 LED120-4S/740 II DM11 CLO- DDF1 D1	Yes	Programmable
910925868939	BGP293 LED220-4S/730 II DM32 GR-10714 MS	Yes	0% (digital)
910925868953	BGP293 LED240-1P/740 UE II DM24P D9 48/6	Yes	0% (digital)
910925868727	BGP290 LED50-1F/740 I DM10 SRG10 SRT SRB	No	0% (digital)
910925868728	BGP390 LED50-1F/740 I DM10 SRG10 SRT SRB	No	0% (digital)
910925869157	BGP290 LED50-1F/730 II DM32 MSP SRTB48/6	No	0% (digital)
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	No	0% (digital)
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	Yes	0% (digital)
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	Yes	0% (digital)
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	No	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	Yes	0% (digital)
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	No	0% (digital)
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	No	0% (digital)
910925866909	BGP294 LED240-4S/830 II DM31 MSP 9 CLO SRT	No	0% (digital)
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	No	0% (digital)
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	No	0% (digital)
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	No	0% (digital)
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	No	0% (digital)
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	No	0% (digital)
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05ZIZI	No	0% (digital)
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05ZIZI	No	Programmable
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05ZIZI	No	Programmable
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	No	Programmable
910925868092	BGP294 LED150-4S/740 II DM11 CLO- DDF1 D1	Yes	Programmable
910925868093	BGP294 LED300-4S/740 II DM11 CLO- DDF1 D1	Yes	Programmable
910925868094	BGP294 LED400-4S/740 II DM11 CLO- DDF1 D1	Yes	Programmable
910925868940	BGP294 LED380-4S/730 II DM32 GR-10714 MS	Yes	0% (digital)
910925869854	BGP294 LED340-1P/740 UE II DM24P D9 48/6	Yes	0% (digital)
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	No	0% (digital)
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	No	0% (digital)
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	No	0% (digital)
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	Yes	0% (digital)
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	Yes	0% (digital)
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	Yes	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	No	0% (digital)
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	Yes	0% (digital)
910925866780	BGP291 LED44-4S/740 II DW50 CLO D9 P1 32/	Yes	0% (digital)
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	No	0% (digital)
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	No	0% (digital)
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	No	0% (digital)
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	Yes	0% (digital)
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	No	0% (digital)
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	No	0% (digital)
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	No	0% (digital)
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	No	0% (digital)
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	No	0% (digital)
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05ZIZI-	No	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05ZIZI-	No	0% (digital)
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	No	0% (digital)
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	No	0% (digital)
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	Yes	0% (digital)
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	Yes	0% (digital)
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	No	0% (digital)
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	No	0% (digital)
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Yes	Programmable
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Yes	Programmable
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes	Programmable
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes	Programmable
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes	Programmable
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes	Programmable
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes	Programmable
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes	Programmable
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	No	Programmable
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	No	Programmable
910925868932	BGP291 LED49-4S/730 II DM32 MSP SRG10 H0	No	0% (digital)
910925868937	BGP291 LED49-4S/730 II DM32 GR-10714 MSP	Yes	0% (digital)
910925869851	BGP291 LED50-1P/740 UE II DM24P D9 48/60	Yes	0% (digital)
910925870248	BGP391 LED82-1P/740 II DM65P FS 32/76P	Yes	0% (digital)
910925870250	BGP391 LED78-1P/730 II DM65P FS 32/76P	Yes	0% (digital)

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Mech. impact protection code
910925868721	BGP290 LED50-1F/740 I DM10 48/60S	Gray	IK08
910925868722	BGP390 LED50-1F/740 I DM10 48/60S	Gray	IK08
910925868724	BGP290 LED50-1F/740 II DM10 48/60S	Gray	IK08
910925868725	BGP390 LED50-1F/740 II DM10 48/60S	Gray	IK08
910925869152	BGP290 LED20-1F/730 II DM50 D9 48/60S	Gray	IK08
910925869153	BGP290 LED40-1F/730 II DM50 D9 48/60S	Gray	IK08
910925869154	BGP290 LED50-1F/730 II DM50 D9 48/60S	Gray	IK08
910925869155	BGP290 LED60-1F/730 II DM50 D9 48/60S	Gray	IK08
910925869156	BGP290 LED50-1F/730 II DM12 SRTB 48/60S	Gray	IK08
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	Gray	IK09
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Gray	IK09
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	Gray	IK09
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	Gray	IK09
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	Gray	IK09
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	Gray	IK09
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	Gray	IK09
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	Gray	IK09
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	Gray	IK09
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	Gray	IK09
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	Gray	IK09
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	Gray	IK09
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	Gray	IK09
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Gray	IK09
91092586702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	Gray	IK09
91092586703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Gray	IK09

Order Code	Full Product Name	Housing Color	Mech. impact protection code
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Gray	IK09
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	Gray	IK09
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	Gray	IK09
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Gray	IK09
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	Gray	IK09
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	Gray	IK09
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Gray	IK09
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	Gray	IK09
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	Gray	IK09
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	Gray	IK09
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	Gray	IK09
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Gray	IK09
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	Gray	IK09
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	Gray	IK09
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	Gray	IK09
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	Gray	IK09
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Gray	IK09
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	Gray	IK09
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	Gray	IK09
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	Gray	IK09
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	Gray	IK09
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	Gray	IK09
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	Gray	IK09
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	Gray	IK09
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	Gray	IK09

Order Code	Full Product Name	Housing Color	Mech. impact protection code
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZI-	Gray	IK09
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	Gray	IK09
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	Gray	IK09
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	Gray	IK09
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZI-	Gray	IK09
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	Gray	IK09
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	Gray	IK09
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	Gray	IK09
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	Gray	IK09
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	Gray	IK09
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Gray	IK09
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Gray	IK09
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	Gray	IK09
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	Gray	IK09
910925868938	BGP292 LED149-4S/730 II DM32 GR-10714 MS	Grey	IK09
910925869852	BGP292 LED120-1P/740 UE II DM24P D9 48/6	Grey	IK09
910925870249	BGP392 LED120-1P/740 II DM65P FS 32/76P	Grey	IK09

Order Code	Full Product Name	Housing Color	Mech. impact protection code
910925870251	BGP392 LED113-1P/730 II DM65P FS 32/76P	Grey	IK09
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	Gray	IK09
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	Gray	IK09
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	Gray	IK09
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	Gray	IK09
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	Gray	IK09
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	Gray	IK09
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866755	BGP293 LED149-4S/740 I DX10 76S	Gray	IK09
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	Gray	IK09
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	Gray	IK09
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	Gray	IK09
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	Gray	IK09
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	Gray	IK09
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	Gray	IK09
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	Gray	IK09
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	Gray	IK09
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	Gray	IK09
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05ZIZI	Gray	IK09
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05ZIZI	Gray	IK09
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05ZIZI	Gray	IK09

LumiStreet gen2

Order Code	Full Product Name	Housing Color	Mech. impact protection code
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	Gray	IK09
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	Gray	IK09
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	Gray	IK09
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	Gray	IK09
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	Gray	IK09
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Gray	IK09
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Gray	IK09
910925868939	BGP293 LED220-4S/730 II DM32 GR-10714 MS	Grey	IK09
910925869853	BGP293 LED240-1P/740 UE II DM24P D9 48/6	Grey	IK09
910925868727	BGP290 LED50-1F/740 I DM10 SRG10 SRT SRB	Gray	IK08
910925868728	BGP390 LED50-1F/740 I DM10 SRG10 SRT SRB	Gray	IK08
910925869157	BGP290 LED50-1F/730 II DM32 MSP SRTB48/6	Gray	IK08
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	Gray	IK09
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	Gray	IK09
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	Gray	IK09
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	Gray	IK09
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	Gray	IK09
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	Gray	IK09
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	Gray	IK09
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	Gray	IK09
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05ZIZ1	Gray	IK09
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	Gray	IK09
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	Gray	IK09
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	Gray	IK09

Order Code	Full Product Name	Housing Color	Mech. impact protection code
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	Gray	IK09
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05ZIZ1	Gray	IK09
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05ZIZ1	Gray	IK09
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05ZIZ1	Gray	IK09
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05ZIZ1	Gray	IK09
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Gray	IK09
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Gray	IK09
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Gray	IK09
910925868940	BGP294 LED380-4S/730 II DM32 GR-10714 MS	Grey	IK09
910925869854	BGP294 LED340-1P/740 UE II DM24P D9 48/6	Grey	IK09
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	Gray	IK09
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	Gray	IK09
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	Gray	IK09
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	Gray	IK09
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	Gray	IK09
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	Gray	IK09
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	Gray	IK09
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	Gray	IK09
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	Gray	IK09
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	Gray	IK09
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	Gray	IK09
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	Gray	IK09
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09

Order Code	Full Product Name	Housing Color	Mech. impact protection code
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	Gray	IK09
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	Gray	IK09
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	Gray	IK09
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	Gray	IK09
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	Gray	IK09
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05ZIZI-	Gray	IK09
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	Gray	IK09
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	Gray	IK09
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	Gray	IK09
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05ZIZI-	Gray	IK09
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05ZIZI-	Gray	IK09
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05ZIZI-	Gray	IK09
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05ZIZI-	Gray	IK09
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	Gray	IK09
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	Gray	IK09

Order Code	Full Product Name	Housing Color	Mech. impact protection code
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	Gray	IK09
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	Gray	IK09
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	Gray	IK09
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	Gray	IK09
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Gray	IK09
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Gray	IK09
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Gray	IK09
91092586808	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Gray	IK09
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Gray	IK09
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	Gray	IK09
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	Gray	IK09
910925868932	BGP291 LED49-4S/730 II DM32 MSP SRG10 H0	Grey	IK09
910925868937	BGP291 LED49-4S/730 II DM32 GR-10714 MSP	Grey	IK09
910925869851	BGP291 LED50-1P/740 UE II DM24P D9 48/60	Grey	IK09
910925870248	BGP391 LED82-1P/740 II DM65P FS 32/76P	Grey	IK09
910925870250	BGP391 LED78-1P/730 II DM65P FS 32/76P	Grey	IK09

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910925868721	BGP290 LED50-1F/740 I DM10 48/60S	-
910925868722	BGP390 LED50-1F/740 I DM10 48/60S	-
910925868724	BGP290 LED50-1F/740 II DM10 48/60S	-
910925868725	BGP390 LED50-1F/740 II DM10 48/60S	-
910925869152	BGP290 LED20-1F/730 II DM50 D9 48/60S	-
910925869153	BGP290 LED40-1F/730 II DM50 D9 48/60S	-
910925869154	BGP290 LED50-1F/730 II DM50 D9 48/60S	-
910925869155	BGP290 LED60-1F/730 II DM50 D9 48/60S	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925869156	BGP290 LED50-1F/730 II DM12 SRTB 48/60S	-
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	0.5 %
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	0.5 %
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	0.5 %
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	0.5 %
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	0.5 %
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	0.5 %
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	0.5 %
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	0.5 %
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	0.5 %
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	0.5 %
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	0.5 %
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	0.5 %
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	0.5 %
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	0.5 %
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	0.5 %
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	0.5 %
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	0.5 %
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	0.5 %
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	0.5 %
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	0.5 %
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	0.5 %
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	0.5 %
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	0.5 %
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	0.5 %
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	0.5 %
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	0.5 %
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	0.5 %
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	0.5 %
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	0.5 %
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	0.5 %
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	0.5 %
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	0.5 %
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	0.5 %
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	0.5 %
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	0.5 %
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	0.5 %
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	0.5 %
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	0.5 %
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	0.5 %
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	0.5 %
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	0.5 %
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	0.5 %
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	0.5 %
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	-
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	-
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	-
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	-
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	-
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	-
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	-
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05Z1Z1-	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	0.5 %
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	0.5 %
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	0.5 %
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	0.5 %
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	-
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	-
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	-
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	-
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	-
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	-
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	-
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	-
910925868938	BGP292 LED149-4S/730 II DM32 GR-10714 MS	-
910925869852	BGP292 LED120-1P/740 UE II DM24P D9 48/6	-
910925870249	BGP392 LED120-1P/740 II DM65P FS 32/76P	-
910925870251	BGP392 LED113-1P/730 II DM65P FS 32/76P	-
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	0.5 %
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	0.5 %
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	0.5 %
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	0.5 %
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	0.5 %
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	0.5 %
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	0.5 %
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	0.5 %
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	0.5 %
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	0.5 %
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	0.5 %
910925866755	BGP293 LED149-4S/740 I DX10 76S	0.5 %
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	0.5 %
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	0.5 %
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	0.5 %
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	0.5 %
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	0.5 %
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	-
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	0.5 %
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	0.5 %
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	0.5 %
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	0.5 %
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	-
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05Z1Z1	0.5 %
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05Z1Z1	0.5 %
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05Z1Z1	0.5 %
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	-
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	-
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	0.5 %
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	-
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	-
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	-
91092586809	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	-
0		

Order Code	Full Product Name	Driver failure rate at 5000 h
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	-
910925868939	BGP293 LED220-4S/730 II DM32 GR-10714 MS	-
910925868953	BGP293 LED240-1P/740 UE II DM24P D9 48/6	-
910925868727	BGP290 LED50-1F/740 I DM10 SRG10 SRT SRB	-
910925868728	BGP390 LED50-1F/740 I DM10 SRG10 SRT SRB	-
910925869157	BGP290 LED50-1F/730 II DM32 MSP SRTB48/6	-
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	0.5 %
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	-
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	-
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	-
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	-
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	-
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	-
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	-
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	-
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	-
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	-
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	-
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	-
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	-
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	-
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	-
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	-
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	-
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	-
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	-
910925868940	BGP294 LED380-4S/730 II DM32 GR-10714 MS	-
910925868954	BGP294 LED340-1P/740 UE II DM24P D9 48/6	-
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	0.5 %
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	0.5 %
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	0.5 %
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	0.5 %
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	0.5 %
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	0.5 %
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	0.5 %
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	0.5 %
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	0.5 %
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	0.5 %
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	0.5 %
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	0.5 %
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	0.5 %
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	0.5 %
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	0.5 %
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	0.5 %
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	0.5 %
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	-
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	-
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	-
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	0.5 %
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	0.5 %
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	-
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	-
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	0.5 %
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	0.5 %
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	0.5 %
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	0.5 %
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	-
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	-
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	-
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	-
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	-
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	-
910925868088	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	-
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	-
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	-
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	-
910925868932	BGP291 LED49-4S/730 II DM32 MSP SRG10 HO	-
910925868937	BGP291 LED49-4S/730 II DM32 GR-10714 MSP	-
910925869851	BGP291 LED50-1P/740 UE II DM24P D9 48/60	-
910925870248	BGP391 LED82-1P/740 II DM65P FS 32/76P	-
910925870250	BGP391 LED78-1P/730 II DM65P FS 32/76P	-

Product Data

Order Code	Full Product Name	Product family code
910925868721	BGP290 LED50-1F/740 I DM10 48/60S	BGP290
910925868722	BGP390 LED50-1F/740 I DM10 48/60S	BGP390
910925868724	BGP290 LED50-1F/740 II DM10 48/60S	BGP290
910925868725	BGP390 LED50-1F/740 II DM10 48/60S	BGP390




Order Code	Full Product Name	Product family code
910925869152	BGP290 LED20-1F/730 II DM50 D9 48/60S	BGP290
910925869153	BGP290 LED40-1F/730 II DM50 D9 48/60S	BGP290
910925869154	BGP290 LED50-1F/730 II DM50 D9 48/60S	BGP290
910925869155	BGP290 LED60-1F/730 II DM50 D9 48/60S	BGP290

Order Code	Full Product Name	Product family code
910925869156	BGP290 LED50-1F/730 II DM12 SRTB 48/60S	BGP290
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	BGP292
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	BGP292
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	BGP292
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	BGP292
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	BGP292
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	BGP292
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	BGP292
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	BGP292
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	BGP292
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	BGP292
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	BGP292
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	BGP292
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	BGP292
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	BGP292
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	BGP292
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	BGP392
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	BGP292
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	BGP292
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	BGP292
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	BGP292
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	BGP292
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	BGP292
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	BGP292
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	BGP292
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	BGP292
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	BGP292
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	BGP292
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	BGP292
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	BGP292
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	BGP292
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	BGP292
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	BGP292
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	BGP292
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	BGP292
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	BGP292
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	BGP292
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	BGP292
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	BGP292
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	BGP292
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	BGP292
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	BGP292
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	BGP292
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	BGP292
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	BGP292
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	BGP292
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	BGP292
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	BGP292
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	BGP292
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05Z1Z1-	BGP292
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05Z1Z1-	BGP292
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05Z1Z1-	BGP292

Order Code	Full Product Name	Product family code
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	BGP292
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	BGP292
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	BGP292
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05Z1Z1-	BGP292
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05Z1Z1-	BGP292
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	BGP292
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05Z1Z1-	BGP292
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	BGP292
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	BGP292
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	BGP292
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	BGP292
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	BGP292
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	BGP292
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	BGP292
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	BGP292
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	BGP292
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	BGP292
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	BGP292
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	BGP292
910925868938	BGP292 LED149-4S/730 II DM32 GR-10714 MS	BGP292
910925869852	BGP292 LED120-1P/740 UE II DM24P D9 48/6	BGP292
910925870249	BGP392 LED120-1P/740 II DM65P FS 32/76P	BGP392
910925870251	BGP392 LED113-1P/730 II DM65P FS 32/76P	BGP392
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	BGP293
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	BGP293
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	BGP293
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	BGP293
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	BGP293
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	BGP293
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	BGP293
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	BGP293
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	BGP293
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	BGP393
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	BGP293
910925866755	BGP293 LED149-4S/740 I DX10 76S	BGP293
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	BGP293
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	BGP293
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	BGP293
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	BGP293
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	BGP293
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	BGP293
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	BGP293
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	BGP293
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	BGP293
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	BGP293
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	BGP293
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05Z1Z1-	BGP293
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05Z1Z1	BGP293
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05Z1Z1	BGP293
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05Z1Z1	BGP293
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	BGP293
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	BGP293

Order Code	Full Product Name	Product family code	Order Code	Full Product Name	Product family code
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	BGP293	910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	BGP291
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	BGP293	910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	BGP291
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	BGP293	910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	BGP291
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	BGP293	910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	BGP291
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	BGP293	910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	BGP291
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	BGP293	910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	BGP291
910925868939	BGP293 LED220-4S/730 II DM32 GR-10714 MS	BGP293	910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	BGP291
910925868953	BGP293 LED240-1P/740 UE II DM24P D9 48/6	BGP293	910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	BGP291
910925868727	BGP290 LED50-1F/740 I DM10 SRG10 SRT SRB	BGP290	910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	BGP291
910925868728	BGP390 LED50-1F/740 I DM10 SRG10 SRT SRB	BGP390	910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	BGP291
910925869157	BGP290 LED50-1F/730 II DM32 MSP SRTB48/6	BGP290	910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	BGP291
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	BGP294	910925866898	BGP291 LED20-4S/740 II DM11 CLO S05ZIZI-	BGP291
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	BGP294	910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	BGP291
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	BGP294	910925866910	BGP291 LED25-4S/830 II DM11 CLO S05ZIZI-	BGP291
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	BGP294	910925866911	BGP291 LED35-4S/740 II DM11 CLO S05ZIZI-	BGP291
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	BGP394	910925866913	BGP291 LED45-4S/740 II DM11 CLO S05ZIZI-	BGP291
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	BGP294	910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	BGP291
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	BGP294	910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	BGP291
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	BGP294	910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	BGP291
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	BGP294	910925866928	BGP291 LED20-4S/830 II DM11 CLO S05ZIZI-	BGP291
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	BGP294	910925866929	BGP291 LED25-4S/740 II DM11 CLO S05ZIZI-	BGP291
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	BGP294	910925866932	BGP291 LED35-4S/830 II DM11 CLO S05ZIZI-	BGP291
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	BGP294	910925866933	BGP291 LED45-4S/830 II DM11 CLO S05ZIZI-	BGP291
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	BGP294	910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	BGP291
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05ZIZI	BGP294	910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	BGP291
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05ZIZI	BGP294	910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	BGP291
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05ZIZI	BGP294	910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	BGP291
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	BGP294	910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	BGP291
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	BGP294	910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	BGP291
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	BGP294	910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	BGP291
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	BGP294	910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	BGP291
910925868940	BGP294 LED380-4S/730 II DM32 GR-10714 MS	BGP294	910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	BGP291
910925868954	BGP294 LED340-1P/740 UE II DM24P D9 48/6	BGP294	910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	BGP291
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	BGP291	910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	BGP291
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	BGP291	910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	BGP291
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	BGP291	910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	BGP291
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	BGP291	910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	BGP291
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	BGP291	910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	BGP291
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	BGP291	910925868106	BGP291 LED51-4S/730 II DM50 48/60S	BGP291
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	BGP291	910925868932	BGP291 LED49-4S/730 II DM32 MSP SRG10 H0	BGP291
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	BGP291	910925868937	BGP291 LED49-4S/730 II DM32 GR-10714 MSP	BGP291
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	BGP291	910925869851	BGP291 LED50-1P/740 UE II DM24P D9 48/60	BGP291
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	BGP391	910925870248	BGP391 LED82-1P/740 II DM65P FS 32/76P	BGP391
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	BGP291	910925870250	BGP391 LED78-1P/730 II DM65P FS 32/76P	BGP391




Polar Wide Diagrams



Polar Normal (separate) - BGP2821 - 910925865683

Polar Normal (separate) - BGP2811 - 910925865679




Polar Normal (separate) - BGP2831 - 910925866444



Polar Normal (separate) - BGP2821 - 910925866628

Polar Normal (separate) - BGP2821 - 910925866607

Polar Normal (separate) - BGP2821 - 910925866697




Polar Normal (separate) - BGP2821 - 910925866716


Polar Normal (separate) - BGP2821 - 910925866615

Polar Normal (separate) - BGP2821 - 910925866698


Polar Wide Diagrams




Polar Normal (separate) - BGP2821 - 910925866727




Polar Normal (separate) - BGP2811 - 910925866860




Polar Normal (separate) - BGP2821 - 910925866753




Polar Normal (separate) - BGP2831 - 910925866762




Polar Normal (separate) - BGP2841 - 910925866908




Polar Normal (separate) - BGP2841 - 910925866667



Polar Normal (separate) - BGP2811 - 910925866652




Polar Normal (separate) - BGP2821 - 910925866930




Polar Normal (separate) - BGP2821 - 910925866772


Polar Wide Diagrams




Polar Normal (separate) - BGP2831 - 910925866755




Polar Normal (separate) - BGP2831 - 910925866789




Polar Normal (separate) - BGP2821 - 910925866941




Polar Normal (separate) - BGP2801 - 910925868722




Polar Normal (separate) - BGP2801 - 910925868727




Polar Normal (separate) - BGP2801 - 910925869152



Polar Normal (separate) - BGP2801 - 910925869154




Polar Normal (separate) - BGP2801 - 910925869156




Polar Normal (separate) - BGP2801 - 910925869153


Polar Wide Diagrams





Polar Normal (separate) - BGP2821 - 910925865677




Polar Normal (separate) - BGP2831 - 910925865680




Polar Normal (separate) - BGP2831 - 910925865671




Polar Normal (separate) - BGP2841 - 910925866445



Polar Normal (separate) - BGP2811 - 910925866610




Polar Normal (separate) - BGP2811 - 910925866613




Polar Normal (separate) - BGP2821 - 910925866616

Polar Normal (separate) - BGP2821 - 910925866443


Polar Wide Diagrams




Polar Normal (separate) - BGP2811 - 91092586644




Polar Normal (separate) - BGP2821 - 910925866617




Polar Normal (separate) - BGP2821 - 910925866618




Polar Normal (separate) - BGP2831 - 910925866630




Polar Normal (separate) - BGP2811 - 910925866644




Polar Normal (separate) - BGP2841 - 910925866636



Polar Normal (separate) - BGP2821 - 910925866642




Polar Normal (separate) - BGP2821 - 910925866657




Polar Normal (separate) - BGP2811 - 910925866612


Polar Wide Diagrams




Polar Normal (separate) - BGP2831 - 91092586662




Polar Normal (separate) - BGP2821 - 910925866721




Polar Normal (separate) - BGP2831 - 910925866759




Polar Normal (separate) - BGP2831 - 910925866631




Polar Normal (separate) - BGP2831 - 910925866633




Polar Normal (separate) - BGP2811 - 910925866611



Polar Normal (separate) - BGP2811 - 910925866614




Polar Normal (separate) - BGP2831 - 910925866632




Polar Normal (separate) - BGP2831 - 910925866643


Polar Wide Diagrams




Polar Normal (separate) - BGP2821 - 910925866712




Polar Normal (separate) - BGP2811 - 910925866780




Polar Normal (separate) - BGP2821 - 910925866796




Polar Normal (separate) - BGP2821 - 910925866704




Polar Normal (separate) - BGP2821 - 910925866724




Polar Normal (separate) - BGP2821 - 910925866734



Polar Normal (separate) - BGP2821 - 910925866761




Polar Normal (separate) - BGP2831 - 910925866777




Polar Normal (separate) - BGP2831 - 910925866810


Polar Wide Diagrams




Polar Normal (separate) - BGP2811 - 910925866862




Polar Normal (separate) - BGP2811 - 910925866865




Polar Normal (separate) - BGP2821 - 910925866899




Polar Normal (separate) - BGP2821 - 910925866730




Polar Normal (separate) - BGP2831 - 910925866757




Polar Normal (separate) - BGP2831 - 910925866904



Polar Normal (separate) - BGP2811 - 910925866911




Polar Normal (separate) - BGP2811 - 910925866932




Polar Normal (separate) - BGP2821 - 910925866722


Polar Wide Diagrams




Polar Normal (separate) - BGP282I - 910925866731




Polar Normal (separate) - BGP283I - 910925866793




Polar Normal (separate) - BGP282I - 910925866809




Polar Normal (separate) - BGP281I - 910925866859




Polar Normal (separate) - BGP282I - 910925866901




Polar Normal (separate) - BGP283I - 910925866905



Polar Normal (separate) - BGP281I - 910925866933




Polar Normal (separate) - BGP283I - 910925866902




Polar Normal (separate) - BGP283I - 910925866926


Polar Wide Diagrams




Polar Normal (separate) - BGP282I - 910925866853




Polar Normal (separate) - BGP281I - 910925866856




Polar Normal (separate) - BGP282I - 910925866912




Polar Normal (separate) - BGP281I - 910925866910




Polar Normal (separate) - BGP281I - 910925866925




Polar Normal (separate) - BGP281I - 910925866928



Polar Normal (separate) - BGP281I - 910925866929




Polar Normal (separate) - BGP281I - 910925867776




Polar Normal (separate) - BGP282I - 910925867777


Polar Wide Diagrams




Polar Normal (separate) - BGP2811 - 910925867775




Polar Normal (separate) - BGP2821 - 910925867778




Polar Normal (separate) - BGP2841 - 910925868071




Polar Normal (separate) - BGP2821 - 910925867781




Polar Normal (separate) - BGP2841 - 910925868093




Polar Normal (separate) - BGP2821 - 910925866804



Polar Normal (separate) - BGP2811 - 910925866898




Polar Normal (separate) - BGP2821 - 910925866934




Polar Normal (separate) - BGP2801 - 910925869155


Polar Wide Diagrams




Polar Normal (separate) - BGP280I - 910925869157




Polar Normal (separate) - BGP284I - 910925866647




Polar Normal (separate) - BGP281I - 910925868932




Polar Normal (separate) - BGP282I - 910925868934




Polar Normal (separate) - BGP284I - 910925868936




Polar Normal (separate) - BGP283I - 910925868939



Polar Normal (separate) - BGP284I - 910925866635




Polar Normal (separate) - BGP281I - 910925866891




Polar Normal (separate) - BGP283I - 910925866894


Polar Wide Diagrams




Polar Normal (separate) - BGP282I -
910925866892




Polar Normal (separate) - BGP281I -
910925866907




Polar Normal (separate) - BGP284I -
910925866909




Polar Normal (separate) - BGP281I -
910925866917




Polar Normal (separate) - BGP282I -
910925866915




Polar Normal (separate) - BGP284I -
910925866914



Polar Normal (separate) - BGP282I -
910925866919




Polar Normal (separate) - BGP284I -
910925866922




Polar Normal (separate) - BGP282I -
910925866918


Polar Wide Diagrams




Polar Normal (separate) - BGP2831 - 910925866920




Polar Normal (separate) - BGP2841 - 910925866923




Polar Normal (separate) - BGP2831 - 910925866921




Polar Normal (separate) - BGP2811 - 910925866935




Polar Normal (separate) - BGP2831 - 910925866936




Polar Normal (separate) - BGP2821 - 910925866938



Polar Normal (separate) - BGP2841 - 910925866937




Polar Normal (separate) - BGP2811 - 910925866939




Polar Normal (separate) - BGP2831 - 910925867860


Polar Wide Diagrams




Polar Normal (separate) - BGP2811 - 910925868105




Polar Normal (separate) - BGP2821 - 910925868107




Polar Normal (separate) - BGP2831 - 910925869853



Polar Normal (separate) - BGP2841 - 910925869854



Polar Normal (separate) - BGP2821 - 910925869852



Polar Normal (separate) - BGP2811 - 910925869851

