



Philips LuxSpace, recessed – high efficiency, visual comfort and a stylish design

LuxSpace, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is. For office applications LuxSpace supports health and wellbeing having dedicated Tunable White products and lighting controls.

Benefits

- Best-in-class efficacy with up to 160lm/W
- Creates a gentle, natural light, ensuring visual comfort
- Perfect ceiling integration with narrow rim or rimless version for plaster ceilings
- Improved glare control with office compliancy
- High color quality with CRI90 option (R9>50)
- Provides uniform lighting thanks to wide light distribution
- Supports Human Centric Lighting with Tunable White and integrated lighting controls

LuxSpace, recessed

Features

- Mini (DN560B/DN561B) and compact (DN570B/DN571B) sizes for recessed
- Square recessed (DN572B) and surface-mounted round (DN570C) versions in compact
- Choice of four optics: high-gloss, faceted, matt and white
- UGR19 and UGR22 versions with different product heights
- Selection of colors: High-gloss metalized, white (RAL9003), grey (RAL9006), black (RAL9004) as standard (any other RAL color possible upon request)
- Compliant for central emergency lighting with DC (upon request)
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), suspended deco glasses, through-wiring, Eca and B2ca cable & connector options
- Extended useful lifetime 50,000 hours at L90

Application



- Retail
- Offices
- Hospitals and Care Centers
- Hospitality
- Airports
- Museums
- Atriums

Versions




LuxSpace recessed with faceted reflector

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Suitable for random switching	Yes
Mechanical and Housing	
Optical cover type	-
Housing Color	White
Mech. impact protection code	IK02
Approval and Application	
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code	Light source replaceable
910505100834	DN570B LED12S/830 PSU-E C EW WH	-	No
910505100835	DN570B LED12S/840 PSU-E C WH	-	No
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	-	No
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	-	No
910505100842	DN570B LED20S/830 PSU-E C WH	-	No
910505100843	DN570B LED20S/840 PSU-E C WH	-	No
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	-	No
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	-	No
910505100850	DN570B LED20S/830 PSU-E C PG WH	-	No
910505100851	DN570B LED20S/840 PSU-E C PG WH	-	No
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	-	No
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	-	No
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	-	No
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	-	No
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	-	No
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	-	No
910505100868	DN570B LED24S/830 PSU-E C WH	-	No
910505100869	DN570B LED24S/840 PSU-E C WH	-	No
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	-	No
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	-	No
910505100884	DN570B LED40S/830 PSU-E C WH	-	No
910505100885	DN570B LED40S/840 PSU-E C WH	-	No
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	-	No
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	-	No
910505100901	DN570B LED40S/TWH PSD-E C WH	-	No
910505100903	DN570B LED60S/830 PSU-E C WH	-	No
910505100904	DN570B LED60S/840 PSU-E C WH	-	No
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	-	No
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	-	No
910505102295	DN570B LED24S/830 WIA-E C WH	-	No
910505102296	DN570B LED24S/840 WIA-E C WH	-	No
910505102299	DN570B LED40S/830 WIA-E C WH	-	No
910505102301	DN570B LED40S/840 WIA-E C WH	-	No
910505102304	DN570B LED24S/930H PSU-E C WH	-	No
910505102305	DN570B LED24S/940H PSU-E C WH	-	No
910505102652	DN570B LED20S/840UE PSU-E C WH	20S	Yes

Order Code	Full Product Name	Lamp family code	Light source replaceable
910505102654	DN570B LED20S/840UE PSU-E WR WH	20S	Yes
910505102656	DN570B LED24S/840UE PSU-E C WH	24S	Yes
910505100852	DN570B LED20S/830 PSU-E F WH	-	No
910505100853	DN570B LED20S/840 PSU-E F WH	-	No
910505100854	DN570B LED20S/830 PSU-E M WH	-	No
910505100855	DN570B LED20S/840 PSU-E M WH	-	No
910505100856	DN570B LED20S/830 PSU-E WR WH	-	No
910505100857	DN570B LED20S/840 PSU-E WR WH	-	No
910505100836	DN571B LED12S/830 PSU-E C WH	-	No
910505100837	DN571B LED12S/840 PSU-E C WH	-	No
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	-	No
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	-	No
910505100846	DN571B LED20S/830 PSU-E C WH	-	No
910505100847	DN571B LED20S/840 PSU-E C WH	-	No
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	-	No
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	-	No
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	-	No
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	-	No
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	-	No
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	-	No
910505100870	DN571B LED24S/830 PSU-E C WH	-	No
910505100871	DN571B LED24S/840 PSU-E C WH	-	No
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	-	No
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	-	No
910505100886	DN571B LED40S/830 PSU-E C WH	-	No
910505100887	DN571B LED40S/840 PSU-E C WH	-	No
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	-	No
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	-	No
910505100902	DN571B LED40S/TWH PSD-E C WH	-	No
910505102297	DN571B LED24S/830 WIA-E C WH	-	No
910505102298	DN571B LED24S/840 WIA-E C WH	-	No
910505102302	DN571B LED40S/830 WIA-E C WH	-	No
910505102303	DN571B LED40S/840 WIA-E C WH	-	No
910505102306	DN571B LED24S/930H PSU-E C WH	-	No
910505102307	DN571B LED24S/940H PSU-E C WH	-	No
910505102653	DN571B LED20S/840UE PSU-E C WH	20S	Yes
910505102655	DN571B LED20S/840UE PSU-E WR WH	20S	Yes
910505102657	DN571B LED24S/840UE PSU-E C WH	24S	Yes

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505100834	DN570B LED12S/830 PSU-E C EW WH	-	3000 K	>80	131 lm/W	910505100838	DN570B LED12S/830 DIA-VLC-E C WH	-	3000 K	>80	131 lm/W
910505100835	DN570B LED12S/840 PSU-E C WH	-	4000 K	>80	141 lm/W	910505100839	DN570B LED12S/840	-	4000 K	>80	141 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	DIA-VLC-E C WH				
910505100842	DN570B LED20S/830 PSU-E C WH	-	3000 K	>80	134 lm/W
910505100843	DN570B LED20S/840 PSU-E C WH	-	4000 K	>80	149 lm/W
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	-	3000 K	>80	113 lm/W
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	-	4000 K	>80	124 lm/W
910505100850	DN570B LED20S/830 PSU-E C PG WH	-	3000 K	>80	134 lm/W
910505100851	DN570B LED20S/840 PSU-E C PG WH	-	4000 K	>80	149 lm/W
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	-	3000 K	>80	134 lm/W
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	-	4000 K	>80	149 lm/W
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	-	3000 K	>80	113 lm/W
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	-	4000 K	>80	124 lm/W
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	-	3000 K	>80	134 lm/W
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	-	4000 K	>80	149 lm/W
910505100868	DN570B LED24S/830 PSU-E C WH	-	3000 K	>80	130 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505100869	DN570B LED24S/840 PSU-E C WH	-	4000 K	>80	141 lm/W
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	-	3000 K	>80	130 lm/W
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	-	4000 K	>80	141 lm/W
910505100884	DN570B LED40S/830 PSU-E C WH	-	3000 K	>80	133 lm/W
910505100885	DN570B LED40S/840 PSU-E C WH	-	4000 K	>80	147 lm/W
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	-	3000 K	>80	133 lm/W
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	-	4000 K	>80	147 lm/W
910505100901	DN570B LED40S/TWH PSD-E C WH	-	Tunable white degree(s) 2700-6500 K	>80	100 lm/W
910505100903	DN570B LED60S/830 PSU-E C WH	-	3000 K	>80	129 lm/W
910505100904	DN570B LED60S/840 PSU-E C WH	-	4000 K	>80	141 lm/W
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	-	3000 K	>80	129 lm/W
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	-	4000 K	>80	141 lm/W
910505102295	DN570B LED24S/830 WIA-E C WH	-	3000 K	>80	130 lm/W
910505102296	DN570B LED24S/840 WIA-E C WH	-	4000 K	>80	130 lm/W

LuxSpace, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505102299	DN570B LED40S/830 WIA-E C WH	-	3000 K	>80	133 lm/W
910505102301	DN570B LED40S/840 WIA-E C WH	-	4000 K	>80	147 lm/W
910505102304	DN570B LED24S/930H PSU-E C WH	-	3000 K	>90	130 lm/W
910505102305	DN570B LED24S/940H PSU-E C WH	-	4000 K	>90	133 lm/W
910505102652	DN570B LED20S/840UE PSU-E C WH	-	4000 K	>80	161 lm/W
910505102654	DN570B LED20S/840UE PSU-E WR WH	-	4000 K	>80	161 lm/W
910505102656	DN570B LED24S/840UE PSU-E C WH	-	4000 K	>80	160 lm/W
910505100852	DN570B LED20S/830 PSU-E F WH	-	3000 K	>80	134 lm/W
910505100853	DN570B LED20S/840 PSU-E F WH	-	4000 K	>80	149 lm/W
910505100854	DN570B LED20S/830 PSU-E M WH	-	3000 K	>80	113 lm/W
910505100855	DN570B LED20S/840 PSU-E M WH	-	4000 K	>80	125 lm/W
910505100856	DN570B LED20S/830 PSU-E WR WH	-	3000 K	>80	134 lm/W
910505100857	DN570B LED20S/840 PSU-E WR WH	-	4000 K	>80	149 lm/W
910505100836	DN571B LED12S/830 PSU-E C WH	-	3000 K	>80	131 lm/W
910505100837	DN571B LED12S/840 PSU-E C WH	-	4000 K	>80	141 lm/W
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	-	3000 K	>80	131 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	-	4000 K	>80	141 lm/W
910505100846	DN571B LED20S/830 PSU-E C WH	-	3000 K	>80	134 lm/W
910505100847	DN571B LED20S/840 PSU-E C WH	-	4000 K	>80	149 lm/W
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	-	3000 K	>80	113 lm/W
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	-	4000 K	>80	124 lm/W
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	-	3000 K	>80	134 lm/W
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	-	4000 K	>80	149 lm/W
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	-	3000 K	>80	113 lm/W
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	-	4000 K	>80	124 lm/W
910505100870	DN571B LED24S/830 PSU-E C WH	-	3000 K	>80	130 lm/W
910505100871	DN571B LED24S/840 PSU-E C WH	-	4000 K	>80	141 lm/W
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	-	3000 K	>80	130 lm/W
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	-	4000 K	>80	141 lm/W

LuxSpace, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505100886	DN571B LED40S/830 PSU-E C WH	-	3000 K	>80	133 lm/W
910505100887	DN571B LED40S/840 PSU-E C WH	-	4000 K	>80	147 lm/W
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	-	3000 K	>80	133 lm/W
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	-	4000 K	>80	147 lm/W
910505100902	DN571B LED40S/TWH PSD-E C WH	-	Tunable white 2700-6500 K	>80	100 lm/W
910505102297	DN571B LED24S/830 WIA-E C WH	-	3000 K	>80	130 lm/W
910505102298	DN571B LED24S/840 WIA-E C WH	-	4000 K	>80	140 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
910505102302	DN571B LED40S/830 WIA-E C WH	-	3000 K	>80	133 lm/W
910505102303	DN571B LED40S/840 WIA-E C WH	-	4000 K	>80	147 lm/W
910505102306	DN571B LED24S/930H PSU-E C WH	-	3000 K	>90	130 lm/W
910505102307	DN571B LED24S/940H PSU-E C WH	-	4000 K	>90	133 lm/W
910505102653	DN571B LED20S/840UE PSU-E C WH	-	4000 K	>80	161 lm/W
910505102655	DN571B LED20S/840UE PSU-E WR WH	-	4000 K	>80	161 lm/W
910505102657	DN571B LED24S/840UE PSU-E C WH	-	4000 K	>80	160 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Upward light output ratio
910505100834	DN570B LED12S/830 PSU-E C EW WH	1,300 lm	-
910505100835	DN570B LED12S/840 PSU-E C WH	1,300 lm	-
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	1,300 lm	-
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	1,300 lm	-
910505100842	DN570B LED20S/830 PSU-E C WH	2,200 lm	-
910505100843	DN570B LED20S/840 PSU-E C WH	2,200 lm	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	2,200 lm	-
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	2,200 lm	-
910505100850	DN570B LED20S/830 PSU-E C PG WH	2,200 lm	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	2,200 lm	-
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	2,200 lm	-
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	2,200 lm	-
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	2,200 lm	-
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	2,200 lm	-
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	2,200 lm	-
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	2,200 lm	-

Order Code	Full Product Name	Luminous Flux	Upward light output ratio
910505100868	DN570B LED24S/830 PSU-E C WH	2,600 lm	-
910505100869	DN570B LED24S/840 PSU-E C WH	2,600 lm	-
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	2,600 lm	-
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	2,600 lm	-
910505100884	DN570B LED40S/830 PSU-E C WH	4,400 lm	-
910505100885	DN570B LED40S/840 PSU-E C WH	4,400 lm	-
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	4,400 lm	-
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	4,400 lm	-
910505100901	DN570B LED40S/TWH PSD-E C WH	3,100 lm	-
910505100903	DN570B LED60S/830 PSU-E C WH	6,200 lm	-
910505100904	DN570B LED60S/840 PSU-E C WH	6,200 lm	-
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	6,200 lm	-
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	6,200 lm	-
910505102295	DN570B LED24S/830 WIA-E C WH	2,600 lm	-
910505102296	DN570B LED24S/840 WIA-E C WH	2,600 lm	-
910505102299	DN570B LED40S/830 WIA-E C WH	4,400 lm	-
910505102301	DN570B LED40S/840 WIA-E C WH	4,400 lm	-
910505102304	DN570B LED24S/930H PSU-E C WH	2,600 lm	-
910505102305	DN570B LED24S/940H PSU-E C WH	2,600 lm	-
910505102652	DN570B LED20S/840UE PSU-E C WH	2,100 lm	0

Order Code	Full Product Name	Luminous Flux	Upward light output ratio
910505102654	DN570B LED20S/840UE PSU-E WR WH	2,100 lm	0
910505102656	DN570B LED24S/840UE PSU-E C WH	2,400 lm	0
910505100852	DN570B LED20S/830 PSU-E F WH	2,200 lm	-
910505100853	DN570B LED20S/840 PSU-E F WH	2,200 lm	-
910505100854	DN570B LED20S/830 PSU-E M WH	1,850 lm	-
910505100855	DN570B LED20S/840 PSU-E M WH	1,850 lm	-
910505100856	DN570B LED20S/830 PSU-E WR WH	2,200 lm	-
910505100857	DN570B LED20S/840 PSU-E WR WH	2,200 lm	-
910505100836	DN571B LED12S/830 PSU-E C WH	1,300 lm	-
910505100837	DN571B LED12S/840 PSU-E C WH	1,300 lm	-
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	1,300 lm	-
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	1,300 lm	-
910505100846	DN571B LED20S/830 PSU-E C WH	2,200 lm	-
910505100847	DN571B LED20S/840 PSU-E C WH	2,200 lm	-
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	2,200 lm	-
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	2,200 lm	-
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	2,200 lm	-
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	2,200 lm	-
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	2,200 lm	-

Order Code	Full Product Name	Luminous Flux	Upward light output ratio
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	2,200 lm	-
910505100870	DN571B LED24S/830 PSU-E C WH	2,600 lm	-
910505100871	DN571B LED24S/840 PSU-E C WH	2,600 lm	-
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	2,600 lm	-
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	2,600 lm	-
910505100886	DN571B LED40S/830 PSU-E C WH	4,400 lm	-
910505100887	DN571B LED40S/840 PSU-E C WH	4,400 lm	-
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	4,400 lm	-
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	4,400 lm	-
910505100902	DN571B LED40S/TWH PSD-E C WH	3,100 lm	-
910505102297	DN571B LED24S/830 WIA-E C WH	2,600 lm	-
910505102298	DN571B LED24S/840 WIA-E C WH	2,600 lm	-
910505102302	DN571B LED40S/830 WIA-E C WH	4,400 lm	-
910505102303	DN571B LED40S/840 WIA-E C WH	4,400 lm	-
910505102306	DN571B LED24S/930H PSU-E C WH	2,600 lm	-
910505102307	DN571B LED24S/940H PSU-E C WH	2,600 lm	-
910505102653	DN571B LED20S/840UE PSU-E C WH	2,100 lm	0
910505102655	DN571B LED20S/840UE PSU-E WR WH	2,100 lm	0
910505102657	DN571B LED24S/840UE PSU-E C WH	2,400 lm	0

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption
910505100834	DN570B LED12S/830 PSU-E C EW WH	50 to 60 Hz	9.9 W
910505100835	DN570B LED12S/840 PSU-E C WH	50 to 60 Hz	9.2 W
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	50 to 60 Hz	9.9 W
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	50 to 60 Hz	9.2 W
910505100842	DN570B LED20S/830 PSU-E C WH	50 to 60 Hz	16.4 W
910505100843	DN570B LED20S/840 PSU-E C WH	50 to 60 Hz	14.8 W
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	50 to 60 Hz	19.4 W
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	50 to 60 Hz	17.8 W
910505100850	DN570B LED20S/830 PSU-E C PG WH	50 to 60 Hz	16.4 W
910505100851	DN570B LED20S/840 PSU-E C PG WH	50 to 60 Hz	14.8 W
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	50 to 60 Hz	16.4 W
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	50 to 60 Hz	14.8 W

Order Code	Full Product Name	Line Frequency	Power Consumption
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	50 to 60 Hz	19.4 W
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	50 to 60 Hz	17.8 W
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	50 to 60 Hz	16.4 W
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	50 to 60 Hz	14.8 W
910505100868	DN570B LED24S/830 PSU-E C WH	0/50/60 Hz	20 W
910505100869	DN570B LED24S/840 PSU-E C WH	50 to 60 Hz	18.4 W
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	50 to 60 Hz	20 W
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	50 to 60 Hz	18.4 W
910505100884	DN570B LED40S/830 PSU-E C WH	0/50/60 Hz	33 W
910505100885	DN570B LED40S/840 PSU-E C WH	0/50/60 Hz	30 W
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	50 to 60 Hz	33 W
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	50 to 60 Hz	30 W

Order Code	Full Product Name	Line Frequency	Power
			Consumption
910505100901	DN570B LED40S/TWH PSD-E C WH	50 to 60 Hz	30 W
910505100903	DN570B LED60S/830 PSU-E C WH	50 to 60 Hz	48 W
910505100904	DN570B LED60S/840 PSU-E C WH	50 to 60 Hz	44 W
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	50 to 60 Hz	48 W
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	50 to 60 Hz	44 W
910505102295	DN570B LED24S/830 WIA-E C WH	0/50/60 Hz	20 W
910505102296	DN570B LED24S/840 WIA-E C WH	0/50/60 Hz	20 W
910505102299	DN570B LED40S/830 WIA-E C WH	0/50/60 Hz	33 W
910505102301	DN570B LED40S/840 WIA-E C WH	0/50/60 Hz	30 W
910505102304	DN570B LED24S/930H PSU-E C WH	0/50/60 Hz	20 W
910505102305	DN570B LED24S/940H PSU-E C WH	0/50/60 Hz	20 W
910505102652	DN570B LED20S/840UE PSU-E C WH	50 to 60 Hz	13 W
910505102654	DN570B LED20S/840UE PSU-E WR WH	50 to 60 Hz	13 W
910505102656	DN570B LED24S/840UE PSU-E C WH	50 to 60 Hz	15 W
910505100852	DN570B LED20S/830 PSU-E F WH	50 to 60 Hz	16.4 W
910505100853	DN570B LED20S/840 PSU-E F WH	50 to 60 Hz	14.8 W
910505100854	DN570B LED20S/830 PSU-E M WH	50 to 60 Hz	16.4 W
910505100855	DN570B LED20S/840 PSU-E M WH	50 to 60 Hz	14.8 W
910505100856	DN570B LED20S/830 PSU-E WR WH	50 to 60 Hz	16.4 W
910505100857	DN570B LED20S/840 PSU-E WR WH	50 to 60 Hz	14.8 W
910505100836	DN571B LED12S/830 PSU-E C WH	50 to 60 Hz	9.9 W
910505100837	DN571B LED12S/840 PSU-E C WH	50 to 60 Hz	9.2 W
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	50 to 60 Hz	9.9 W
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	50 to 60 Hz	9.2 W
910505100846	DN571B LED20S/830 PSU-E C WH	50 to 60 Hz	16.4 W

Order Code	Full Product Name	Line Frequency	Power
			Consumption
910505100847	DN571B LED20S/840 PSU-E C WH	50 to 60 Hz	14.8 W
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	50 to 60 Hz	19.4 W
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	50 to 60 Hz	17.8 W
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	50 to 60 Hz	16.4 W
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	50 to 60 Hz	14.8 W
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	50 to 60 Hz	19.4 W
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	50 to 60 Hz	17.8 W
910505100870	DN571B LED24S/830 PSU-E C WH	0/50/60 Hz	20 W
910505100871	DN571B LED24S/840 PSU-E C WH	50 to 60 Hz	18.4 W
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	50 to 60 Hz	20 W
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	50 to 60 Hz	18.4 W
910505100886	DN571B LED40S/830 PSU-E C WH	50 to 60 Hz	33 W
910505100887	DN571B LED40S/840 PSU-E C WH	50 to 60 Hz	30 W
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	50 to 60 Hz	33 W
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	50 to 60 Hz	30 W
910505100902	DN571B LED40S/TWH PSD-E C WH	50 to 60 Hz	30 W
910505102297	DN571B LED24S/830 WIA-E C WH	0/50/60 Hz	20 W
910505102298	DN571B LED24S/840 WIA-E C WH	0/50/60 Hz	20 W
910505102302	DN571B LED40S/830 WIA-E C WH	0/50/60 Hz	33 W
910505102303	DN571B LED40S/840 WIA-E C WH	0/50/60 Hz	30 W
910505102306	DN571B LED24S/930H PSU-E C WH	0/50/60 Hz	20 W
910505102307	DN571B LED24S/940H PSU-E C WH	0/50/60 Hz	20 W
910505102653	DN571B LED20S/840UE PSU-E C WH	50 to 60 Hz	13 W
910505102655	DN571B LED20S/840UE PSU-E WR WH	50 to 60 Hz	13 W
910505102657	DN571B LED24S/840UE PSU-E C WH	50 to 60 Hz	15 W

Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910505100834	DN570B LED12S/830 PSU-E C EW WH	No	-
910505100835	DN570B LED12S/840 PSU-E C WH	No	-
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	Yes	1%
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	Yes	1%
910505100842	DN570B LED20S/830 PSU-E C WH	No	-
910505100843	DN570B LED20S/840 PSU-E C WH	No	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	No	-
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	No	-
910505100850	DN570B LED20S/830 PSU-E C PG WH	No	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	No	-
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	Yes	1%
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	Yes	1%
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	Yes	1%
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	Yes	1%
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	Yes	1%
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	Yes	1%
910505100868	DN570B LED24S/830 PSU-E C WH	No	Not applicable
910505100869	DN570B LED24S/840 PSU-E C WH	No	-
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	Yes	1%
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	Yes	1%
910505100884	DN570B LED40S/830 PSU-E C WH	No	Not applicable
910505100885	DN570B LED40S/840 PSU-E C WH	No	Not applicable
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	Yes	1%
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	Yes	1%
910505100901	DN570B LED40S/TWH PSD-E C WH	Yes	1%
910505100903	DN570B LED60S/830 PSU-E C WH	No	-
910505100904	DN570B LED60S/840 PSU-E C WH	No	-
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	Yes	1%
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	Yes	1%
910505102295	DN570B LED24S/830 WIA-E C WH	Yes	10%
910505102296	DN570B LED24S/840 WIA-E C WH	Yes	10%
910505102299	DN570B LED40S/830 WIA-E C WH	Yes	10%
910505102301	DN570B LED40S/840 WIA-E C WH	Yes	10%
910505102304	DN570B LED24S/930H PSU-E C WH	No	Not applicable
910505102305	DN570B LED24S/940H PSU-E C WH	No	Not applicable
910505102652	DN570B LED20S/840UE PSU-E C WH	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910505102654	DN570B LED20S/840UE PSU-E WR WH	No	Not applicable
910505102656	DN570B LED24S/840UE PSU-E C WH	No	Not applicable
910505100852	DN570B LED20S/830 PSU-E F WH	No	-
910505100853	DN570B LED20S/840 PSU-E F WH	No	-
910505100854	DN570B LED20S/830 PSU-E M WH	No	-
910505100855	DN570B LED20S/840 PSU-E M WH	No	-
910505100856	DN570B LED20S/830 PSU-E WR WH	No	-
910505100857	DN570B LED20S/840 PSU-E WR WH	No	-
910505100836	DN571B LED12S/830 PSU-E C WH	No	-
910505100837	DN571B LED12S/840 PSU-E C WH	No	-
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	Yes	1%
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	Yes	1%
910505100846	DN571B LED20S/830 PSU-E C WH	No	-
910505100847	DN571B LED20S/840 PSU-E C WH	No	-
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	No	-
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	No	-
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	Yes	1%
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	Yes	1%
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	Yes	1%
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	Yes	1%
910505100870	DN571B LED24S/830 PSU-E C WH	No	Not applicable
910505100871	DN571B LED24S/840 PSU-E C WH	No	-
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	Yes	1%
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	Yes	1%
910505100886	DN571B LED40S/830 PSU-E C WH	No	-
910505100887	DN571B LED40S/840 PSU-E C WH	No	-
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	Yes	1%
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	Yes	1%
910505100902	DN571B LED40S/TWH PSD-E C WH	Yes	1%
910505102297	DN571B LED24S/830 WIA-E C WH	Yes	10%
910505102298	DN571B LED24S/840 WIA-E C WH	Yes	10%
910505102302	DN571B LED40S/830 WIA-E C WH	Yes	10%
910505102303	DN571B LED40S/840 WIA-E C WH	Yes	10%
910505102306	DN571B LED24S/930H PSU-E C WH	No	Not applicable
910505102307	DN571B LED24S/940H PSU-E C WH	No	Not applicable
910505102653	DN571B LED20S/840UE PSU-E C WH	No	Not applicable
910505102655	DN571B LED20S/840UE PSU-E WR WH	No	Not applicable
910505102657	DN571B LED24S/840UE PSU-E C WH	No	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
910505100834	DN570B LED12S/830 PSU-E C EW WH	IP20
910505100835	DN570B LED12S/840 PSU-E C WH	IP20
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	IP20
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	IP20
910505100842	DN570B LED20S/830 PSU-E C WH	IP20
910505100843	DN570B LED20S/840 PSU-E C WH	IP20
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	IP20

Order Code	Full Product Name	Ingress protection code
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	IP20
910505100850	DN570B LED20S/830 PSU-E C PG WH	IP20/54
910505100851	DN570B LED20S/840 PSU-E C PG WH	IP20/54
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	IP20
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	IP20
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	IP20
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	IP20

Order Code	Full Product Name	Ingress protection code
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	IP20/54
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	IP20/54
910505100868	DN570B LED24S/830 PSU-E C WH	IP20
910505100869	DN570B LED24S/840 PSU-E C WH	IP20
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	IP20
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	IP20
910505100884	DN570B LED40S/830 PSU-E C WH	IP20
910505100885	DN570B LED40S/840 PSU-E C WH	IP20
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	IP20
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	IP20
910505100901	DN570B LED40S/TWH PSD-E C WH	IP20
910505100903	DN570B LED60S/830 PSU-E C WH	IP20
910505100904	DN570B LED60S/840 PSU-E C WH	IP20
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	IP20
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	IP20
910505102295	DN570B LED24S/830 WIA-E C WH	IP20
910505102296	DN570B LED24S/840 WIA-E C WH	IP20
910505102299	DN570B LED40S/830 WIA-E C WH	IP20
910505102301	DN570B LED40S/840 WIA-E C WH	IP20
910505102304	DN570B LED24S/930H PSU-E C WH	IP20
910505102305	DN570B LED24S/940H PSU-E C WH	IP20
910505102652	DN570B LED20S/840UE PSU-E C WH	IP20
910505102654	DN570B LED20S/840UE PSU-E WR WH	IP20
910505102656	DN570B LED24S/840UE PSU-E C WH	IP20
910505100852	DN570B LED20S/830 PSU-E F WH	IP20
910505100853	DN570B LED20S/840 PSU-E F WH	IP20
910505100854	DN570B LED20S/830 PSU-E M WH	IP20
910505100855	DN570B LED20S/840 PSU-E M WH	IP20
910505100856	DN570B LED20S/830 PSU-E WR WH	IP20
910505100857	DN570B LED20S/840 PSU-E WR WH	IP20

Order Code	Full Product Name	Ingress protection code
910505100836	DN571B LED12S/830 PSU-E C WH	IP20
910505100837	DN571B LED12S/840 PSU-E C WH	IP20
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	IP20
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	IP20
910505100846	DN571B LED20S/830 PSU-E C WH	IP20
910505100847	DN571B LED20S/840 PSU-E C WH	IP20
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	IP20
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	IP20
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	IP20
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	IP20
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	IP20
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	IP20
910505100870	DN571B LED24S/830 PSU-E C WH	IP20
910505100871	DN571B LED24S/840 PSU-E C WH	IP20
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	IP20
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	IP20
910505100886	DN571B LED40S/830 PSU-E C WH	IP20
910505100887	DN571B LED40S/840 PSU-E C WH	IP20
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	IP20
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	IP20
910505100902	DN571B LED40S/TWH PSD-E C WH	IP20
910505102297	DN571B LED24S/830 WIA-E C WH	IP20
910505102298	DN571B LED24S/840 WIA-E C WH	IP20
910505102302	DN571B LED40S/830 WIA-E C WH	IP20
910505102303	DN571B LED40S/840 WIA-E C WH	IP20
910505102306	DN571B LED24S/930H PSU-E C WH	IP20
910505102307	DN571B LED24S/940H PSU-E C WH	IP20
910505102653	DN571B LED20S/840UE PSU-E C WH	IP20
910505102655	DN571B LED20S/840UE PSU-E WR WH	IP20
910505102657	DN571B LED24S/840UE PSU-E C WH	IP20

Emergency Operation

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505100834	DN570B LED12S/830 PSU-E C EW WH	-	-
910505100835	DN570B LED12S/840 PSU-E C WH	-	-
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	-	-
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	-	-
910505100842	DN570B LED20S/830 PSU-E C WH	-	-
910505100843	DN570B LED20S/840 PSU-E C WH	-	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	Emergency lighting 3 hours duration Pro version	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	Emergency lighting 3 hours duration Pro version	3 hour(s)
910505100850	DN570B LED20S/830 PSU-E C PG WH	-	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	-	-
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	-	-
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	-	-
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	Emergency lighting 3 hours	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
		duration Pro version	
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	Emergency lighting 3 hours duration Pro version	3 hour(s)
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	-	-
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	-	-
910505100868	DN570B LED24S/830 PSU-E C WH	-	-
910505100869	DN570B LED24S/840 PSU-E C WH	-	-
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	-	-
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	-	-
910505100884	DN570B LED40S/830 PSU-E C WH	-	-
910505100885	DN570B LED40S/840 PSU-E C WH	-	-
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	-	-
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	-	-
910505100901	DN570B LED40S/TWH PSD-E C WH	-	-
910505100903	DN570B LED60S/830 PSU-E C WH	-	-
910505100904	DN570B LED60S/840 PSU-E C WH	-	-
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	-	-
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	-	-
910505102295	DN570B LED24S/830 WIA-E C WH	-	-
910505102296	DN570B LED24S/840 WIA-E C WH	-	-
910505102299	DN570B LED40S/830 WIA-E C WH	-	-
910505102301	DN570B LED40S/840 WIA-E C WH	-	-
910505102304	DN570B LED24S/930H PSU-E C WH	-	-
910505102305	DN570B LED24S/940H PSU-E C WH	-	-
910505102652	DN570B LED20S/840UE PSU-E C WH	-	-
910505102654	DN570B LED20S/840UE PSU-E WR WH	-	-
910505102656	DN570B LED24S/840UE PSU-E C WH	-	-
910505100852	DN570B LED20S/830 PSU-E F WH	-	-
910505100853	DN570B LED20S/840 PSU-E F WH	-	-
910505100854	DN570B LED20S/830 PSU-E M WH	-	-
910505100855	DN570B LED20S/840 PSU-E M WH	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505100856	DN570B LED20S/830 PSU-E WR WH	-	-
910505100857	DN570B LED20S/840 PSU-E WR WH	-	-
910505100836	DN571B LED12S/830 PSU-E C WH	-	-
910505100837	DN571B LED12S/840 PSU-E C WH	-	-
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	-	-
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	-	-
910505100846	DN571B LED20S/830 PSU-E C WH	-	-
910505100847	DN571B LED20S/840 PSU-E C WH	-	-
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	Emergency lighting 3 hours duration Pro version	3 hour(s)
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	Emergency lighting 3 hours duration Pro version	3 hour(s)
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	-	-
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	-	-
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	Emergency lighting 3 hours duration Pro version	3 hour(s)
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	Emergency lighting 3 hours duration Pro version	3 hour(s)
910505100870	DN571B LED24S/830 PSU-E C WH	-	-
910505100871	DN571B LED24S/840 PSU-E C WH	-	-
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	-	-
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	-	-
910505100886	DN571B LED40S/830 PSU-E C WH	-	-
910505100887	DN571B LED40S/840 PSU-E C WH	-	-
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	-	-
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	-	-
910505100902	DN571B LED40S/TWH PSD-E C WH	-	-
910505102297	DN571B LED24S/830 WIA-E C WH	-	-
910505102298	DN571B LED24S/840 WIA-E C WH	-	-
910505102302	DN571B LED40S/830 WIA-E C WH	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505102303	DN571B LED40S/840 WIA-E C WH	-	-
910505102306	DN571B LED24S/930H PSU-E C WH	-	-
910505102307	DN571B LED24S/940H PSU-E C WH	-	-
910505102653	DN571B LED20S/840UE PSU-E C WH	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910505102655	DN571B LED20S/840UE PSU-E WR WH	-	-
910505102657	DN571B LED24S/840UE PSU-E C WH	-	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Stroboscopic effect visibility measure (SVM)
910505100834	DN570B LED12S/830 PSU-E C EW WH	+10 to +25 °C	ENEC mark	-
910505100835	DN570B LED12S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100842	DN570B LED20S/830 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100843	DN570B LED20S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	+10 to +25 °C	ENEC mark	-
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	+10 to +25 °C	ENEC mark	-
910505100850	DN570B LED20S/830 PSU-E C PG WH	+10 to +25 °C	ENEC mark	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	+10 to +25 °C	ENEC mark	-
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	+10 to +25 °C	ENEC mark	-
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	+10 to +25 °C	ENEC mark	-
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	+10 to +25 °C	ENEC mark	-
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	+10 to +25 °C	ENEC mark	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Stroboscopic effect visibility measure (SVM)
910505100868	DN570B LED24S/830 PSU-E C WH	+10 to +25 °C	ENEC mark	0.4
910505100869	DN570B LED24S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100884	DN570B LED40S/830 PSU-E C WH	+10 to +25 °C	ENEC mark	0.4
910505100885	DN570B LED40S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	0.4
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100901	DN570B LED40S/TWH PSD-E C WH	+10 to +25 °C	-	-
910505100903	DN570B LED60S/830 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100904	DN570B LED60S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505102295	DN570B LED24S/830 WIA-E C WH	+10 to +25 °C	ENEC mark	0.5
910505102296	DN570B LED24S/840 WIA-E C WH	+10 to +25 °C	ENEC mark	0.5
910505102299	DN570B LED40S/830 WIA-E C WH	+10 to +25 °C	ENEC mark	0.5

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Stroboscopic effect visibility measure (SVM)
910505102301	DN570B LED40S/840 WIA-E C WH	+10 to +25 °C	ENEC mark	0.5
910505102304	DN570B LED24S/930H PSU-E C WH	+10 to +25 °C	ENEC mark	0.4
910505102305	DN570B LED24S/940H PSU-E C WH	+10 to +25 °C	ENEC mark	0.4
910505102652	DN570B LED20S/840UE PSU-E C WH	+10 to +35 °C	ENEC mark	-
910505102654	DN570B LED20S/840UE PSU-E WR WH	+10 to +35 °C	ENEC mark	-
910505102656	DN570B LED24S/840UE PSU-E C WH	+10 to +35 °C	ENEC mark	-
910505100852	DN570B LED20S/830 PSU-E F WH	+10 to +25 °C	ENEC mark	-
910505100853	DN570B LED20S/840 PSU-E F WH	+10 to +25 °C	ENEC mark	-
910505100854	DN570B LED20S/830 PSU-E M WH	+10 to +25 °C	ENEC mark	-
910505100855	DN570B LED20S/840 PSU-E M WH	+10 to +25 °C	ENEC mark	-
910505100856	DN570B LED20S/830 PSU-E WR WH	+10 to +25 °C	ENEC mark	-
910505100857	DN570B LED20S/840 PSU-E WR WH	+10 to +25 °C	ENEC mark	-
910505100836	DN571B LED12S/830 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100837	DN571B LED12S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100846	DN571B LED20S/830 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100847	DN571B LED20S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	+10 to +25 °C	ENEC mark	-
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	+10 to +25 °C	ENEC mark	-
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Stroboscopic effect visibility measure (SVM)
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	+10 to +25 °C	ENEC mark	-
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	+10 to +25 °C	ENEC mark	-
910505100870	DN571B LED24S/830 PSU-E C WH	+10 to +25 °C	ENEC mark	0.4
910505100871	DN571B LED24S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100886	DN571B LED40S/830 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100887	DN571B LED40S/840 PSU-E C WH	+10 to +25 °C	ENEC mark	-
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	+10 to +25 °C	ENEC mark	-
910505100902	DN571B LED40S/TWH PSD-E C WH	+10 to +25 °C	-	-
910505102297	DN571B LED24S/830 WIA-E C WH	+10 to +25 °C	ENEC mark	0.5
910505102298	DN571B LED24S/840 WIA-E C WH	+10 to +25 °C	ENEC mark	0.5
910505102302	DN571B LED40S/830 WIA-E C WH	+10 to +25 °C	ENEC mark	0.5
910505102303	DN571B LED40S/840 WIA-E C WH	+10 to +25 °C	ENEC mark	0.5
910505102306	DN571B LED24S/930H PSU-E C WH	+10 to +25 °C	ENEC mark	0.4
910505102307	DN571B LED24S/940H PSU-E C WH	+10 to +25 °C	ENEC mark	0.4
910505102653	DN571B LED20S/840UE PSU-E C WH	+10 to +35 °C	ENEC mark	-
910505102655	DN571B LED20S/840UE PSU-E WR WH	+10 to +35 °C	ENEC mark	-
910505102657	DN571B LED24S/840UE PSU-E C WH	+10 to +35 °C	ENEC mark	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505100834	DN570B LED12S/830 PSU-E C EW WH	(0.43, 0.40) SDCM≤2

Order Code	Full Product Name	Initial chromaticity
910505100835	DN570B LED12S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2

Order Code	Full Product Name	Initial chromaticity
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100842	DN570B LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100843	DN570B LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM≤2
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38) SDCM≤2
910505100850	DN570B LED20S/830 PSU-E C PG WH	(0.43, 0.40) SDCM≤2
910505100851	DN570B LED20S/840 PSU-E C PG WH	(0.38, 0.38) SDCM≤2
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40) SDCM≤2
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38) SDCM≤2
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	(0.43, 0.40) SDCM≤2
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	(0.38, 0.38) SDCM≤2
910505100868	DN570B LED24S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100869	DN570B LED24S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100884	DN570B LED40S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100885	DN570B LED40S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100901	DN570B LED40S/TWH PSD-E C WH	(0.307,0.326) SDCM≤4
910505100903	DN570B LED60S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100904	DN570B LED60S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505102295	DN570B LED24S/830 WIA-E C WH	(0.43, 0.40) SDCM≤2
910505102296	DN570B LED24S/840 WIA-E C WH	(0.38, 0.38) SDCM≤2
910505102299	DN570B LED40S/830 WIA-E C WH	(0.43, 0.40) SDCM≤2
910505102301	DN570B LED40S/840 WIA-E C WH	(0.38, 0.38) SDCM≤2
910505102304	DN570B LED24S/930H PSU-E C WH	(0.43, 0.40) SDCM≤2
910505102305	DN570B LED24S/940H PSU-E C WH	(0.38, 0.38) SDCM≤2
910505102652	DN570B LED20S/840UE PSU-E C WH	-
910505102654	DN570B LED20S/840UE PSU-E WR WH	-
910505102656	DN570B LED24S/840UE PSU-E C WH	-

Order Code	Full Product Name	Initial chromaticity
910505100852	DN570B LED20S/830 PSU-E F WH	(0.43, 0.40) SDCM≤2
910505100853	DN570B LED20S/840 PSU-E F WH	(0.38, 0.38) SDCM≤2
910505100854	DN570B LED20S/830 PSU-E M WH	(0.43, 0.40) SDCM≤2
910505100855	DN570B LED20S/840 PSU-E M WH	(0.38, 0.38) SDCM≤2
910505100856	DN570B LED20S/830 PSU-E WR WH	(0.43, 0.40) SDCM≤2
910505100857	DN570B LED20S/840 PSU-E WR WH	(0.38, 0.38) SDCM≤2
910505100836	DN571B LED12S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100837	DN571B LED12S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100846	DN571B LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100847	DN571B LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM≤2
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38) SDCM≤2
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40) SDCM≤2
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38) SDCM≤2
910505100870	DN571B LED24S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100871	DN571B LED24S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100886	DN571B LED40S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100887	DN571B LED40S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100902	DN571B LED40S/TWH PSD-E C WH	(0.307,0.326) SDCM≤4
910505102297	DN571B LED24S/830 WIA-E C WH	(0.43, 0.40) SDCM≤2
910505102298	DN571B LED24S/840 WIA-E C WH	(0.38, 0.38) SDCM≤2
910505102302	DN571B LED40S/830 WIA-E C WH	(0.43, 0.40) SDCM≤2
910505102303	DN571B LED40S/840 WIA-E C WH	(0.38, 0.38) SDCM≤2
910505102306	DN571B LED24S/930H PSU-E C WH	(0.43, 0.40) SDCM≤2
910505102307	DN571B LED24S/940H PSU-E C WH	(0.38, 0.38) SDCM≤2
910505102653	DN571B LED20S/840UE PSU-E C WH	-
910505102655	DN571B LED20S/840UE PSU-E WR WH	-
910505102657	DN571B LED24S/840UE PSU-E C WH	-

Product Data


Order Code	Full Product Name	Product family code
910505100834	DN570B LED12S/830 PSU-E C EW WH	DN570B
910505100835	DN570B LED12S/840 PSU-E C WH	DN570B
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	DN570B
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	DN570B
910505100842	DN570B LED20S/830 PSU-E C WH	DN570B
910505100843	DN570B LED20S/840 PSU-E C WH	DN570B
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	DN570B
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	DN570B
910505100850	DN570B LED20S/830 PSU-E C PG WH	DN570B
910505100851	DN570B LED20S/840 PSU-E C PG WH	DN570B
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	DN570B
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	DN570B

Order Code	Full Product Name	Product family code
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	DN570B
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	DN570B
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	DN570B
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	DN570B
910505100868	DN570B LED24S/830 PSU-E C WH	DN570B
910505100869	DN570B LED24S/840 PSU-E C WH	DN570B
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	DN570B
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	DN570B
910505100884	DN570B LED40S/830 PSU-E C WH	DN570B
910505100885	DN570B LED40S/840 PSU-E C WH	DN570B
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	DN570B
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	DN570B


Order Code	Full Product Name	Product family code
910505100901	DN570B LED40S/TWH PSD-E C WH	DN570B
910505100903	DN570B LED60S/830 PSU-E C WH	DN570B
910505100904	DN570B LED60S/840 PSU-E C WH	DN570B
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	DN570B
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	DN570B
910505102295	DN570B LED24S/830 WIA-E C WH	DN570B
910505102296	DN570B LED24S/840 WIA-E C WH	DN570B
910505102299	DN570B LED40S/830 WIA-E C WH	DN570B
910505102301	DN570B LED40S/840 WIA-E C WH	DN570B
910505102304	DN570B LED24S/930H PSU-E C WH	DN570B
910505102305	DN570B LED24S/940H PSU-E C WH	DN570B
910505102652	DN570B LED20S/840UE PSU-E C WH	DN570B
910505102654	DN570B LED20S/840UE PSU-E WR WH	DN570B
910505102656	DN570B LED24S/840UE PSU-E C WH	DN570B
910505100852	DN570B LED20S/830 PSU-E F WH	DN570B
910505100853	DN570B LED20S/840 PSU-E F WH	DN570B
910505100854	DN570B LED20S/830 PSU-E M WH	DN570B
910505100855	DN570B LED20S/840 PSU-E M WH	DN570B
910505100856	DN570B LED20S/830 PSU-E WR WH	DN570B
910505100857	DN570B LED20S/840 PSU-E WR WH	DN570B
910505100836	DN571B LED12S/830 PSU-E C WH	DN571B
910505100837	DN571B LED12S/840 PSU-E C WH	DN571B
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	DN571B
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	DN571B
910505100846	DN571B LED20S/830 PSU-E C WH	DN571B

Order Code	Full Product Name	Product family code
910505100847	DN571B LED20S/840 PSU-E C WH	DN571B
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	DN571B
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	DN571B
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	DN571B
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	DN571B
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	DN571B
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	DN571B
910505100870	DN571B LED24S/830 PSU-E C WH	DN571B
910505100871	DN571B LED24S/840 PSU-E C WH	DN571B
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	DN571B
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	DN571B
910505100886	DN571B LED40S/830 PSU-E C WH	DN571B
910505100887	DN571B LED40S/840 PSU-E C WH	DN571B
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	DN571B
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	DN571B
910505100902	DN571B LED40S/TWH PSD-E C WH	DN571B
910505102297	DN571B LED24S/830 WIA-E C WH	DN571B
910505102298	DN571B LED24S/840 WIA-E C WH	DN571B
910505102302	DN571B LED40S/830 WIA-E C WH	DN571B
910505102303	DN571B LED40S/840 WIA-E C WH	DN571B
910505102306	DN571B LED24S/930H PSU-E C WH	DN571B
910505102307	DN571B LED24S/940H PSU-E C WH	DN571B
910505102653	DN571B LED20S/840UE PSU-E C WH	DN571B
910505102655	DN571B LED20S/840UE PSU-E WR WH	DN571B
910505102657	DN571B LED24S/840UE PSU-E C WH	DN571B


Polar Wide Diagrams



Polar Normal (separate) - DN570BI - 910505100875




Polar Normal (separate) - DN570BI - 910505102303




Polar Normal (separate) - DN570BI - 910505100838


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505100856




Polar Normal (separate) - DN570BI - 910505100865




Polar Normal (separate) - DN570BI - 910505102299




Polar Normal (separate) - DN570BI - 910505100873




Polar Normal (separate) - DN570BI - 910505100886




Polar Normal (separate) - DN570BI - 910505100845



Polar Normal (separate) - DN570BI - 910505100904




Polar Normal (separate) - DN570BI - 910505100888




Polar Normal (separate) - DN570BI - 910505100868


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505102295




Polar Normal (separate) - DN570BI - 910505102305




Polar Normal (separate) - DN570BI - 910505102298




Polar Normal (separate) - DN570BI - 910505100874




Polar Normal (separate) - DN570BI - 910505100841




Polar Normal (separate) - DN570BI - 910505100853



Polar Normal (separate) - DN570BI - 910505100834




Polar Normal (separate) - DN570BI - 910505102304




Polar Normal (separate) - DN570BI - 910505100848


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505100872




Polar Normal (separate) - DN570BI - 910505100847




Polar Normal (separate) - DN570BI - 910505100867




Polar Normal (separate) - DN570BI - 910505100902




Polar Normal (separate) - DN570BI - 910505100905




Polar Normal (separate) - DN570BI - 910505100863



Polar Normal (separate) - DN570BI - 910505100836




Polar Normal (separate) - DN570BI - 910505102301




Polar Normal (separate) - DN570BI - 910505100885


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505100861




Polar Normal (separate) - DN570BI - 910505100906




Polar Normal (separate) - DN570BI - 910505100835




Polar Normal (separate) - DN570BI - 910505102307




Polar Normal (separate) - DN570BI - 910505100887




Polar Normal (separate) - DN570BI - 910505100871



Polar Normal (separate) - DN570BI - 910505100859




Polar Normal (separate) - DN570BI - 910505100869




Polar Normal (separate) - DN570BI - 910505100843


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505102302




Polar Normal (separate) - DN570BI - 910505100901




Polar Normal (separate) - DN570BI - 910505100846




Polar Normal (separate) - DN570BI - 910505100858




Polar Normal (separate) - DN570BI - 910505100890




Polar Normal (separate) - DN570BI - 910505100870



Polar Normal (separate) - DN570BI - 910505100839




Polar Normal (separate) - DN570BI - 910505100891




Polar Normal (separate) - DN570BI - 910505100852


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505100884




Polar Normal (separate) - DN570BI - 910505102296




Polar Normal (separate) - DN570BI - 910505100857




Polar Normal (separate) - DN570BI - 910505100864




Polar Normal (separate) - DN570BI - 910505100844




Polar Normal (separate) - DN570BI - 910505100866



Polar Normal (separate) - DN570BI - 910505100851




Polar Normal (separate) - DN570BI - 910505100849




Polar Normal (separate) - DN570BI - 910505100903


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505100837




Polar Normal (separate) - DN570BI - 910505100840




Polar Normal (separate) - DN570BI - 910505100842




Polar Normal (separate) - DN570BI - 910505100850




Polar Normal (separate) - DN570BI - 910505100854




Polar Normal (separate) - DN570BI - 910505100855



Polar Normal (separate) - DN570BI - 910505100862




Polar Normal (separate) - DN570BI - 910505100860




Polar Normal (separate) - DN570BI - 910505100889


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505102297




Polar Normal (separate) - DN570BI - 910505102306




Polar Normal (separate) - DN570BI - 910505102656




Polar Normal (separate) - DN570BI - 910505102655




Polar Normal (separate) - DN570BI - 910505102653



Polar Normal (separate) - DN570BI - 910505102657



Polar Normal (separate) - DN570BI - 910505102654



Polar Normal (separate) - DN570BI - 910505102652

