



# The ultimate in retail flexibility and performance

## StyliD Evo

With StyliD Evo, retailers can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a series of flexible and future-proof projectors. StyliD Evo projectors are easy to reconfigure with quick and easy optic upgrades that require no tools. They also support frequent changes in store layouts, as the StyliD Evo projector can be easily repositioned on the track or Maxos fusion backbone. Covering a wide range of lighting applications, from lower light levels in convenience formats to high-ceiling installations where very high light output is required, StyliD offers continuity for every retail concept. StyliD Evo can be mounted on 3C or DALI track (ST770T, ST780T), on Maxos fusion (ST770S, ST780S, ST770X), or into the ceiling with a semi-recessed version (ST770B). All StyliD Evo projectors with PerfectAccent reflectors are certified as a circular lighting product and offer multiple system integration and dimming options, including wired as well as wireless. For prolonged shelf life and better visual representation of food, reducing food waste and increasing sales, fresh food LED lighting recipes are available. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

### Benefits

- Attract shoppers with more sparkle and superior eye comfort
- Easy to reposition and upgrade for frequent store updates
- Best-in class efficacy to reduce carbon footprint and save on energy use
- Certified as circular lighting with PerfectAccent high-efficacy reflectors

# StyliD Evo

## Features

- Easy optic replacement or upgrades that require no tools
- Available with PerfectAccent high-efficacy reflectors
- Optional front glass (advised in dusty environments)
- Up to 6000 lm output for high installation heights
- Available with fresh food LED lighting recipes and LED flavors
- Wired (DALI) and wireless connectivity options
- High intensity oval beam allows increased luminaire spacing when lighting fresh food counters or wordmarks on the wall

## Application

- Convenience stores
- Supermarkets & hypermarkets
- Large Retail formats

## Warnings and Safety

- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth.
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

## Versions



StyliD Evo Compact ST770B white,  
semi recessed



ST771T StyliD Evo Driver-in-track -  
white



StyliD Evo Compact HR for maxos  
fusion

# StyliD Evo

## Versions



StyliD Evo Compact ST770B black,  
semi recessed



StyliD Evo Performance HR



StyliD Evo Performance ST780S  
black, Maxos fusion version



StyliD Evo Compact HR



StyliD Evo Performance ST780T  
silver, track version



StyliD Evo Compact HR



StyliD Evo Performance HR



StyliD Evo Compact ST770T black,  
track version

# StyliD Evo

## Versions



ST771T StyliD Evo Driver-in-track - Silver







StyliD Evo Compact HR for maxos fusion




StyliD Evo Performance HR for maxos fusion








## Dimensional drawing



## Dimensional drawing



	PSU	DIA	W/A
A	160	260	220
B	≤395	>395	
C	190	205	
	124	139	



# StyliD Evo


## Product details



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Compact black, side view



StyliD Evo Compact ST770X  
Mounting interface



StyliD Evo Performance black, side view



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Compact HR



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Compact white, side view

# StyliD Evo

## Product details



StyliD Evo ST770B semi recessed installation rim



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Performance in black, full rotation flexibility



StyliD Evo Compact in white, full rotation flexibility



StyliD Evo Compact white, front view

# StyliD Evo

## Product details



OptiShield protects the optical compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR black



StyliD Evo Performance HR



Aiming indication, with marking for Indoor Positioning operation



StyliD Evo Performance white, side view



StyliD Evo Compact black, front view



StyliD Evo Performance white, front view



# StyliD Evo

## Product details



StyliD Evo Performance black,  
front view



OptiShield protects the optical  
compartment from bugs and dust



StyliD Evo Performance HR



StyliD Evo Compact HR white



StyliD Evo Exploded View



StyliD Evo Compact in black, full  
rotation flexibility



StyliD Evo Performance in white,  
full rotation flexibility

## General Information

Driver included	Yes
Number of gear units	1 unit
Service tag	Yes

## Light Technical

Beam angle of light source	120 degree(s)
----------------------------	---------------

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

## Mechanical and Housing

Optical cover type	-
Mech. impact protection code	IK02
Ingress protection code	IP20

## Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## General Information

Order Code	Full Product Name	Lamp family code	Light source replaceable
910505100730	ST770T LED27S/PW930 PSU HMB SI	-	No
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	-	No
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	LED27S	No
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	LED39S	No
910505101207	ST770B 17S/830 PSU-E MB FG WH	-	No
910505101208	ST770B 20S/830 PSU-E NB FG WH	-	No
910505101212	ST770B 27S/830 PSU-E MB FG WH	-	No
910505101213	ST770B 27S/840 PSU-E VWB FG WH	-	No
910505101214	ST770B 27S/930 PSU-E MB FG WH	-	No
910505101215	ST770B 27S/CH PSU-E MB FG WH	-	No
910505101216	ST770B 27S/FMT PSU-E MB FG WH	-	No
910505101217	ST770B 27S/FR PSU-E MB FG WH	-	No
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	-	No
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	-	No
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	-	No
910505101221	ST770B 39S/827 PSU-E WB FG WH	-	No
910505101223	ST770B 39S/830 PSU-E MB FG WH	-	No
910505101224	ST770B 39S/840 PSU-E VWB FG WH	-	No
910505102730	ST771T 27S/830 PSU WB WH	-	-
910505102733	ST771T 39S/PW930 WIA WB WH	-	-
910505102736	ST771T 39S/PW930 DIA WB WH	-	-
910505101368	ST770S 39S/930 DIA-VLC HWB BK	-	No
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	-	No
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	-	No
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	-	No
910505101410	ST770X 17S/830 DIA MB FG WH	-	No
910505101411	ST770X 20S/830 DIA NB FG WH	-	No
910505101412	ST770X 27S/827 DIA WB FG WH	-	No
910505101413	ST770X 27S/830 DIA MB FG WH	-	No
910505101414	ST770X 27S/840 DIA VWB FG WH	-	No
910505101415	ST770X 27S/930 DIA OVL-H WH	-	No
910505101416	ST770X 27S/CH DIA MB FG WH	-	No
910505101417	ST770X 27S/FMT DIA MB FG WH	-	No
910505101418	ST770X 27S/FR DIA MB FG WH	-	No
910505101421	ST770X 27S/ROSE DIA MB FG WH	-	No
910505101422	ST770X 39S/830 DIA MB FG WH	-	No
910505101423	ST770X 39S/930 DIA OVL-H WH	-	No
910505100749	ST780T LED49S/827 PSU HWB SI FG	-	No
910505100756	ST780T 60S/827 PSU HWB FG SI	-	No
910505101419	ST770X 27S/PC930 DIA MB FG BK	-	No
910505101420	ST770X 27S/PW930 DIA MB FG BK	-	No
910505102731	ST771T 27S/830 PSU WB BK	-	-
910505102734	ST771T 39S/PW930 WIA WB BK	-	-
910505102737	ST771T 39S/PW930 DIA WB BK	-	-
910505101434	ST780T 39S/827 PSU NB FG WH	-	No
910505101435	ST780T 39S/830 PSU NB FG WH	-	No
910505101436	ST780T 39S/840 PSU NB FG WH	-	No
910505101437	ST780T 39S/930 PSU NB FG WH	-	No
910505101438	ST780T 49S/827 PSU WB FG WH	-	No
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	-	No
910505101441	ST780T 49S/830 PSU MB FG WH	-	No

Order Code	Full Product Name	Lamp family code	Light source replaceable
910505101442	ST780T 49S/840 PSU VWB FG WH	-	No
910505101446	ST780T 60S/830 PSU MB FG WH	-	No
910505101447	ST780T 60S/840 PSU MB FG WH	-	No
910505101431	ST780S 60S/827 DIA-VLC HWB BK	-	No
910505101432	ST780S 60S/830 DIA-VLC HMB BK	-	No
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	-	No
910505101386	ST770T 27S/930 PSU MB FG SI	-	No
910505101390	ST770T 27S/PC930 PSU MB FG SI	-	No
910505101392	ST770T 27S/PW930 PSU MB FG SI	-	No
910505100743	ST770T LED49S/830 PSU HMB SI	-	No
910505101443	ST780T 49S/930 PSU MB FG SI	-	No
910505101444	ST780T 49S/PW930 PSU MB FG SI	-	No
910505101445	ST780T 60S/827 PSU WB FG SI	-	No
910505101228	ST770S 17S/827 PSU WB FG WH	-	No
910505101229	ST770S 17S/830 PSU MB FG WH	-	No
910505101230	ST770S 17S/840 PSU VWB FG WH	-	No
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	-	No
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	-	No
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	-	No
910505101371	ST770S 39S/PW930 PSU VWB FG WH	-	No
910505100723	ST770T 20S/830 PSU HNB WH	-	No
910505100724	ST770T 27S/830 PSU HMB WH	-	No
910505100725	ST770T LED27S/827 PSU HWB WH	-	No
910505100736	ST770T 39S/830 PSU HMB WH	-	No
910505100737	ST770T LED39S/827 PSU HWB WH	-	No
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	-	No
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	-	No
910505102315	ST770T 27S/ROSE WIA WB FG WH	-	No
910505102316	ST770T 39S/PW930 WIA WB WH	-	No
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	-	No
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	-	No
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	-	No
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	-	No
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	-	No
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	-	No
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	-	No
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	-	No
910505101425	ST780S 39S/827 PSU NB FG WH	-	No
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	-	No
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	-	No
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	-	No
910505101379	ST770T 20S/830 PSU NB FG WH	-	No
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	-	No
910505101381	ST770T 27S/827 PSU WB FG WH	-	No
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	-	No
910505101384	ST770T 27S/830 PSU MB FG WH	-	No
910505101385	ST770T 27S/840 PSU VWB FG WH	-	No
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	-	No
910505101395	ST770T 39S/827 PSU WB FG WH	-	No
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	-	No
910505101398	ST770T 39S/830 PSU MB FG WH	-	No
910505101399	ST770T 39S/840 PSU MB FG WH	-	No

Order Code	Full Product Name	Lamp family code	Light source replaceable
910505101378	ST770T 17S/930 PSU MB FG BK	-	No
910505101387	ST770T 27S/CH PSU MB FG BK	-	No
910505101388	ST770T 27S/FMT PSU MB FG BK	-	No
910505101389	ST770T 27S/FR PSU MB FG BK	-	No
910505101393	ST770T 27S/ROSE PSU MB FG BK	-	No
910505101401	ST770T 39S/930 PSU MB FG BK	-	No
910505101402	ST770T 39S/PC930 PSU MB FG BK	-	No
910505101403	ST770T 39S/PW930 PSU MB FG BK	-	No
910505100722	ST770T LED17S/930 PSU HMB BK	-	No
910505100731	ST770T LED27S/CH PSU HMB BK FG	-	No
910505100732	ST770T 27S/FR PSU HMB FG BK	-	No
910505100733	ST770T 27S/FMT PSU HMB FG BK	-	No
910505102732	ST771T 27S/830 PSU WB SI	-	-
910505102735	ST771T 39S/PW930 WIA WB SI	-	-
910505102738	ST771T 39S/PW930 DIA WB SI	-	-
910505100747	ST780T 39S/830 PSU HNB WH	-	No
910505100748	ST780T 49S/830 PSU HMB WH	-	No
910505100755	ST780T LED60S/830 PSU HMB WH	-	No
910505100721	ST770S LED17S/830 PSU HMB WH FG	-	No
910505101429	ST780S 49S/930 DIA-VLC HWB WH	-	No
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	-	No

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505100730	ST770T LED27S/PW930 PSU HMB SI	3000 K	>90	137 lm/W	2,600 lm
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	3000 K	>80	133 lm/W	3,900 lm
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	3000 K	>80	121 lm/W	2,700 lm
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	3000 K	>90	124 lm/W	3,850 lm
910505101207	ST770B 17S/830 PSU-E MB FG WH	3000 K	>80	125 lm/W	1,800 lm
910505101208	ST770B 20S/830 PSU-E NB FG WH	3000 K	>80	105 lm/W	2,200 lm
910505101212	ST770B 27S/830 PSU-E MB FG WH	3000 K	>80	121 lm/W	2,850 lm
910505101213	ST770B 27S/840 PSU-E VWB FG WH	4000 K	>80	125 lm/W	2,700 lm
910505101214	ST770B 27S/930 PSU-E MB FG WH	3000 K	>90	122 lm/W	2,800 lm
910505101215	ST770B 27S/CH PSU-E MB FG WH	2700 K	>80	115 lm/W	2,700 lm
910505101216	ST770B 27S/FMT PSU-E MB FG WH	3000 K	>90	74 lm/W	2,600 lm
910505101217	ST770B 27S/FR PSU-E MB FG WH	5000 K	>90	93 lm/W	3,000 lm
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	3000 K	>90	119 lm/W	2,750 lm
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	3000 K	>90	121 lm/W	2,850 lm
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	2200 K	>80	96 lm/W	2,800 lm

# StyliD Evo

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101221	ST770B 39S/827 PSU- E WB FG WH	2700 K	>80	124 lm/W	3,900 lm
910505101223	ST770B 39S/830 PSU- E MB FG WH	3000 K	>80	123 lm/W	3,900 lm
910505101224	ST770B 39S/840 PSU- E VWB FG WH	4000 K	>80	135 lm/W	4,000 lm
910505102730	ST771T 27S/830 PSU WB WH	3000 K	>80	117 lm/W	2,750 lm
910505102733	ST771T 39S/ PW930 WIA WB WH	3000 K	>90	124 lm/W	3,850 lm
910505102736	ST771T 39S/ PW930 DIA WB WH	3000 K	>90	124 lm/W	3,850 lm
910505101368	ST770S 39S/930 DIA- VLC HWB BK	3000 K	>90	133 lm/W	4,000 lm
910505101209	ST770B 27S/827 DIA- VLC-E WB FG BK	2700 K	>80	115 lm/W	2,700 lm
910505101210	ST770B 27S/830 DIA- VLC-E MB FG BK	3000 K	>80	121 lm/W	2,850 lm
910505101211	ST770B 27S/830 DIA- VLC-E OVL-H BK	3000 K	>80	121 lm/W	2,700 lm
910505101410	ST770X 17S/830 DIA MB FG WH	3000 K	>80	125 lm/W	1,800 lm
910505101411	ST770X 20S/830 DIA NB FG WH	3000 K	>80	105 lm/W	2,200 lm
910505101412	ST770X 27S/827 DIA WB FG WH	2700 K	>80	115 lm/W	2,700 lm
910505101413	ST770X 27S/830 DIA MB FG WH	3000 K	>80	121 lm/W	2,850 lm
910505101414	ST770X 27S/840 DIA VWB FG WH	4000 K	>80	125 lm/W	2,700 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101415	ST770X 27S/930 DIA OVL-H WH	3000 K	>90	122 lm/W	2,800 lm
910505101416	ST770X 27S/CH DIA MB FG WH	2700 K	>80	115 lm/W	2,700 lm
910505101417	ST770X 27S/FMT DIA MB FG WH	3000 K	>90	74 lm/W	2,600 lm
910505101418	ST770X 27S/FR DIA MB FG WH	5000 K	>90	93 lm/W	3,000 lm
910505101421	ST770X 27S/ ROSE DIA MB FG WH	2200 K	>80	96 lm/W	2,800 lm
910505101422	ST770X 39S/830 DIA MB FG WH	3000 K	>80	123 lm/W	3,900 lm
910505101423	ST770X 39S/930 DIA OVL-H WH	3000 K	>90	124 lm/W	3,850 lm
910505100749	ST780T LED49S/827 PSU HWB SI FG	2700 K	>80	126 lm/W	4,900 lm
910505100756	ST780T 60S/827 PSU HWB FG SI	2700 K	>80	123 lm/W	6,100 lm
910505101419	ST770X 27S/ PC930 DIA MB FG BK	3000 K	>90	119 lm/W	2,750 lm
910505101420	ST770X 27S/ PW930 DIA MB FG BK	3000 K	>90	121 lm/W	2,850 lm
910505102731	ST771T 27S/830 PSU WB BK	3000 K	>80	117 lm/W	2,750 lm
910505102734	ST771T 39S/ PW930 WIA WB BK	3000 K	>90	124 lm/W	3,850 lm
910505102737	ST771T 39S/ PW930 DIA WB BK	3000 K	>90	124 lm/W	3,850 lm
910505101434	ST780T 39S/827 PSU NB FG WH	2700 K	>80	103 lm/W	3,400 lm
910505101435	ST780T 39S/830 PSU NB FG WH	3000 K	>80	111 lm/W	3,700 lm

# StyliD Evo

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101436	ST780T 39S/840 PSU NB FG WH	4000 K	>80	112 lm/W	3,700 lm
910505101437	ST780T 39S/930 PSU NB FG WH	3000 K	>90	124 lm/W	3,850 lm
910505101438	ST780T 49S/827 PSU WB FG WH	2700 K	>80	122 lm/W	4,700 lm
910505101440	ST780T 49S/830 DIA- VLC OVL-H WH	3000 K	>80	125 lm/W	4,800 lm
910505101441	ST780T 49S/830 PSU MB FG WH	3000 K	>80	125 lm/W	4,800 lm
910505101442	ST780T 49S/840 PSU VWB FG WH	4000 K	>80	132 lm/W	5,100 lm
910505101446	ST780T 60S/830 PSU MB FG WH	3000 K	>80	122 lm/W	6,100 lm
910505101447	ST780T 60S/840 PSU MB FG WH	4000 K	>80	129 lm/W	6,400 lm
910505101431	ST780S 60S/827 DIA- VLC HWB BK	2700 K	>80	123 lm/W	6,100 lm
910505101432	ST780S 60S/830 DIA- VLC HMB BK	3000 K	>80	126 lm/W	6,300 lm
910505101433	ST780S 60S/840 DIA- VLC VWB FG BK	4000 K	>80	129 lm/W	6,400 lm
910505101386	ST770T 27S/930 PSU MB FG SI	3000 K	>90	122 lm/W	2,800 lm
910505101390	ST770T 27S/ PC930 PSU MB FG SI	3000 K	>90	119 lm/W	2,750 lm
910505101392	ST770T 27S/ PW930 PSU MB FG SI	3000 K	>90	121 lm/W	2,850 lm
910505100743	ST770T LED49S/830 PSU HMB SI	3000 K	>80	129 lm/W	5,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101443	ST780T 49S/930 PSU MB FG SI	3000 K	>90	120 lm/W	4,700 lm
910505101444	ST780T 49S/ PW930 PSU MB FG SI	3000 K	>90	120 lm/W	4,700 lm
910505101445	ST780T 60S/827 PSU WB FG SI	2700 K	>80	119 lm/W	5,900 lm
910505101228	ST770S 17S/827 PSU WB FG WH	2700 K	>80	119 lm/W	1,700 lm
910505101229	ST770S 17S/830 PSU MB FG WH	3000 K	>80	125 lm/W	1,800 lm
910505101230	ST770S 17S/840 PSU VWB FG WH	4000 K	>80	131 lm/W	1,900 lm
910505101231	ST770S 27S/827 DIA- VLC WB FG WH	2700 K	>80	115 lm/W	2,700 lm
910505101232	ST770S 27S/830 DIA- VLC MB FG WH	3000 K	>80	121 lm/W	2,850 lm
910505101364	ST770S 27S/840 DIA- VLC VWB FG WH	4000 K	>80	125 lm/W	2,700 lm
910505101371	ST770S 39S/ PW930 PSU VWB FG WH	3000 K	>90	124 lm/W	3,850 lm
910505100723	ST770T 20S/830 PSU HNB WH	3000 K	>80	108 lm/W	2,250 lm
910505100724	ST770T 27S/830 PSU HMB WH	3000 K	>80	138 lm/W	2,600 lm
910505100725	ST770T LED27S/827 PSU HWB WH	2700 K	>80	138 lm/W	2,700 lm
910505100736	ST770T 39S/830 PSU HMB WH	3000 K	>80	133 lm/W	3,900 lm
910505100737	ST770T LED39S/827 PSU HWB WH	2700 K	>80	129 lm/W	3,800 lm
910505101382	ST770T 27S/830 DIA-	3000 K	>80	138 lm/W	2,650 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	VLC HOVL-H WH				
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	3000 K	>90	137 lm/W	2,600 lm
910505102315	ST770T 27S/ROSE WIA WB FG WH	2200 K	>80	96 lm/W	2,800 lm
910505102316	ST770T 39S/PW930 WIA WB WH	3000 K	>90	124 lm/W	3,850 lm
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	2700 K	>80	124 lm/W	3,900 lm
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	3000 K	>80	123 lm/W	3,900 lm
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	4000 K	>80	135 lm/W	4,000 lm
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	3000 K	>80	129 lm/W	5,000 lm
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	3000 K	>80	129 lm/W	5,000 lm
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	3000 K	>90	124 lm/W	4,000 lm
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	3000 K	>90	133 lm/W	4,000 lm
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	3000 K	>90	126 lm/W	4,900 lm
910505101425	ST780S 39S/827 PSU NB FG WH	2700 K	>80	103 lm/W	3,400 lm
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	2700 K	>80	122 lm/W	4,700 lm
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	3000 K	>80	125 lm/W	4,800 lm
910505101428	ST780S 49S/840 DIA-	4000 K	>80	132 lm/W	5,100 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	VLC VWB FG WH				
910505101379	ST770T 20S/830 PSU NB FG WH	3000 K	>80	105 lm/W	2,200 lm
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	2700 K	>80	115 lm/W	2,700 lm
910505101381	ST770T 27S/827 PSU WB FG WH	2700 K	>80	115 lm/W	2,700 lm
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	3000 K	>80	121 lm/W	2,700 lm
910505101384	ST770T 27S/830 PSU MB FG WH	3000 K	>80	121 lm/W	2,850 lm
910505101385	ST770T 27S/840 PSU VWB FG WH	4000 K	>80	125 lm/W	2,700 lm
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	2700 K	>80	124 lm/W	3,900 lm
910505101395	ST770T 39S/827 PSU WB FG WH	2700 K	>80	124 lm/W	3,900 lm
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	3000 K	>80	123 lm/W	3,900 lm
910505101398	ST770T 39S/830 PSU MB FG WH	3000 K	>80	123 lm/W	3,900 lm
910505101399	ST770T 39S/840 PSU MB FG WH	4000 K	>80	135 lm/W	4,000 lm
910505101378	ST770T 17S/930 PSU MB FG BK	3000 K	>90	124 lm/W	1,750 lm
910505101387	ST770T 27S/CH PSU MB FG BK	2700 K	>80	115 lm/W	2,700 lm
910505101388	ST770T 27S/FMT PSU MB FG BK	3000 K	>90	74 lm/W	2,600 lm
910505101389	ST770T 27S/FR PSU MB FG BK	5000 K	>90	93 lm/W	3,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101393	ST770T 27S/ROSE PSU MB FG BK	2200 K	>80	96 lm/W	2,800 lm
910505101401	ST770T 39S/930 PSU MB FG BK	3000 K	>90	124 lm/W	3,850 lm
910505101402	ST770T 39S/PC930 PSU MB FG BK	3000 K	>90	116 lm/W	4,100 lm
910505101403	ST770T 39S/PW930 PSU MB FG BK	3000 K	>90	124 lm/W	3,850 lm
910505100722	ST770T LED17S/930 PSU HMB BK	3000 K	>90	128 lm/W	1,800 lm
910505100731	ST770T LED27S/CH PSU HMB BK FG	2700 K	>80	132 lm/W	2,500 lm
910505100732	ST770T 27S/FR PSU HMB FG BK	5000 K	>90	98 lm/W	2,700 lm
910505100733	ST770T 27S/FMT PSU HMB FG BK	3000 K	>90	81 lm/W	2,600 lm
910505102732	ST771T 27S/830 PSU WB SI	3000 K	>80	117 lm/W	2,750 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102735	ST771T 39S/PW930 WIA WB SI	3000 K	>90	124 lm/W	3,850 lm
910505102738	ST771T 39S/PW930 DIA WB SI	3000 K	>90	124 lm/W	3,850 lm
910505100747	ST780T 39S/830 PSU HNB WH	3000 K	>80	118 lm/W	3,900 lm
910505100748	ST780T 49S/830 PSU HMB WH	3000 K	>80	129 lm/W	5,000 lm
910505100755	ST780T LED60S/830 PSU HMB WH	3000 K	>80	126 lm/W	6,300 lm
910505100721	ST770S LED17S/830 PSU HMB WH FG	3000 K	>80	129 lm/W	1,850 lm
910505101429	ST780S 49S/930 DIA-VLC HWB WH	3000 K	>90	125 lm/W	4,900 lm
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	3000 K	>90	125 lm/W	4,900 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Optic type
910505100730	ST770T LED27S/PW930 PSU HMB SI	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101396	ST770T 39S/830 DIA-VLC HOVL- H SI	-	High-reflective metal reflector Oval - Horizontal beam
910500465998	ST770B LED27S/830 PSU-E OVL- H WH	1	Oval horizontal beam
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	1	Oval horizontal beam
910505101207	ST770B 17S/830 PSU-E MB FG WH	-	Medium beam
910505101208	ST770B 20S/830 PSU-E NB FG WH	-	Narrow beam

Order Code	Full Product Name	Number of light sources	Optic type
910505101212	ST770B 27S/830 PSU-E MB FG WH	-	Medium beam
910505101213	ST770B 27S/840 PSU-E VWB FG WH	-	Very wide beam
910505101214	ST770B 27S/930 PSU-E MB FG WH	-	Medium beam
910505101215	ST770B 27S/CH PSU-E MB FG WH	-	Medium beam
910505101216	ST770B 27S/FMT PSU-E MB FG WH	-	Medium beam
910505101217	ST770B 27S/FR PSU-E MB FG WH	-	Medium beam
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	-	Medium beam



Order Code	Full Product Name	Number of light	
		sources	Optic type
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	-	Medium beam
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	-	Medium beam
910505101221	ST770B 39S/827 PSU-E WB FG WH	-	Wide beam
910505101223	ST770B 39S/830 PSU-E MB FG WH	-	Medium beam
910505101224	ST770B 39S/840 PSU-E VWB FG WH	-	Very wide beam
910505102730	ST77IT 27S/830 PSU WB WH	-	Wide beam
910505102733	ST77IT 39S/PW930 WIA WB WH	-	Wide beam
910505102736	ST77IT 39S/PW930 DIA WB WH	-	Wide beam
910505101368	ST770S 39S/930 DIA-VLC HWB BK	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	-	Wide beam
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	-	Medium beam
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	-	Oval horizontal beam
910505101410	ST770X 17S/830 DIA MB FG WH	-	Medium beam
910505101411	ST770X 20S/830 DIA NB FG WH	-	Narrow beam
910505101412	ST770X 27S/827 DIA WB FG WH	-	Wide beam
910505101413	ST770X 27S/830 DIA MB FG WH	-	Medium beam
910505101414	ST770X 27S/840 DIA VWB FG WH	-	Very wide beam
910505101415	ST770X 27S/930 DIA OVL-H WH	-	Oval horizontal beam
910505101416	ST770X 27S/CH DIA MB FG WH	-	Medium beam
910505101417	ST770X 27S/FMT DIA MB FG WH	-	Medium beam
910505101418	ST770X 27S/FR DIA MB FG WH	-	Medium beam
910505101421	ST770X 27S/ROSE DIA MB FG WH	-	Medium beam
910505101422	ST770X 39S/830 DIA MB FG WH	-	Medium beam
910505101423	ST770X 39S/930 DIA OVL-H WH	-	Oval horizontal beam
910505100749	ST780T LED49S/827 PSU HWB SI FG	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505100756	ST780T 60S/827 PSU HWB FG SI	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101419	ST770X 27S/PC930 DIA MB FG BK	-	Medium beam
910505101420	ST770X 27S/PW930 DIA MB FG BK	-	Medium beam
910505102731	ST77IT 27S/830 PSU WB BK	-	Wide beam
910505102734	ST77IT 39S/PW930 WIA WB BK	-	Wide beam
910505102737	ST77IT 39S/PW930 DIA WB BK	-	Wide beam
910505101434	ST780T 39S/827 PSU NB FG WH	-	Narrow beam
910505101435	ST780T 39S/830 PSU NB FG WH	-	Narrow beam

Order Code	Full Product Name	Number of light	
		sources	Optic type
910505101436	ST780T 39S/840 PSU NB FG WH	-	Narrow beam
910505101437	ST780T 39S/930 PSU NB FG WH	-	Narrow beam
910505101438	ST780T 49S/827 PSU WB FG WH	-	Wide beam
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	-	Oval horizontal beam
910505101441	ST780T 49S/830 PSU MB FG WH	-	Medium beam
910505101442	ST780T 49S/840 PSU VWB FG WH	-	Very wide beam
910505101446	ST780T 60S/830 PSU MB FG WH	-	Medium beam
910505101447	ST780T 60S/840 PSU MB FG WH	-	Medium beam
910505101431	ST780S 60S/827 DIA-VLC HWB BK	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101432	ST780S 60S/830 DIA-VLC HMB BK	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	-	Very wide beam
910505101386	ST770T 27S/930 PSU MB FG SI	-	Medium beam
910505101390	ST770T 27S/PC930 PSU MB FG SI	-	Medium beam
910505101392	ST770T 27S/PW930 PSU MB FG SI	-	Medium beam
910505100743	ST770T LED49S/830 PSU HMB SI	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101443	ST780T 49S/930 PSU MB FG SI	-	Medium beam
910505101444	ST780T 49S/PW930 PSU MB FG SI	-	Medium beam
910505101445	ST780T 60S/827 PSU WB FG SI	-	Wide beam
910505101228	ST770S 17S/827 PSU WB FG WH	-	Wide beam
910505101229	ST770S 17S/830 PSU MB FG WH	-	Medium beam
910505101230	ST770S 17S/840 PSU VWB FG WH	-	Very wide beam
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	-	Wide beam
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	-	Medium beam
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	-	Very wide beam
910505101371	ST770S 39S/PW930 PSU VWB FG WH	-	Very wide beam
910505100723	ST770T 20S/830 PSU HNB WH	-	High-reflective metal reflector Narrow beam 10 to 20 degrees
910505100724	ST770T 27S/830 PSU HMB WH	-	High-reflective metal reflector Medium

Order Code	Full Product Name	Number of light	
		sources	Optic type
			beam 20 to 40 degrees
910505100725	ST770T LED27S/827 PSU HWB WH	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505100736	ST770T 39S/830 PSU HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100737	ST770T LED39S/827 PSU HWB WH	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	-	High-reflective metal reflector Oval - Horizontal beam
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505102315	ST770T 27S/ROSE WIA WB FG WH	-	Wide beam
910505102316	ST770T 39S/PW930 WIA WB WH	-	Wide beam
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	-	Wide beam
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	-	Medium beam
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	-	Very wide beam
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	-	High-reflective metal reflector Oval - Vertical beam
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	-	High-reflective metal reflector Oval - Horizontal beam
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	-	High-reflective metal reflector very wide beam >80 degrees
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	-	High-reflective metal reflector very wide beam >80 degrees
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505101425	ST780S 39S/827 PSU NB FG WH	-	Narrow beam
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	-	Wide beam
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	-	Medium beam

Order Code	Full Product Name	Number of light	
		sources	Optic type
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	-	Very wide beam
910505101379	ST770T 20S/830 PSU NB FG WH	-	Narrow beam
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	-	Oval vertical beam
910505101381	ST770T 27S/827 PSU WB FG WH	-	Wide beam
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	-	Oval horizontal beam
910505101384	ST770T 27S/830 PSU MB FG WH	-	Medium beam
910505101385	ST770T 27S/840 PSU VWB FG WH	-	Very wide beam
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	-	Oval vertical beam
910505101395	ST770T 39S/827 PSU WB FG WH	-	Wide beam
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	-	Oval horizontal beam
910505101398	ST770T 39S/830 PSU MB FG WH	-	Medium beam
910505101399	ST770T 39S/840 PSU MB FG WH	-	Medium beam
910505101378	ST770T 17S/930 PSU MB FG BK	-	Medium beam
910505101387	ST770T 27S/CH PSU MB FG BK	-	Medium beam
910505101388	ST770T 27S/FMT PSU MB FG BK	-	Medium beam
910505101389	ST770T 27S/FR PSU MB FG BK	-	Medium beam
910505101393	ST770T 27S/ROSE PSU MB FG BK	-	Medium beam
910505101401	ST770T 39S/930 PSU MB FG BK	-	Medium beam
910505101402	ST770T 39S/PC930 PSU MB FG BK	-	Medium beam
910505101403	ST770T 39S/PW930 PSU MB FG BK	-	Medium beam
910505100722	ST770T LED17S/930 PSU HMB BK	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100731	ST770T LED27S/CH PSU HMB BK FG	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100732	ST770T 27S/FR PSU HMB FG BK	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100733	ST770T 27S/FMT PSU HMB FG BK	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505102732	ST771T 27S/830 PSU WB SI	-	Wide beam
910505102735	ST771T 39S/PW930 WIA WB SI	-	Wide beam
910505102738	ST771T 39S/PW930 DIA WB SI	-	Wide beam
910505100747	ST780T 39S/830 PSU HNB WH	-	High-reflective metal reflector Narrow beam 10 to 20 degrees

Order Code	Full Product Name	Number of light	
		sources	Optic type
910505100748	ST780T 49S/830 PSU HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100755	ST780T LED60S/830 PSU HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees
910505100721	ST770S LED17S/830 PSU HMB WH FG	-	High-reflective metal reflector Medium beam 20 to 40 degrees

Order Code	Full Product Name	Number of light	
		sources	Optic type
910505101429	ST780S 49S/930 DIA-VLC HWB WH	-	High-reflective metal reflector Wide beam 40 to 80 degrees
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	-	High-reflective metal reflector Medium beam 20 to 40 degrees

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for
				random switching
910505100730	ST770T LED27S/PW930 PSU HMB SI	Safety class II	18.8 W	No
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	Safety class II	29.5 W	No
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	Safety class II	23.5 W	No
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	Safety class II	31 W	No
910505101207	ST770B 17S/830 PSU-E MB FG WH	Safety class II	14.4 W	No
910505101208	ST770B 20S/830 PSU-E NB FG WH	Safety class II	20.5 W	No
910505101212	ST770B 27S/830 PSU-E MB FG WH	Safety class II	23.5 W	No
910505101213	ST770B 27S/840 PSU-E VWB FG WH	Safety class II	23.5 W	No
910505101214	ST770B 27S/930 PSU-E MB FG WH	Safety class II	23 W	No
910505101215	ST770B 27S/CH PSU-E MB FG WH	Safety class II	23.5 W	No
910505101216	ST770B 27S/FMT PSU-E MB FG WH	Safety class II	35 W	No
910505101217	ST770B 27S/FR PSU-E MB FG WH	Safety class II	32.5 W	No
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	Safety class II	23 W	No
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	Safety class II	23.5 W	No
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	Safety class II	29 W	No
910505101221	ST770B 39S/827 PSU-E WB FG WH	Safety class II	31.5 W	No

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for
				random switching
910505101223	ST770B 39S/830 PSU-E MB FG WH	Safety class II	31.5 W	No
910505101224	ST770B 39S/840 PSU-E VWB FG WH	Safety class II	29.5 W	No
910505102730	ST771T 27S/830 PSU WB WH	Safety class II	23.5 W	Not applicable
910505102733	ST771T 39S/PW930 WIA WB WH	Safety class II	31 W	Not applicable
910505102736	ST771T 39S/PW930 DIA WB WH	Safety class II	31 W	Not applicable
910505101368	ST770S 39S/930 DIA-VLC HWB BK	Safety class II	30 W	No
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	Safety class II	23.5 W	No
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	Safety class II	23.5 W	No
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	Safety class II	23.5 W	No
910505101410	ST770X 17S/830 DIA MB FG WH	Safety class I	14.4 W	No
910505101411	ST770X 20S/830 DIA NB FG WH	Safety class I	20.5 W	No
910505101412	ST770X 27S/827 DIA WB FG WH	Safety class I	23.5 W	No
910505101413	ST770X 27S/830 DIA MB FG WH	Safety class I	23.5 W	No
910505101414	ST770X 27S/840 DIA VWB FG WH	Safety class I	23.5 W	No
910505101415	ST770X 27S/930 DIA OVL-H WH	Safety class I	23 W	No

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910505101416	ST770X 27S/CH DIA MB FG WH	Safety class I	23.5 W	No
910505101417	ST770X 27S/FMT DIA MB FG WH	Safety class I	35 W	No
910505101418	ST770X 27S/FR DIA MB FG WH	Safety class I	32.5 W	No
910505101421	ST770X 27S/ROSE DIA MB FG WH	Safety class I	29 W	No
910505101422	ST770X 39S/830 DIA MB FG WH	Safety class I	31.5 W	No
910505101423	ST770X 39S/930 DIA OVL-H WH	Safety class I	31 W	No
910505100749	ST780T LED49S/827 PSU HWB SI FG	Safety class II	38.5 W	No
910505100756	ST780T 60S/827 PSU HWB FG SI	Safety class II	50 W	No
910505101419	ST770X 27S/PC930 DIA MB FG BK	Safety class I	23 W	No
910505101420	ST770X 27S/PW930 DIA MB FG BK	Safety class I	23.5 W	No
910505102731	ST77IT 27S/830 PSU WB BK	Safety class II	23.5 W	Not applicable
910505102734	ST77IT 39S/PW930 WIA WB BK	Safety class II	31 W	Not applicable
910505102737	ST77IT 39S/PW930 DIA WB BK	Safety class II	31 W	Not applicable
910505101434	ST780T 39S/827 PSU NB FG WH	Safety class II	33 W	No
910505101435	ST780T 39S/830 PSU NB FG WH	Safety class II	33 W	No
910505101436	ST780T 39S/840 PSU NB FG WH	Safety class II	33 W	No
910505101437	ST780T 39S/930 PSU NB FG WH	Safety class II	31 W	No
910505101438	ST780T 49S/827 PSU WB FG WH	Safety class II	38.5 W	No
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	Safety class II	38.5 W	No
910505101441	ST780T 49S/830 PSU MB FG WH	Safety class II	38.5 W	No
910505101442	ST780T 49S/840 PSU VWB FG WH	Safety class II	38.5 W	No
910505101446	ST780T 60S/830 PSU MB FG WH	Safety class II	50 W	No
910505101447	ST780T 60S/840 PSU MB FG WH	Safety class II	50 W	No
910505101431	ST780S 60S/827 DIA-VLC HWB BK	Safety class II	50 W	No
910505101432	ST780S 60S/830 DIA-VLC HMB BK	Safety class II	50 W	No

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	Safety class II	50 W	No
910505101386	ST770T 27S/930 PSU MB FG SI	Safety class II	23 W	No
910505101390	ST770T 27S/PC930 PSU MB FG SI	Safety class II	23 W	No
910505101392	ST770T 27S/PW930 PSU MB FG SI	Safety class II	23.5 W	No
910505100743	ST770T LED49S/830 PSU HMB SI	Safety class II	38.5 W	No
910505101443	ST780T 49S/930 PSU MB FG SI	Safety class II	39 W	No
910505101444	ST780T 49S/PW930 PSU MB FG SI	Safety class II	39 W	No
910505101445	ST780T 60S/827 PSU WB FG SI	Safety class II	50 W	No
910505101228	ST770S 17S/827 PSU WB FG WH	Safety class II	14.4 W	No
910505101229	ST770S 17S/830 PSU MB FG WH	Safety class II	14.4 W	No
910505101230	ST770S 17S/840 PSU VWB FG WH	Safety class II	14.4 W	No
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	Safety class II	23.5 W	No
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	Safety class II	23.5 W	No
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	Safety class II	23.5 W	No
910505101371	ST770S 39S/PW930 PSU VWB FG WH	Safety class II	31 W	No
910505100723	ST770T 20S/830 PSU HNB WH	Safety class II	20.5 W	No
910505100724	ST770T 27S/830 PSU HMB WH	Safety class II	19 W	No
910505100725	ST770T LED27S/827 PSU HWB WH	Safety class II	19 W	No
910505100736	ST770T 39S/830 PSU HMB WH	Safety class II	29.5 W	No
910505100737	ST770T LED39S/827 PSU HWB WH	Safety class II	29.5 W	No
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	Safety class II	19 W	No
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	Safety class II	18.8 W	No
910505102315	ST770T 27S/ROSE WIA WB FG WH	Safety class II	29 W	No
910505102316	ST770T 39S/PW930 WIA WB WH	Safety class II	31 W	No
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	Safety class II	31.5 W	No

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	Safety class II	31.5 W	No
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	Safety class II	29.5 W	No
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	Safety class II	38.5 W	No
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	Safety class II	38.5 W	No
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	Safety class II	32 W	No
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	Safety class II	30 W	No
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	Safety class II	39 W	No
910505101425	ST780S 39S/827 PSU NB FG WH	Safety class II	33 W	No
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	Safety class II	38.5 W	No
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	Safety class II	38.5 W	No
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	Safety class II	38.5 W	No
910505101379	ST770T 20S/830 PSU NB FG WH	Safety class II	20.5 W	No
910505101380	ST770T 27S/827 DIA- VLC OVL-V WH	Safety class II	23.5 W	No
910505101381	ST770T 27S/827 PSU WB FG WH	Safety class II	23.5 W	No
910505101383	ST770T 27S/830 DIA- VLC OVL-H WH	Safety class II	23.5 W	No
910505101384	ST770T 27S/830 PSU MB FG WH	Safety class II	23.5 W	No
910505101385	ST770T 27S/840 PSU VWB FG WH	Safety class II	23.5 W	No
910505101394	ST770T 39S/827 DIA- VLC OVL-V WH	Safety class II	31.5 W	No
910505101395	ST770T 39S/827 PSU WB FG WH	Safety class II	31.5 W	No
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	Safety class II	31.5 W	No
910505101398	ST770T 39S/830 PSU MB FG WH	Safety class II	31.5 W	No
910505101399	ST770T 39S/840 PSU MB FG WH	Safety class II	29.5 W	No

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910505101378	ST770T 17S/930 PSU MB FG BK	Safety class II	14 W	No
910505101387	ST770T 27S/CH PSU MB FG BK	Safety class II	23.5 W	No
910505101388	ST770T 27S/FMT PSU MB FG BK	Safety class II	35 W	No
910505101389	ST770T 27S/FR PSU MB FG BK	Safety class II	32.5 W	No
910505101393	ST770T 27S/ROSE PSU MB FG BK	Safety class II	29 W	No
910505101401	ST770T 39S/930 PSU MB FG BK	Safety class II	31 W	No
910505101402	ST770T 39S/PC930 PSU MB FG BK	Safety class II	35 W	No
910505101403	ST770T 39S/PW930 PSU MB FG BK	Safety class II	31 W	No
910505100722	ST770T LED17S/930 PSU HMB BK	Safety class II	14 W	No
910505100731	ST770T LED27S/CH PSU HMB BK FG	Safety class II	19 W	No
910505100732	ST770T 27S/FR PSU HMB FG BK	Safety class II	28.5 W	No
910505100733	ST770T 27S/FMT PSU HMB FG BK	Safety class II	31.5 W	No
910505102732	ST771T 27S/830 PSU WB SI	Safety class II	23.5 W	Not applicable
910505102735	ST771T 39S/PW930 WIA WB SI	Safety class II	31 W	Not applicable
910505102738	ST771T 39S/PW930 DIA WB SI	Safety class II	31 W	Not applicable
910505100747	ST780T 39S/830 PSU HNB WH	Safety class II	33 W	No
910505100748	ST780T 49S/830 PSU HMB WH	Safety class II	38.5 W	No
910505100755	ST780T LED60S/830 PSU HMB WH	Safety class II	50 W	No
910505100721	ST770S LED17S/830 PSU HMB WH FG	Safety class II	14.4 W	No
910505101429	ST780S 49S/930 DIA-VLC HWB WH	Safety class II	39 W	No
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	Safety class II	39 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100730	ST770T LED27S/PW930 PSU HMB SI	No	-	Not applicable
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	Yes	Visible light communication	1%
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	No	-	-
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	No	-	-
910505101207	ST770B 17S/830 PSU-E MB FG WH	No	-	Not applicable
910505101208	ST770B 20S/830 PSU-E NB FG WH	No	-	Not applicable
910505101212	ST770B 27S/830 PSU-E MB FG WH	No	-	Not applicable
910505101213	ST770B 27S/840 PSU-E VWB FG WH	No	-	Not applicable
910505101214	ST770B 27S/930 PSU-E MB FG WH	No	-	Not applicable
910505101215	ST770B 27S/CH PSU-E MB FG WH	No	-	Not applicable
910505101216	ST770B 27S/FMT PSU-E MB FG WH	No	-	Not applicable
910505101217	ST770B 27S/FR PSU-E MB FG WH	No	-	Not applicable
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	No	-	Not applicable
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	No	-	Not applicable
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	No	-	Not applicable
910505101221	ST770B 39S/827 PSU-E WB FG WH	No	-	Not applicable
910505101223	ST770B 39S/830 PSU-E MB FG WH	No	-	Not applicable
910505101224	ST770B 39S/840 PSU-E VWB FG WH	No	-	Not applicable
910505102730	ST771T 27S/830 PSU WB WH	No	-	-
910505102733	ST771T 39S/PW930 WIA WB WH	Yes	-	-
910505102736	ST771T 39S/PW930 DIA WB WH	Yes	-	-
910505101368	ST770S 39S/930 DIA-VLC HWB BK	Yes	-	1%
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	Yes	Visible light communication	1%
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	Yes	Visible light communication	1%
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	Yes	Visible light communication	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101410	ST770X 17S/830 DIA MB FG WH	Yes	-	1%
910505101411	ST770X 20S/830 DIA NB FG WH	Yes	-	1%
910505101412	ST770X 27S/827 DIA WB FG WH	Yes	-	1%
910505101413	ST770X 27S/830 DIA MB FG WH	Yes	-	1%
910505101414	ST770X 27S/840 DIA VWB FG WH	Yes	-	1%
910505101415	ST770X 27S/930 DIA OVL-H WH	Yes	-	1%
910505101416	ST770X 27S/CH DIA MB FG WH	Yes	-	1%
910505101417	ST770X 27S/FMT DIA MB FG WH	Yes	-	1%
910505101418	ST770X 27S/FR DIA MB FG WH	Yes	-	1%
910505101421	ST770X 27S/ROSE DIA MB FG WH	Yes	-	1%
910505101422	ST770X 39S/830 DIA MB FG WH	Yes	-	1%
910505101423	ST770X 39S/930 DIA OVL-H WH	Yes	-	1%
910505100749	ST780T LED49S/827 PSU HWB SI FG	No	-	Not applicable
910505100756	ST780T 60S/827 PSU HWB FG SI	No	-	Not applicable
910505101419	ST770X 27S/PC930 DIA MB FG BK	Yes	-	1%
910505101420	ST770X 27S/PW930 DIA MB FG BK	Yes	-	1%
910505102731	ST771T 27S/830 PSU WB BK	No	-	-
910505102734	ST771T 39S/PW930 WIA WB BK	Yes	-	-
910505102737	ST771T 39S/PW930 DIA WB BK	Yes	-	-
910505101434	ST780T 39S/827 PSU NB FG WH	No	-	Not applicable
910505101435	ST780T 39S/830 PSU NB FG WH	No	-	Not applicable
910505101436	ST780T 39S/840 PSU NB FG WH	No	-	Not applicable
910505101437	ST780T 39S/930 PSU NB FG WH	No	-	Not applicable
910505101438	ST780T 49S/827 PSU WB FG WH	No	-	Not applicable
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	Yes	Visible light communication	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101441	ST780T 49S/830 PSU MB FG WH	No	-	Not applicable
910505101442	ST780T 49S/840 PSU VWB FG WH	No	-	Not applicable
910505101446	ST780T 60S/830 PSU MB FG WH	No	-	Not applicable
910505101447	ST780T 60S/840 PSU MB FG WH	No	-	Not applicable
910505101431	ST780S 60S/827 DIA-VLC HWB BK	Yes	Visible light communication	1%
910505101432	ST780S 60S/830 DIA-VLC HMB BK	Yes	Visible light communication	1%
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	Yes	Visible light communication	1%
910505101386	ST770T 27S/930 PSU MB FG SI	No	-	Not applicable
910505101390	ST770T 27S/PC930 PSU MB FG SI	No	-	Not applicable
910505101392	ST770T 27S/PW930 PSU MB FG SI	No	-	Not applicable
910505100743	ST770T LED49S/830 PSU HMB SI	No	-	Not applicable
910505101443	ST780T 49S/930 PSU MB FG SI	No	-	Not applicable
910505101444	ST780T 49S/PW930 PSU MB FG SI	No	-	Not applicable
910505101445	ST780T 60S/827 PSU WB FG SI	No	-	Not applicable
910505101228	ST770S 17S/827 PSU WB FG WH	No	-	Not applicable
910505101229	ST770S 17S/830 PSU MB FG WH	No	-	Not applicable
910505101230	ST770S 17S/840 PSU VWB FG WH	No	-	Not applicable
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	Yes	Visible light communication	1%
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	Yes	-	1%
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	Yes	Visible light communication	1%
910505101371	ST770S 39S/PW930 PSU VWB FG WH	No	-	Not applicable
910505100723	ST770T 20S/830 PSU HNB WH	No	-	Not applicable
910505100724	ST770T 27S/830 PSU HMB WH	No	-	Not applicable
910505100725	ST770T LED27S/827 PSU HWB WH	No	-	Not applicable
910505100736	ST770T 39S/830 PSU HMB WH	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100737	ST770T LED39S/827 PSU HWB WH	No	-	Not applicable
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	Yes	Visible light communication	1%
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	Yes	-	1%
910505102315	ST770T 27S/ROSE WIA WB FG WH	Yes	-	Not applicable
910505102316	ST770T 39S/PW930 WIA WB WH	Yes	-	Not applicable
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	Yes	Visible light communication	1%
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	Yes	Visible light communication	1%
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	Yes	-	1%
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	Yes	-	1%
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	Yes	Visible light communication	1%
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	Yes	-	1%
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	Yes	Visible light communication	1%
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	Yes	-	1%
910505101425	ST780S 39S/827 PSU NB FG WH	No	-	Not applicable
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	Yes	Visible light communication	1%
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	Yes	Visible light communication	1%
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	Yes	Visible light communication	1%
910505101379	ST770T 20S/830 PSU NB FG WH	No	-	Not applicable
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	Yes	-	1%
910505101381	ST770T 27S/827 PSU WB FG WH	No	-	Not applicable
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	Yes	-	1%
910505101384	ST770T 27S/830 PSU MB FG WH	No	-	Not applicable
910505101385	ST770T 27S/840 PSU VWB FG WH	No	-	Not applicable
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	Yes	-	1%
910505101395	ST770T 39S/827 PSU WB FG WH	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	Yes	-	1%
910505101398	ST770T 39S/830 PSU MB FG WH	No	-	Not applicable
910505101399	ST770T 39S/840 PSU MB FG WH	No	-	Not applicable
910505101378	ST770T 17S/930 PSU MB FG BK	No	-	Not applicable
910505101387	ST770T 27S/CH PSU MB FG BK	No	-	Not applicable
910505101388	ST770T 27S/FMT PSU MB FG BK	No	-	Not applicable
910505101389	ST770T 27S/FR PSU MB FG BK	No	-	Not applicable
910505101393	ST770T 27S/ROSE PSU MB FG BK	No	-	Not applicable
910505101401	ST770T 39S/930 PSU MB FG BK	No	-	Not applicable
910505101402	ST770T 39S/PC930 PSU MB FG BK	No	-	Not applicable
910505101403	ST770T 39S/PW930 PSU MB FG BK	No	-	Not applicable
910505100722	ST770T LED17S/930 PSU HMB BK	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910505100731	ST770T LED27S/CH PSU HMB BK FG	No	-	Not applicable
910505100732	ST770T 27S/FR PSU HMB FG BK	No	-	Not applicable
910505100733	ST770T 27S/FMT PSU HMB FG BK	No	-	Not applicable
910505102732	ST771T 27S/830 PSU WB SI	No	-	-
910505102735	ST771T 39S/PW930 WIA WB SI	Yes	-	-
910505102738	ST771T 39S/PW930 DIA WB SI	Yes	-	-
910505100747	ST780T 39S/830 PSU HNB WH	No	-	Not applicable
910505100748	ST780T 49S/830 PSU HMB WH	No	-	Not applicable
910505100755	ST780T LED60S/830 PSU HMB WH	No	-	Not applicable
910505100721	ST770S LED17S/830 PSU HMB WH FG	No	-	Not applicable
910505101429	ST780S 49S/930 DIA-VLC HWB WH	Yes	Visible light communication	1%
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	Yes	Visible light communication	1%

**Mechanical and Housing**

Order Code	Full Product Name	Housing Color
910505100730	ST770T LED27S/PW930 PSU HMB SI	Silver
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	Silver
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	White
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	White
910505101207	ST770B 17S/830 PSU-E MB FG WH	White
910505101208	ST770B 20S/830 PSU-E NB FG WH	White
910505101212	ST770B 27S/830 PSU-E MB FG WH	White
910505101213	ST770B 27S/840 PSU-E VWB FG WH	White
910505101214	ST770B 27S/930 PSU-E MB FG WH	White
910505101215	ST770B 27S/CH PSU-E MB FG WH	White
910505101216	ST770B 27S/FMT PSU-E MB FG WH	White
910505101217	ST770B 27S/FR PSU-E MB FG WH	White
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	White
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	White
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	White
910505101221	ST770B 39S/827 PSU-E WB FG WH	White
910505101223	ST770B 39S/830 PSU-E MB FG WH	White
910505101224	ST770B 39S/840 PSU-E VWB FG WH	White
910505102730	ST771T 27S/830 PSU WB WH	White
910505102733	ST771T 39S/PW930 WIA WB WH	White
910505102736	ST771T 39S/PW930 DIA WB WH	White
910505101368	ST770S 39S/930 DIA-VLC HWB BK	Black
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	Black

Order Code	Full Product Name	Housing Color
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	Black
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	Black
910505101410	ST770X 17S/830 DIA MB FG WH	White
910505101411	ST770X 20S/830 DIA NB FG WH	White
910505101412	ST770X 27S/827 DIA WB FG WH	White
910505101413	ST770X 27S/830 DIA MB FG WH	White
910505101414	ST770X 27S/840 DIA VWB FG WH	White
910505101415	ST770X 27S/930 DIA OVL-H WH	White
910505101416	ST770X 27S/CH DIA MB FG WH	White
910505101417	ST770X 27S/FMT DIA MB FG WH	White
910505101418	ST770X 27S/FR DIA MB FG WH	White
910505101421	ST770X 27S/ROSE DIA MB FG WH	White
910505101422	ST770X 39S/830 DIA MB FG WH	White
910505101423	ST770X 39S/930 DIA OVL-H WH	White
910505100749	ST780T LED49S/827 PSU HWB SI FG	Silver
910505100756	ST780T 60S/827 PSU HWB FG SI	Silver
910505101419	ST770X 27S/PC930 DIA MB FG BK	Black
910505101420	ST770X 27S/PW930 DIA MB FG BK	Black
910505102731	ST771T 27S/830 PSU WB BK	Black
910505102734	ST771T 39S/PW930 WIA WB BK	Black
910505102737	ST771T 39S/PW930 DIA WB BK	Black
910505101434	ST780T 39S/827 PSU NB FG WH	White
910505101435	ST780T 39S/830 PSU NB FG WH	White



Order Code	Full Product Name	Housing Color
910505101436	ST780T 39S/840 PSU NB FG WH	White
910505101437	ST780T 39S/930 PSU NB FG WH	White
910505101438	ST780T 49S/827 PSU WB FG WH	White
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	White
910505101441	ST780T 49S/830 PSU MB FG WH	White
910505101442	ST780T 49S/840 PSU VWB FG WH	White
910505101446	ST780T 60S/830 PSU MB FG WH	White
910505101447	ST780T 60S/840 PSU MB FG WH	White
910505101431	ST780S 60S/827 DIA-VLC HWB BK	Black
910505101432	ST780S 60S/830 DIA-VLC HMB BK	Black
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	Black
910505101386	ST770T 27S/930 PSU MB FG SI	Silver
910505101390	ST770T 27S/PC930 PSU MB FG SI	Silver
910505101392	ST770T 27S/PW930 PSU MB FG SI	Silver
910505100743	ST770T LED49S/830 PSU HMB SI	Silver
910505101443	ST780T 49S/930 PSU MB FG SI	Silver
910505101444	ST780T 49S/PW930 PSU MB FG SI	Silver
910505101445	ST780T 60S/827 PSU WB FG SI	Silver
910505101228	ST770S 17S/827 PSU WB FG WH	White
910505101229	ST770S 17S/830 PSU MB FG WH	White
910505101230	ST770S 17S/840 PSU VWB FG WH	White
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	White
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	White
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	White
910505101371	ST770S 39S/PW930 PSU VWB FG WH	White
910505100723	ST770T 20S/830 PSU HNB WH	White
910505100724	ST770T 27S/830 PSU HMB WH	White
910505100725	ST770T LED27S/827 PSU HWB WH	White
910505100736	ST770T 39S/830 PSU HMB WH	White
910505100737	ST770T LED39S/827 PSU HWB WH	White
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	White
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	White
910505102315	ST770T 27S/ROSE WIA WB FG WH	Black
910505102316	ST770T 39S/PW930 WIA WB WH	Black
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	Silver
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	Silver
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	Silver
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	White
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	Black

Order Code	Full Product Name	Housing Color
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	Black
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	Black
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	White
910505101425	ST780S 39S/827 PSU NB FG WH	White
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	White
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	White
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	White
910505101379	ST770T 20S/830 PSU NB FG WH	White
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	White
910505101381	ST770T 27S/827 PSU WB FG WH	White
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	White
910505101384	ST770T 27S/830 PSU MB FG WH	White
910505101385	ST770T 27S/840 PSU VWB FG WH	White
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	White
910505101395	ST770T 39S/827 PSU WB FG WH	White
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	White
910505101398	ST770T 39S/830 PSU MB FG WH	White
910505101399	ST770T 39S/840 PSU MB FG WH	White
910505101378	ST770T 17S/930 PSU MB FG BK	Black
910505101387	ST770T 27S/CH PSU MB FG BK	Black
910505101388	ST770T 27S/FMT PSU MB FG BK	Black
910505101389	ST770T 27S/FR PSU MB FG BK	Black
910505101393	ST770T 27S/ROSE PSU MB FG BK	Black
910505101401	ST770T 39S/930 PSU MB FG BK	Black
910505101402	ST770T 39S/PC930 PSU MB FG BK	Black
910505101403	ST770T 39S/PW930 PSU MB FG BK	Black
910505100722	ST770T LED17S/930 PSU HMB BK	Black
910505100731	ST770T LED27S/CH PSU HMB BK FG	Black
910505100732	ST770T 27S/FR PSU HMB FG BK	Black
910505100733	ST770T 27S/FMT PSU HMB FG BK	Black
910505102732	ST771T 27S/830 PSU WB SI	Silver
910505102735	ST771T 39S/PW930 WIA WB SI	Silver
910505102738	ST771T 39S/PW930 DIA WB SI	Silver
910505100747	ST780T 39S/830 PSU HNB WH	White
910505100748	ST780T 49S/830 PSU HMB WH	White
910505100755	ST780T LED60S/830 PSU HMB WH	White
910505100721	ST770S LED17S/830 PSU HMB WH FG	White
910505101429	ST780S 49S/930 DIA-VLC HWB WH	White
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	White

## Emergency Operation

Order Code	Full Product Name	Central Emergency
910505100730	ST770T LED27S/PW930 PSU HMB SI	-
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	-
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	-
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	-
910505101207	ST770B 17S/830 PSU-E MB FG WH	-
910505101208	ST770B 20S/830 PSU-E NB FG WH	-
910505101212	ST770B 27S/830 PSU-E MB FG WH	-
910505101213	ST770B 27S/840 PSU-E VWB FG WH	-
910505101214	ST770B 27S/930 PSU-E MB FG WH	-

Order Code	Full Product Name	Central Emergency
910505101215	ST770B 27S/CH PSU-E MB FG WH	-
910505101216	ST770B 27S/FMT PSU-E MB FG WH	-
910505101217	ST770B 27S/FR PSU-E MB FG WH	-
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	-
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	-
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	-
910505101221	ST770B 39S/827 PSU-E WB FG WH	-
910505101223	ST770B 39S/830 PSU-E MB FG WH	-
910505101224	ST770B 39S/840 PSU-E VWB FG WH	-

Order Code	Full Product Name	Central Emergency
910505102730	ST771T 27S/830 PSU WB WH	No
910505102733	ST771T 39S/PW930 WIA WB WH	No
910505102736	ST771T 39S/PW930 DIA WB WH	No
910505101368	ST770S 39S/930 DIA-VLC HWB BK	-
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	-
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	-
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	-
910505101410	ST770X 17S/830 DIA MB FG WH	-
910505101411	ST770X 20S/830 DIA NB FG WH	-
910505101412	ST770X 27S/827 DIA WB FG WH	-
910505101413	ST770X 27S/830 DIA MB FG WH	-
910505101414	ST770X 27S/840 DIA VWB FG WH	-
910505101415	ST770X 27S/930 DIA OVL-H WH	-
910505101416	ST770X 27S/CH DIA MB FG WH	-
910505101417	ST770X 27S/FMT DIA MB FG WH	-
910505101418	ST770X 27S/FR DIA MB FG WH	-
910505101421	ST770X 27S/ROSE DIA MB FG WH	-
910505101422	ST770X 39S/830 DIA MB FG WH	-
910505101423	ST770X 39S/930 DIA OVL-H WH	-
910505100749	ST780T LED49S/827 PSU HWB SI FG	-
910505100756	ST780T 60S/827 PSU HWB FG SI	-
910505101419	ST770X 27S/PC930 DIA MB FG BK	-
910505101420	ST770X 27S/PW930 DIA MB FG BK	-
910505102731	ST771T 27S/830 PSU WB BK	No
910505102734	ST771T 39S/PW930 WIA WB BK	No
910505102737	ST771T 39S/PW930 DIA WB BK	No
910505101434	ST780T 39S/827 PSU NB FG WH	-
910505101435	ST780T 39S/830 PSU NB FG WH	-
910505101436	ST780T 39S/840 PSU NB FG WH	-
910505101437	ST780T 39S/930 PSU NB FG WH	-
910505101438	ST780T 49S/827 PSU WB FG WH	-
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	-
910505101441	ST780T 49S/830 PSU MB FG WH	-
910505101442	ST780T 49S/840 PSU VWB FG WH	-
910505101446	ST780T 60S/830 PSU MB FG WH	-
910505101447	ST780T 60S/840 PSU MB FG WH	-
910505101431	ST780S 60S/827 DIA-VLC HWB BK	-
910505101432	ST780S 60S/830 DIA-VLC HMB BK	-
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	-
910505101386	ST770T 27S/930 PSU MB FG SI	-
910505101390	ST770T 27S/PC930 PSU MB FG SI	-
910505101392	ST770T 27S/PW930 PSU MB FG SI	-
910505100743	ST770T LED49S/830 PSU HMB SI	-
910505101443	ST780T 49S/930 PSU MB FG SI	-
910505101444	ST780T 49S/PW930 PSU MB FG SI	-
910505101445	ST780T 60S/827 PSU WB FG SI	-
910505101228	ST770S 17S/827 PSU WB FG WH	-
910505101229	ST770S 17S/830 PSU MB FG WH	-
910505101230	ST770S 17S/840 PSU VWB FG WH	-
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	-
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	-
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	-

Order Code	Full Product Name	Central Emergency
910505101371	ST770S 39S/PW930 PSU VWB FG WH	-
910505100723	ST770T 20S/830 PSU HNB WH	-
910505100724	ST770T 27S/830 PSU HMB WH	-
910505100725	ST770T LED27S/827 PSU HWB WH	-
910505100736	ST770T 39S/830 PSU HMB WH	-
910505100737	ST770T LED39S/827 PSU HWB WH	-
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	-
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	-
910505102315	ST770T 27S/ROSE WIA WB FG WH	-
910505102316	ST770T 39S/PW930 WIA WB WH	-
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	-
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	-
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	-
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	-
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	-
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	-
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	-
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	-
910505101425	ST780S 39S/827 PSU NB FG WH	-
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	-
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	-
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	-
910505101379	ST770T 20S/830 PSU NB FG WH	-
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	-
910505101381	ST770T 27S/827 PSU WB FG WH	-
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	-
910505101384	ST770T 27S/830 PSU MB FG WH	-
910505101385	ST770T 27S/840 PSU VWB FG WH	-
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	-
910505101395	ST770T 39S/827 PSU WB FG WH	-
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	-
910505101398	ST770T 39S/830 PSU MB FG WH	-
910505101399	ST770T 39S/840 PSU MB FG WH	-
910505101378	ST770T 17S/930 PSU MB FG BK	-
910505101387	ST770T 27S/CH PSU MB FG BK	-
910505101388	ST770T 27S/FMT PSU MB FG BK	-
910505101389	ST770T 27S/FR PSU MB FG BK	-
910505101393	ST770T 27S/ROSE PSU MB FG BK	-
910505101401	ST770T 39S/930 PSU MB FG BK	-
910505101402	ST770T 39S/PC930 PSU MB FG BK	-
910505101403	ST770T 39S/PW930 PSU MB FG BK	-
910505100722	ST770T LED17S/930 PSU HMB BK	-
910505100731	ST770T LED27S/CH PSU HMB BK FG	-
910505100732	ST770T 27S/FR PSU HMB FG BK	-
910505100733	ST770T 27S/FMT PSU HMB FG BK	-
910505102732	ST771T 27S/830 PSU WB SI	No
910505102735	ST771T 39S/PW930 WIA WB SI	No
910505102738	ST771T 39S/PW930 DIA WB SI	No
910505100747	ST780T 39S/830 PSU HNB WH	-
910505100748	ST780T 49S/830 PSU HMB WH	-
910505100755	ST780T LED60S/830 PSU HMB WH	-
910505100721	ST770S LED17S/830 PSU HMB WH FG	-

Order Code	Full Product Name	Central Emergency
910505101429	ST780S 49S/930 DIA-VLC HWB WH	-

Order Code	Full Product Name	Central Emergency
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	-

Approval and Application

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505100730	ST770T LED27S/PW930 PSU HMB SI	1	0.5
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	1	0.5
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	1	0.5
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	1	0.5
910505101207	ST770B 17S/830 PSU-E MB FG WH	1	0.5
910505101208	ST770B 20S/830 PSU-E NB FG WH	1	0.5
910505101212	ST770B 27S/830 PSU-E MB FG WH	1	0.5
910505101213	ST770B 27S/840 PSU-E VWB FG WH	1	0.5
910505101214	ST770B 27S/930 PSU-E MB FG WH	1	0.5
910505101215	ST770B 27S/CH PSU-E MB FG WH	1	0.5
910505101216	ST770B 27S/FMT PSU-E MB FG WH	1	0.5
910505101217	ST770B 27S/FR PSU-E MB FG WH	1	0.5
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	1	0.5
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	1	0.5
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	1	0.5
910505101221	ST770B 39S/827 PSU-E WB FG WH	1	0.5
910505101223	ST770B 39S/830 PSU-E MB FG WH	1	0.5
910505101224	ST770B 39S/840 PSU-E VWB FG WH	1	0.5
910505102730	ST771T 27S/830 PSU WB WH	-	-
910505102733	ST771T 39S/PW930 WIA WB WH	-	-
910505102736	ST771T 39S/PW930 DIA WB WH	-	-
910505101368	ST770S 39S/930 DIA-VLC HWB BK	1	0.5
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	1	0.5
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	1	0.5
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	1	0.5
910505101410	ST770X 17S/830 DIA MB FG WH	1	0.5
910505101411	ST770X 20S/830 DIA NB FG WH	1	0.5
910505101412	ST770X 27S/827 DIA WB FG WH	1	0.5
910505101413	ST770X 27S/830 DIA MB FG WH	1	0.5
910505101414	ST770X 27S/840 DIA VWB FG WH	1	0.5
910505101415	ST770X 27S/930 DIA OVL-H WH	1	0.5

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505101416	ST770X 27S/CH DIA MB FG WH	1	0.5
910505101417	ST770X 27S/FMT DIA MB FG WH	1	0.5
910505101418	ST770X 27S/FR DIA MB FG WH	1	0.5
910505101421	ST770X 27S/ROSE DIA MB FG WH	1	0.5
910505101422	ST770X 39S/830 DIA MB FG WH	1	0.5
910505101423	ST770X 39S/930 DIA OVL-H WH	1	0.5
910505100749	ST780T LED49S/827 PSU HWB SI FG	1	0.5
910505100756	ST780T 60S/827 PSU HWB FG SI	1	0.5
910505101419	ST770X 27S/PC930 DIA MB FG BK	1	0.5
910505101420	ST770X 27S/PW930 DIA MB FG BK	1	0.5
910505102731	ST771T 27S/830 PSU WB BK	-	-
910505102734	ST771T 39S/PW930 WIA WB BK	-	-
910505102737	ST771T 39S/PW930 DIA WB BK	-	-
910505101434	ST780T 39S/827 PSU NB FG WH	1	0.5
910505101435	ST780T 39S/830 PSU NB FG WH	1	0.5
910505101436	ST780T 39S/840 PSU NB FG WH	1	0.5
910505101437	ST780T 39S/930 PSU NB FG WH	1	0.5
910505101438	ST780T 49S/827 PSU WB FG WH	1	0.5
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	1	0.5
910505101441	ST780T 49S/830 PSU MB FG WH	1	0.5
910505101442	ST780T 49S/840 PSU VWB FG WH	1	0.5
910505101446	ST780T 60S/830 PSU MB FG WH	1	0.5
910505101447	ST780T 60S/840 PSU MB FG WH	1	0.5
910505101431	ST780S 60S/827 DIA-VLC HWB BK	1	0.5
910505101432	ST780S 60S/830 DIA-VLC HMB BK	1	0.5
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	1	0.5
910505101386	ST770T 27S/930 PSU MB FG SI	1	0.5
910505101390	ST770T 27S/PC930 PSU MB FG SI	1	0.5
910505101392	ST770T 27S/PW930 PSU MB FG SI	1	0.5
910505100743	ST770T LED49S/830 PSU HMB SI	1	0.5
910505101443	ST780T 49S/930 PSU MB FG SI	1	0.5
910505101444	ST780T 49S/PW930 PSU MB FG SI	1	0.5
910505101445	ST780T 60S/827 PSU WB FG SI	1	0.5
910505101228	ST770S 17S/827 PSU WB FG WH	1	0.5
910505101229	ST770S 17S/830 PSU MB FG WH	1	0.5
910505101230	ST770S 17S/840 PSU VWB FG WH	1	0.5
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	1	0.5
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	1	0.5

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	1	0.5
910505101371	ST770S 39S/PW930 PSU VWB FG WH	1	0.5
910505100723	ST770T 20S/830 PSU HNB WH	1	0.5
910505100724	ST770T 27S/830 PSU HMB WH	1	0.5
910505100725	ST770T LED27S/827 PSU HWB WH	1	0.5
910505100736	ST770T 39S/830 PSU HMB WH	1	0.5
910505100737	ST770T LED39S/827 PSU HWB WH	1	0.5
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	1	0.5
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	1	0.5
910505102315	ST770T 27S/ROSE WIA WB FG WH	1	0.5
910505102316	ST770T 39S/PW930 WIA WB WH	1	0.5
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	1	0.5
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	1	0.5
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	1	0.5
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	1	0.5
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	1	0.5
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	1	0.5
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	1	0.5
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	1	0.5
910505101425	ST780S 39S/827 PSU NB FG WH	1	0.5
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	1	0.5
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	1	0.5
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	1	0.5
910505101379	ST770T 20S/830 PSU NB FG WH	1	0.5
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	1	0.5

**Initial Performance (IEC Compliant)**

Order Code	Full Product Name	Initial chromaticity
910505100730	ST770T LED27S/PW930 PSU HMB SI	(0.422,0.386)<2
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	(0.434,0.403)<3
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	(0.434,0.403)<3
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	(0.434,0.403)<2
910505101207	ST770B 17S/830 PSU-E MB FG WH	(0.434,0.403)<3

Order Code	Full Product Name	Flickering value (PstLM)	
		- Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910505101381	ST770T 27S/827 PSU WB FG WH	1	0.5
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	1	0.5
910505101384	ST770T 27S/830 PSU MB FG WH	1	0.5
910505101385	ST770T 27S/840 PSU VWB FG WH	1	0.5
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	1	0.5
910505101395	ST770T 39S/827 PSU WB FG WH	1	0.5
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	1	0.5
910505101398	ST770T 39S/830 PSU MB FG WH	1	0.5
910505101399	ST770T 39S/840 PSU MB FG WH	1	0.5
910505101378	ST770T 17S/930 PSU MB FG BK	1	0.5
910505101387	ST770T 27S/CH PSU MB FG BK	1	0.5
910505101388	ST770T 27S/FMT PSU MB FG BK	1	0.5
910505101389	ST770T 27S/FR PSU MB FG BK	1	0.5
910505101393	ST770T 27S/ROSE PSU MB FG BK	1	0.5
910505101401	ST770T 39S/930 PSU MB FG BK	1	0.5
910505101402	ST770T 39S/PC930 PSU MB FG BK	1	0.5
910505101403	ST770T 39S/PW930 PSU MB FG BK	1	0.5
910505100722	ST770T LED17S/930 PSU HMB BK	1	0.5
910505100731	ST770T LED27S/CH PSU HMB BK FG	1	0.5
910505100732	ST770T 27S/FR PSU HMB FG BK	1	0.5
910505100733	ST770T 27S/FMT PSU HMB FG BK	1	0.5
910505102732	ST771T 27S/830 PSU WB SI	-	-
910505102735	ST771T 39S/PW930 WIA WB SI	-	-
910505102738	ST771T 39S/PW930 DIA WB SI	-	-
910505100747	ST780T 39S/830 PSU HNB WH	1	0.5
910505100748	ST780T 49S/830 PSU HMB WH	1	0.5
910505100755	ST780T LED60S/830 PSU HMB WH	1	0.5
910505100721	ST770S LED17S/830 PSU HMB WH FG	1	0.5
910505101429	ST780S 49S/930 DIA-VLC HWB WH	1	0.5
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	1	0.5

Order Code	Full Product Name	Initial chromaticity
910505101208	ST770B 20S/830 PSU-E NB FG WH	(0.434,0.403)<3
910505101212	ST770B 27S/830 PSU-E MB FG WH	(0.434,0.403)<3
910505101213	ST770B 27S/840 PSU-E VWB FG WH	(0.382,0.380)<3
910505101214	ST770B 27S/930 PSU-E MB FG WH	(0.434,0.403)<2
910505101215	ST770B 27S/CH PSU-E MB FG WH	(0.458,0.410)<3

Order Code	Full Product Name	Initial chromaticity
910505101216	ST770B 27S/FMT PSU-E MB FG WH	(0.457,0.385)<3
910505101217	ST770B 27S/FR PSU-E MB FG WH	(0.343,0.331)<3
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	(0.422,0.386)<2
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	(0.422,0.386)<2
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	(0.478,0.382)<2
910505101221	ST770B 39S/827 PSU-E WB FG WH	(0.458,0.410)<3
910505101223	ST770B 39S/830 PSU-E MB FG WH	(0.434,0.403)<3
910505101224	ST770B 39S/840 PSU-E VWB FG WH	(0.382,0.380)<3
910505102730	ST771T 27S/830 PSU WB WH	(0.458, 0.410) SDCM <3
910505102733	ST771T 39S/PW930 WIA WB WH	(0.422, 0.386) SDCM <2
910505102736	ST771T 39S/PW930 DIA WB WH	(0.422, 0.386) SDCM <2
910505101368	ST770S 39S/930 DIA-VLC HWB BK	(0.434,0.403)<2
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	(0.458,0.410)<3
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	(0.434,0.403)<3
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	(0.434,0.403)<3
910505101410	ST770X 17S/830 DIA MB FG WH	(0.434,0.403)<3
910505101411	ST770X 20S/830 DIA NB FG WH	(0.434,0.403)<3
910505101412	ST770X 27S/827 DIA WB FG WH	(0.458,0.410)<3
910505101413	ST770X 27S/830 DIA MB FG WH	(0.434,0.403)<3
910505101414	ST770X 27S/840 DIA VWB FG WH	(0.382,0.380)<3
910505101415	ST770X 27S/930 DIA OVL-H WH	(0.434,0.403)<2
910505101416	ST770X 27S/CH DIA MB FG WH	(0.458,0.410)<3
910505101417	ST770X 27S/FMT DIA MB FG WH	(0.457,0.385)<3
910505101418	ST770X 27S/FR DIA MB FG WH	(0.343,0.331)<3
910505101421	ST770X 27S/ROSE DIA MB FG WH	(0.478,0.382)<2
910505101422	ST770X 39S/830 DIA MB FG WH	(0.434,0.403)<3
910505101423	ST770X 39S/930 DIA OVL-H WH	(0.434,0.403)<2
910505100749	ST780T LED49S/827 PSU HWB SI FG	(0.458,0.410)<3
910505100756	ST780T 60S/827 PSU HWB FG SI	(0.458,0.410)<3
910505101419	ST770X 27S/PC930 DIA MB FG BK	(0.422,0.386)<2
910505101420	ST770X 27S/PW930 DIA MB FG BK	(0.422,0.386)<2
910505102731	ST771T 27S/830 PSU WB BK	(0.458, 0.410) SDCM <3
910505102734	ST771T 39S/PW930 WIA WB BK	(0.422, 0.386) SDCM <2
910505102737	ST771T 39S/PW930 DIA WB BK	(0.422, 0.386) SDCM <2
910505101434	ST780T 39S/827 PSU NB FG WH	(0.458,0.410)<3
910505101435	ST780T 39S/830 PSU NB FG WH	(0.434,0.403)<3
910505101436	ST780T 39S/840 PSU NB FG WH	(0.382,0.380)<3
910505101437	ST780T 39S/930 PSU NB FG WH	(0.434,0.403)<2
910505101438	ST780T 49S/827 PSU WB FG WH	(0.458,0.410)<3
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101441	ST780T 49S/830 PSU MB FG WH	(0.434,0.403)<3
910505101442	ST780T 49S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101446	ST780T 60S/830 PSU MB FG WH	(0.434,0.403)<3
910505101447	ST780T 60S/840 PSU MB FG WH	(0.382,0.380)<3
910505101431	ST780S 60S/827 DIA-VLC HWB BK	(0.458,0.410)<3
910505101432	ST780S 60S/830 DIA-VLC HMB BK	(0.434,0.403)<3
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	(0.382,0.380)<3
910505101386	ST770T 27S/930 PSU MB FG SI	(0.434,0.403)<2
910505101390	ST770T 27S/PC930 PSU MB FG SI	(0.422,0.386)<2
910505101392	ST770T 27S/PW930 PSU MB FG SI	(0.422,0.386)<2
910505100743	ST770T LED49S/830 PSU HMB SI	(0.434,0.403)<3
910505101443	ST780T 49S/930 PSU MB FG SI	(0.434,0.403)<2

Order Code	Full Product Name	Initial chromaticity
910505101444	ST780T 49S/PW930 PSU MB FG SI	(0.422,0.386)<2
910505101445	ST780T 60S/827 PSU WB FG SI	(0.458,0.410)<3
910505101228	ST770S 17S/827 PSU WB FG WH	(0.458,0.410)<3
910505101229	ST770S 17S/830 PSU MB FG WH	(0.434,0.403)<3
910505101230	ST770S 17S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	(0.458,0.410)<3
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	(0.434,0.403)<3
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	(0.382,0.380)<3
910505101371	ST770S 39S/PW930 PSU VWB FG WH	(0.422,0.386)<2
910505100723	ST770T 20S/830 PSU HNB WH	(0.434,0.403)<3
910505100724	ST770T 27S/830 PSU HMB WH	(0.434,0.403)<3
910505100725	ST770T LED27S/827 PSU HWB WH	(0.458,0.410)<3
910505100736	ST770T 39S/830 PSU HMB WH	(0.434,0.403)<3
910505100737	ST770T LED39S/827 PSU HWB WH	(0.458,0.410)<3
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	(0.434,0.403)<3
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2
910505102315	ST770T 27S/ROSE WIA WB FG WH	(0.478,0.382)<2
910505102316	ST770T 39S/PW930 WIA WB WH	(0.422,0.386)<2
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	(0.458,0.410)<3
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	(0.434,0.403)<3
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	(0.382,0.380)<3
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	(0.434,0.403)<3
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	(0.434,0.403)<3
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	(0.422,0.386)<2
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	(0.422,0.386)<2
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2
910505101425	ST780S 39S/827 PSU NB FG WH	(0.458,0.410)<3
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	(0.458,0.410)<3
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	(0.434,0.403)<3
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	(0.382,0.380)<3
910505101379	ST770T 20S/830 PSU NB FG WH	(0.434,0.403)<3
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	(0.458,0.410)<3
910505101381	ST770T 27S/827 PSU WB FG WH	(0.458,0.410)<3
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101384	ST770T 27S/830 PSU MB FG WH	(0.434,0.403)<3
910505101385	ST770T 27S/840 PSU VWB FG WH	(0.382,0.380)<3
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	(0.458,0.410)<3
910505101395	ST770T 39S/827 PSU WB FG WH	(0.458,0.410)<3
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	(0.434,0.403)<3
910505101398	ST770T 39S/830 PSU MB FG WH	(0.434,0.403)<3
910505101399	ST770T 39S/840 PSU MB FG WH	(0.382,0.380)<3
910505101378	ST770T 17S/930 PSU MB FG BK	(0.434,0.403)<2
910505101387	ST770T 27S/CH PSU MB FG BK	(0.458,0.410)<3
910505101388	ST770T 27S/FMT PSU MB FG BK	(0.457,0.385)<3
910505101389	ST770T 27S/FR PSU MB FG BK	(0.343,0.331)<3
910505101393	ST770T 27S/ROSE PSU MB FG BK	(0.478,0.382)<2
910505101401	ST770T 39S/930 PSU MB FG BK	(0.434,0.403)<2
910505101402	ST770T 39S/PC930 PSU MB FG BK	(0.422,0.386)<2
910505101403	ST770T 39S/PW930 PSU MB FG BK	(0.422,0.386)<2
910505100722	ST770T LED17S/930 PSU HMB BK	(0.434,0.403)<2
910505100731	ST770T LED27S/CH PSU HMB BK FG	(0.458,0.410)<3
910505100732	ST770T 27S/FR PSU HMB FG BK	(0.343,0.331)<3

Order Code	Full Product Name	Initial chromaticity
910505100733	ST770T 27S/FMT PSU HMB FG BK	(0.457,0.385)<3
910505102732	ST771T 27S/830 PSU WB SI	(0.458, 0.410) SDCM <3
910505102735	ST771T 39S/PW930 WIA WB SI	(0.422, 0.386) SDCM <2
910505102738	ST771T 39S/PW930 DIA WB SI	(0.422, 0.386) SDCM <2
910505100747	ST780T 39S/830 PSU HNB WH	(0.434,0.403)<3

Order Code	Full Product Name	Initial chromaticity
910505100748	ST780T 49S/830 PSU HMB WH	(0.434,0.403)<3
910505100755	ST780T LED60S/830 PSU HMB WH	(0.434,0.403)<3
910505100721	ST770S LED17S/830 PSU HMB WH FG	(0.434,0.403)<3
910505101429	ST780S 49S/930 DIA-VLC HWB WH	(0.434,0.403)<2
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	(0.422,0.386)<2

**Over Time Performance (IEC Compliant)**

Order Code	Full Product Name	Driver failure rate at 5000 h
910505100730	ST770T LED27S/PW930 PSU HMB SI	-
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	-
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	1 %
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	1 %
910505101207	ST770B 17S/830 PSU-E MB FG WH	-
910505101208	ST770B 20S/830 PSU-E NB FG WH	-
910505101212	ST770B 27S/830 PSU-E MB FG WH	-
910505101213	ST770B 27S/840 PSU-E VWB FG WH	-
910505101214	ST770B 27S/930 PSU-E MB FG WH	-
910505101215	ST770B 27S/CH PSU-E MB FG WH	-
910505101216	ST770B 27S/FMT PSU-E MB FG WH	-
910505101217	ST770B 27S/FR PSU-E MB FG WH	-
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	-
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	-
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	-
910505101221	ST770B 39S/827 PSU-E WB FG WH	-
910505101223	ST770B 39S/830 PSU-E MB FG WH	-
910505101224	ST770B 39S/840 PSU-E VWB FG WH	-
910505102730	ST771T 27S/830 PSU WB WH	-
910505102733	ST771T 39S/PW930 WIA WB WH	-
910505102736	ST771T 39S/PW930 DIA WB WH	-
910505101368	ST770S 39S/930 DIA-VLC HWB BK	-
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	-
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	-
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	-
910505101410	ST770X 17S/830 DIA MB FG WH	-
910505101411	ST770X 20S/830 DIA NB FG WH	-
910505101412	ST770X 27S/827 DIA WB FG WH	-
910505101413	ST770X 27S/830 DIA MB FG WH	-
910505101414	ST770X 27S/840 DIA VWB FG WH	-
910505101415	ST770X 27S/930 DIA OVL-H WH	-
910505101416	ST770X 27S/CH DIA MB FG WH	-
910505101417	ST770X 27S/FMT DIA MB FG WH	-
910505101418	ST770X 27S/FR DIA MB FG WH	-
910505101421	ST770X 27S/ROSE DIA MB FG WH	-
910505101422	ST770X 39S/830 DIA MB FG WH	-
910505101423	ST770X 39S/930 DIA OVL-H WH	-
910505100749	ST780T LED49S/827 PSU HWB SI FG	-
910505100756	ST780T 60S/827 PSU HWB FG SI	-
910505101419	ST770X 27S/PC930 DIA MB FG BK	-
910505101420	ST770X 27S/PW930 DIA MB FG BK	-
910505102731	ST771T 27S/830 PSU WB BK	-
910505102734	ST771T 39S/PW930 WIA WB BK	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910505102737	ST771T 39S/PW930 DIA WB BK	-
910505101434	ST780T 39S/827 PSU NB FG WH	-
910505101435	ST780T 39S/830 PSU NB FG WH	-
910505101436	ST780T 39S/840 PSU NB FG WH	-
910505101437	ST780T 39S/930 PSU NB FG WH	-
910505101438	ST780T 49S/827 PSU WB FG WH	-
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	-
910505101441	ST780T 49S/830 PSU MB FG WH	-
910505101442	ST780T 49S/840 PSU VWB FG WH	-
910505101446	ST780T 60S/830 PSU MB FG WH	-
910505101447	ST780T 60S/840 PSU MB FG WH	-
910505101431	ST780S 60S/827 DIA-VLC HWB BK	-
910505101432	ST780S 60S/830 DIA-VLC HMB BK	-
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	-
910505101386	ST770T 27S/930 PSU MB FG SI	-
910505101390	ST770T 27S/PC930 PSU MB FG SI	-
910505101392	ST770T 27S/PW930 PSU MB FG SI	-
910505100743	ST770T LED49S/830 PSU HMB SI	-
910505101443	ST780T 49S/930 PSU MB FG SI	-
910505101444	ST780T 49S/PW930 PSU MB FG SI	-
910505101445	ST780T 60S/827 PSU WB FG SI	-
910505101228	ST770S 17S/827 PSU WB FG WH	-
910505101229	ST770S 17S/830 PSU MB FG WH	-
910505101230	ST770S 17S/840 PSU VWB FG WH	-
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	-
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	-
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	-
910505101371	ST770S 39S/PW930 PSU VWB FG WH	-
910505100723	ST770T 20S/830 PSU HNB WH	-
910505100724	ST770T 27S/830 PSU HMB WH	-
910505100725	ST770T LED27S/827 PSU HWB WH	-
910505100736	ST770T 39S/830 PSU HMB WH	-
910505100737	ST770T LED39S/827 PSU HWB WH	-
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	-
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	-
910505102315	ST770T 27S/ROSE WIA WB FG WH	-
910505102316	ST770T 39S/PW930 WIA WB WH	-
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	-
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	-
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	-
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	-
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	-
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	-



Order Code	Full Product Name	Driver failure rate at 5000 h
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	-
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	-
910505101425	ST780S 39S/827 PSU NB FG WH	-
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	-
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	-
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	-
910505101379	ST770T 20S/830 PSU NB FG WH	-
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	-
910505101381	ST770T 27S/827 PSU WB FG WH	-
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	-
910505101384	ST770T 27S/830 PSU MB FG WH	-
910505101385	ST770T 27S/840 PSU VWB FG WH	-
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	-
910505101395	ST770T 39S/827 PSU WB FG WH	-
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	-
910505101398	ST770T 39S/830 PSU MB FG WH	-
910505101399	ST770T 39S/840 PSU MB FG WH	-
910505101378	ST770T 17S/930 PSU MB FG BK	-
910505101387	ST770T 27S/CH PSU MB FG BK	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910505101388	ST770T 27S/FMT PSU MB FG BK	-
910505101389	ST770T 27S/FR PSU MB FG BK	-
910505101393	ST770T 27S/ROSE PSU MB FG BK	-
910505101401	ST770T 39S/930 PSU MB FG BK	-
910505101402	ST770T 39S/PC930 PSU MB FG BK	-
910505101403	ST770T 39S/PW930 PSU MB FG BK	-
910505100722	ST770T LED17S/930 PSU HMB BK	-
910505100731	ST770T LED27S/CH PSU HMB BK FG	-
910505100732	ST770T 27S/FR PSU HMB FG BK	-
910505100733	ST770T 27S/FMT PSU HMB FG BK	-
910505102732	ST771T 27S/830 PSU WB SI	-
910505102735	ST771T 39S/PW930 WIA WB SI	-
910505102738	ST771T 39S/PW930 DIA WB SI	-
910505100747	ST780T 39S/830 PSU HNB WH	-
910505100748	ST780T 49S/830 PSU HMB WH	-
910505100755	ST780T LED60S/830 PSU HMB WH	-
910505100721	ST770S LED17S/830 PSU HMB WH FG	-
910505101429	ST780S 49S/930 DIA-VLC HWB WH	-
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	-

Product Data


Order Code	Full Product Name	Product family code
910505100730	ST770T LED27S/PW930 PSU HMB SI	ST770T
910505101396	ST770T 39S/830 DIA-VLC HOVL-H SI	ST770T
910500465998	ST770B LED27S/830 PSU-E OVL-H WH	ST770B
910505100014	ST770B LED39S/930 PSU-E OVL-H WH	ST770B
910505101207	ST770B 17S/830 PSU-E MB FG WH	ST770B
910505101208	ST770B 20S/830 PSU-E NB FG WH	ST770B
910505101212	ST770B 27S/830 PSU-E MB FG WH	ST770B
910505101213	ST770B 27S/840 PSU-E VWB FG WH	ST770B
910505101214	ST770B 27S/930 PSU-E MB FG WH	ST770B
910505101215	ST770B 27S/CH PSU-E MB FG WH	ST770B
910505101216	ST770B 27S/FMT PSU-E MB FG WH	ST770B
910505101217	ST770B 27S/FR PSU-E MB FG WH	ST770B
910505101218	ST770B 27S/PC930 PSU-E MB FG WH	ST770B
910505101219	ST770B 27S/PW930 PSU-E MB FG WH	ST770B
910505101220	ST770B 27S/ROSE PSU-E MB FG WH	ST770B
910505101221	ST770B 39S/827 PSU-E WB FG WH	ST770B
910505101223	ST770B 39S/830 PSU-E MB FG WH	ST770B
910505101224	ST770B 39S/840 PSU-E VWB FG WH	ST770B
910505102730	ST771T 27S/830 PSU WB WH	ST771T
910505102733	ST771T 39S/PW930 WIA WB WH	ST771T
910505102736	ST771T 39S/PW930 DIA WB WH	ST771T
910505101368	ST770S 39S/930 DIA-VLC HWB BK	ST770S
910505101209	ST770B 27S/827 DIA-VLC-E WB FG BK	ST770B
910505101210	ST770B 27S/830 DIA-VLC-E MB FG BK	ST770B
910505101211	ST770B 27S/830 DIA-VLC-E OVL-H BK	ST770B
910505101410	ST770X 17S/830 DIA MB FG WH	ST770X
910505101411	ST770X 20S/830 DIA NB FG WH	ST770X
910505101412	ST770X 27S/827 DIA WB FG WH	ST770X
910505101413	ST770X 27S/830 DIA MB FG WH	ST770X

Order Code	Full Product Name	Product family code
910505101414	ST770X 27S/840 DIA VWB FG WH	ST770X
910505101415	ST770X 27S/930 DIA OVL-H WH	ST770X
910505101416	ST770X 27S/CH DIA MB FG WH	ST770X
910505101417	ST770X 27S/FMT DIA MB FG WH	ST770X
910505101418	ST770X 27S/FR DIA MB FG WH	ST770X
910505101421	ST770X 27S/ROSE DIA MB FG WH	ST770X
910505101422	ST770X 39S/830 DIA MB FG WH	ST770X
910505101423	ST770X 39S/930 DIA OVL-H WH	ST770X
910505100749	ST780T LED49S/827 PSU HWB SI FG	ST780T
910505100756	ST780T 60S/827 PSU HWB FG SI	ST780T
910505101419	ST770X 27S/PC930 DIA MB FG BK	ST770X
910505101420	ST770X 27S/PW930 DIA MB FG BK	ST770X
910505102731	ST771T 27S/830 PSU WB BK	ST771T
910505102734	ST771T 39S/PW930 WIA WB BK	ST771T
910505102737	ST771T 39S/PW930 DIA WB BK	ST771T
910505101434	ST780T 39S/827 PSU NB FG WH	ST780T
910505101435	ST780T 39S/830 PSU NB FG WH	ST780T
910505101436	ST780T 39S/840 PSU NB FG WH	ST780T
910505101437	ST780T 39S/930 PSU NB FG WH	ST780T
910505101438	ST780T 49S/827 PSU WB FG WH	ST780T
910505101440	ST780T 49S/830 DIA-VLC OVL-H WH	ST780T
910505101441	ST780T 49S/830 PSU MB FG WH	ST780T
910505101442	ST780T 49S/840 PSU VWB FG WH	ST780T
910505101446	ST780T 60S/830 PSU MB FG WH	ST780T
910505101447	ST780T 60S/840 PSU MB FG WH	ST780T
910505101431	ST780S 60S/827 DIA-VLC HWB BK	ST780S
910505101432	ST780S 60S/830 DIA-VLC HMB BK	ST780S
910505101433	ST780S 60S/840 DIA-VLC VWB FG BK	ST780S
910505101386	ST770T 27S/930 PSU MB FG SI	ST770T


Order Code	Full Product Name	Product family code
910505101390	ST770T 27S/PC930 PSU MB FG SI	ST770T
910505101392	ST770T 27S/PW930 PSU MB FG SI	ST770T
910505100743	ST770T LED49S/830 PSU HMB SI	ST770T
910505101443	ST780T 49S/930 PSU MB FG SI	ST780T
910505101444	ST780T 49S/PW930 PSU MB FG SI	ST780T
910505101445	ST780T 60S/827 PSU WB FG SI	ST780T
910505101228	ST770S 17S/827 PSU WB FG WH	ST770S
910505101229	ST770S 17S/830 PSU MB FG WH	ST770S
910505101230	ST770S 17S/840 PSU VWB FG WH	ST770S
910505101231	ST770S 27S/827 DIA-VLC WB FG WH	ST770S
910505101232	ST770S 27S/830 DIA-VLC MB FG WH	ST770S
910505101364	ST770S 27S/840 DIA-VLC VWB FG WH	ST770S
910505101371	ST770S 39S/PW930 PSU VWB FG WH	ST770S
910505100723	ST770T 20S/830 PSU HNB WH	ST770T
910505100724	ST770T 27S/830 PSU HMB WH	ST770T
910505100725	ST770T LED27S/827 PSU HWB WH	ST770T
910505100736	ST770T 39S/830 PSU HMB WH	ST770T
910505100737	ST770T LED39S/827 PSU HWB WH	ST770T
910505101382	ST770T 27S/830 DIA-VLC HOVL-H WH	ST770T
910505101391	ST770T 27S/PW930 DIA-VLC HMB WH	ST770T
910505102315	ST770T 27S/ROSE WIA WB FG WH	ST770T
910505102316	ST770T 39S/PW930 WIA WB WH	ST770T
910505101365	ST770S 39S/827 DIA-VLC WB FG SI	ST770S
910505101366	ST770S 39S/830 DIA-VLC MB FG SI	ST770S
910505101367	ST770S 39S/840 DIA-VLC VWB FG SI	ST770S
910505101405	ST770T 49S/830 DIA-VLC HOVL-V WH	ST770T
910505101439	ST780T 49S/830 DIA-VLC HOVL-H BK	ST780T
910505101369	ST770S 39S/PC930 DIA-VLC HVWB BK	ST770S
910505101370	ST770S 39S/PW930 DIA-VLC HVWB BK	ST770S
910505101377	ST770S 49S/PW930 DIA-VLC HMB WH	ST770S
910505101425	ST780S 39S/827 PSU NB FG WH	ST780S
910505101426	ST780S 49S/827 DIA-VLC WB FG WH	ST780S
910505101427	ST780S 49S/830 DIA-VLC MB FG WH	ST780S

Order Code	Full Product Name	Product family code
910505101428	ST780S 49S/840 DIA-VLC VWB FG WH	ST780S
910505101379	ST770T 20S/830 PSU NB FG WH	ST770T
910505101380	ST770T 27S/827 DIA-VLC OVL-V WH	ST770T
910505101381	ST770T 27S/827 PSU WB FG WH	ST770T
910505101383	ST770T 27S/830 DIA-VLC OVL-H WH	ST770T
910505101384	ST770T 27S/830 PSU MB FG WH	ST770T
910505101385	ST770T 27S/840 PSU VWB FG WH	ST770T
910505101394	ST770T 39S/827 DIA-VLC OVL-V WH	ST770T
910505101395	ST770T 39S/827 PSU WB FG WH	ST770T
910505101397	ST770T 39S/830 DIA-VLC OVL-H WH	ST770T
910505101398	ST770T 39S/830 PSU MB FG WH	ST770T
910505101399	ST770T 39S/840 PSU MB FG WH	ST770T
910505101378	ST770T 17S/930 PSU MB FG BK	ST770T
910505101387	ST770T 27S/CH PSU MB FG BK	ST770T
910505101388	ST770T 27S/FMT PSU MB FG BK	ST770T
910505101389	ST770T 27S/FR PSU MB FG BK	ST770T
910505101393	ST770T 27S/ROSE PSU MB FG BK	ST770T
910505101401	ST770T 39S/930 PSU MB FG BK	ST770T
910505101402	ST770T 39S/PC930 PSU MB FG BK	ST770T
910505101403	ST770T 39S/PW930 PSU MB FG BK	ST770T
910505100722	ST770T LED17S/930 PSU HMB BK	ST770T
910505100731	ST770T LED27S/CH PSU HMB BK FG	ST770T
910505100732	ST770T 27S/FR PSU HMB FG BK	ST770T
910505100733	ST770T 27S/FMT PSU HMB FG BK	ST770T
910505102732	ST771T 27S/830 PSU WB SI	ST771T
910505102735	ST771T 39S/PW930 WIA WB SI	ST771T
910505102738	ST771T 39S/PW930 DIA WB SI	ST771T
910505100747	ST780T 39S/830 PSU HNB WH	ST780T
910505100748	ST780T 49S/830 PSU HMB WH	ST780T
910505100755	ST780T LED60S/830 PSU HMB WH	ST780T
910505100721	ST770S LED17S/830 PSU HMB WH FG	ST770S
910505101429	ST780S 49S/930 DIA-VLC HWB WH	ST780S
910505101430	ST780S 49S/PW930 DIA-VLC HMB WH	ST780S


## Polar Wide Diagrams



Polar Normal (separate) - ST770TI -  
910500465998




Polar Normal (separate) - ST770TI -  
910505101405




Polar Normal (separate) - ST770TI -  
910505101224




Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101371




Polar Normal (separate) - ST780TI - 910505101439




Polar Normal (separate) - ST770TI - 910505101410




Polar Normal (separate) - ST770TI - 910505101392




Polar Normal (separate) - ST770TI - 910505101402




Polar Normal (separate) - ST770TI - 910505101213



Polar Normal (separate) - ST770TI - 910505101423




Polar Normal (separate) - ST770TI - 910505101232




Polar Normal (separate) - ST770TI - 910505101391


Polar Wide Diagrams




Polar Normal (separate) - ST770TI -  
910505101207




Polar Normal (separate) - ST780TI -  
910505101426




Polar Normal (separate) - ST770TI -  
910505101367




Polar Normal (separate) - ST780TI -  
910505101431




Polar Normal (separate) - ST780TI -  
910505101440




Polar Normal (separate) - ST770TI -  
910505101403



Polar Normal (separate) - ST780TI -  
910505101447




Polar Normal (separate) - ST770TI -  
910505101395




Polar Normal (separate) - ST770TI -  
910505101394


Polar Wide Diagrams




Polar Normal (separate) - ST770TI -  
910505101216




Polar Normal (separate) - ST770TI -  
910505100731




Polar Normal (separate) - ST770TI -  
910505101397




Polar Normal (separate) - ST780TI -  
910505101428




Polar Normal (separate) - ST770TI -  
910505101368




Polar Normal (separate) - ST770TI -  
910505101369



Polar Normal (separate) - ST770TI -  
910505101419




Polar Normal (separate) - ST770TI -  
910505101413




Polar Normal (separate) - ST770TI -  
910505101414


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101377




Polar Normal (separate) - ST770TI - 910505101387




Polar Normal (separate) - ST770TI - 910505101418




Polar Normal (separate) - ST770TI - 910505101380




Polar Normal (separate) - ST770TI - 910505101384




Polar Normal (separate) - ST770TI - 910505101411



Polar Normal (separate) - ST770TI - 910505101386




Polar Normal (separate) - ST780TI - 910505101433




Polar Normal (separate) - ST780TI - 910505101437


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101208




Polar Normal (separate) - ST780TI - 910505101430




Polar Normal (separate) - ST770TI - 910505101383




Polar Normal (separate) - ST770TI - 910505101212




Polar Normal (separate) - ST770TI - 910505101228




Polar Normal (separate) - ST780TI - 910505101438



Polar Normal (separate) - ST770TI - 910505101381




Polar Normal (separate) - ST780TI - 910505101445




Polar Normal (separate) - ST770TI - 910505101421


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505102316




Polar Normal (separate) - ST770TI - 910505101417




Polar Normal (separate) - ST770TI - 910505101396




Polar Normal (separate) - ST780TI - 910505101425




Polar Normal (separate) - ST770TI - 910505101388




Polar Normal (separate) - ST770TI - 910505101214



Polar Normal (separate) - ST770TI - 910505101370




Polar Normal (separate) - ST770TI - 910505101390




Polar Normal (separate) - ST770TI - 910505101382


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101221




Polar Normal (separate) - ST780TI - 910505101432




Polar Normal (separate) - ST770TI - 910505101416




Polar Normal (separate) - ST770TI - 910505101219




Polar Normal (separate) - ST780TI - 910505101435




Polar Normal (separate) - ST780TI - 910505101441



Polar Normal (separate) - ST770TI - 910505101364




Polar Normal (separate) - ST770TI - 910505101215




Polar Normal (separate) - ST780TI - 910505101427


Polar Wide Diagrams




Polar Normal (separate) - ST770TI -  
910505100733




Polar Normal (separate) - ST770TI -  
910505101231




Polar Normal (separate) - ST770TI -  
910505101223




Polar Normal (separate) - ST770TI -  
910505101366




Polar Normal (separate) - ST770TI -  
910505101422




Polar Normal (separate) - ST770TI -  
910505101211



Polar Normal (separate) - ST770TI -  
910505101378




Polar Normal (separate) - ST770TI -  
910505101210




Polar Normal (separate) - ST770TI -  
910505101393




Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101415




Polar Normal (separate) - ST770TI - 910505101389




Polar Normal (separate) - ST770TI - 910505101401




Polar Normal (separate) - ST780TI - 910505101442




Polar Normal (separate) - ST770TI - 910505102315




Polar Normal (separate) - ST770TI - 910505101365



Polar Normal (separate) - ST770TI - 910505101218






Polar Normal (separate) - ST770TI - 910505101420



Polar Normal (separate) - ST780TI - 910505101436




Polar Wide Diagrams



Polar Normal (separate) - ST770TI - 910505101220

Polar Normal (separate) - ST780TI - 910505101443




Polar Normal (separate) - ST770TI - 910505101379



Polar Normal (separate) - ST770TI - 910505101398

Polar Normal (separate) - ST770TI - 910505101399

Polar Normal (separate) - ST780TI - 910505101429




Polar Normal (separate) - ST770TI - 910505101209


Polar Normal (separate) - ST770TI - 910505101217

Polar Normal (separate) - ST770TI - 910505101230


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505101229




Polar Normal (separate) - ST770TI - 910505101385




Polar Normal (separate) - ST770TI - 910505101412




Polar Normal (separate) - ST780TI - 910505101434




Polar Normal (separate) - ST780TI - 910505101444




Polar Normal (separate) - ST780TI - 910505101446



Polar Normal (separate) - ST770TI - 910505100014




Polar Normal (separate) - ST770TI - 910505100723




Polar Normal (separate) - ST770TI - 910505100721


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505100722




Polar Normal (separate) - ST770TI - 910505100724




Polar Normal (separate) - ST770TI - 910505100725




Polar Normal (separate) - ST770TI - 910505100730




Polar Normal (separate) - ST770TI - 910505100732




Polar Normal (separate) - ST770TI - 910505100743



Polar Normal (separate) - ST780TI - 910505100747




Polar Normal (separate) - ST780TI - 910505100748




Polar Normal (separate) - ST770TI - 910505100737


Polar Wide Diagrams




Polar Normal (separate) - ST770TI - 910505100736




Polar Normal (separate) - ST780TI - 910505100755




Polar Normal (separate) - ST780TI - 910505100756




Polar Normal (separate) - ST780TI - 910505100749




Polar Normal (separate) - ST770TI - 910505102732




Polar Normal (separate) - ST770TI - 910505102731



Polar Normal (separate) - ST770TI - 910505102738




Polar Normal (separate) - ST770TI - 910505102736




Polar Normal (separate) - ST770TI - 910505102735


## Polar Wide Diagrams




Polar Normal (separate) - ST770TI -  
910505102730



Polar Normal (separate) - ST770TI -  
910505102733



Polar Normal (separate) - ST770TI -  
910505102737



Polar Normal (separate) - ST770TI -  
910505102734

