



TUV TL Mini - Small diameter lamps for residential applications

TUV TL Mini

TUV TL Mini lamps are slim double-ended UV-C 253.7 nm emitting lamps. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime.

Benefits

- Controlled UV-C output over lifetime of the lamp
- High system efficacy
- Good environmental choice because of lowest amount of mercury

Features

- Short-wave UV radiation with a peak at 253.7 nm (UV-C)
- Protective inside coating ensures almost constant UV output over the complete lifetime of the lamp
- Special lamp glass filters out the 185 nm ozone-forming radiation
- Warning sign on lamp indicates that the lamp radiates UVC

Application

- Residential drinking water units
- Fish pond water units
- In-duct air treatment units
- Stand alone air handling units

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

Versions




XPPR XUTUV 0003

Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 11W 4P SE UNP/32	19 mm	251.8 mm	244.1 mm
TUV 20W 4P SE UNP/32	19.3 mm	437.7 mm	430 mm
TUV 25W - 4P SE UNP/32	19.3 mm	556.6 mm	548.9 mm



Product	D	C
TUV 11W FAM/10X25BOX	16 mm	226.3 mm

Approval and Application

Mercury (Hg) Content (Nom) 4.4 mg

TUV TL Mini

General Information

Order Code	Full Product Name	Cap-Base
927971204099	TUV 11W 4P SE UNP/32	4PINSSINGLEENDED
927972204099	TUV 25W - 4P SE UNP/32	4PINSSINGLEENDED

Order Code	Full Product Name	Cap-Base
927973404099	TUV 20W 4P SE UNP/32	4PINSSINGLEENDED
928002204013	TUV 11W FAM/10X25BOX	G5

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927971204099	TUV 11W 4P SE UNP/32	0.4 A	11.5 W
927972204099	TUV 25W - 4P SE UNP/32	0.35 A	23 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927973404099	TUV 20W 4P SE UNP/32	0.45 A	20.24 W
928002204013	TUV 11W FAM/10X25BOX	0.4 A	11.5 W

