



Product Description

TUV TL Mini

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Benefits

- Security of effective disinfection over the complete lifetime of the lamp
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection

Features

- Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection purposes
- Protective inside coating ensures constant UV output over the complete lifetime of the lamp
- Lamp glass filters out the 185 nm ozone-forming line
- Warning sign on lamp indicates that the lamp radiates UVC

Application

- Deactivation of bacteria, viruses and other micro-organisms
- Residential drinking water units
- Fish pond water units
- In-duct air treatment units
- Stand alone air purifiers

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

TUV TL Mini


Versions



Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 16W 4P SE UNP/32	19 mm	328 mm	320.3 mm
TUV 25W - 4P SE UNP/32	19.3 mm	556.6 mm	548.9 mm



Product	D	C
TUV 11W CN FAM/10X25BOX	16 mm	226.3 mm
TUV 16W CN FAM/10X25BOX	16 mm	302.5 mm

Light Technical

Color Designation -

Approval and Application

Mercury (Hg) Content (Nom) 4.4 mg

General Information

Order Code	Full Product Name	Cap-Base
927971404099	TUV 16W 4P SE UNP/32	4PINSSINGLEENDED
927972204099	TUV 25W - 4P SE UNP/32	4PINSSINGLEENDED

Order Code	Full Product Name	Cap-Base
928002004019	TUV 16W CN FAM/10X25BOX	G5
928002204019	TUV 11W CN FAM/10X25BOX	G5

Light Technical

TUV TL Mini

Order Code	Full Product Name	Color Code
927971404099	TUV 16W 4P SE UNP/32	-
927972204099	TUV 25W - 4P SE UNP/32	-

Order Code	Full Product Name	Color Code
928002004019	TUV 16W CN FAM/10X25BOX	TUV
928002204019	TUV 11W CN FAM/10X25BOX	TUV

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927971404099	TUV 16W 4P SE UNP/32	0.4 A	15 W
927972204099	TUV 25W - 4P SE UNP/32	0.35 A	23 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928002004019	TUV 16W CN FAM/10X25BOX	0.4 A	15 W
928002204019	TUV 11W CN FAM/10X25BOX	0.4 A	11.5 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
927971404099	TUV 16W 4P SE UNP/32	-
927972204099	TUV 25W - 4P SE UNP/32	-

Order Code	Full Product Name	Bulb Shape
928002004019	TUV 16W CN FAM/10X25BOX	T16
928002204019	TUV 11W CN FAM/10X25BOX	T16

