

# PHILIPS

Spot

LED

5W (50W)

GU5.3 cap

Cool daylight

Non-dimmable



8718696579572



## Durable LED accent lighting with a focused beam

Philips LED spots provide a focused bright beam, an long life, and significant energy savings.

### Beacon of trust

- You can trust what the Philips packaging is saying.

### Simple replacement

- Get maximum light output as soon as you flip the switch.

### Create an active atmosphere

- Soft sparkling light for modern interior

### Choose for a sustainable solution

- Safe for any room and convenient to recycle

# Highlights

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Instant start

Immediate light when switching on, that is the promise of the Philips instant starting energy saving LED lamps.

## 4000K Bright white light

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

# Specifications

## Bulb characteristics

- Shape: Spot
- Lamp shape: Directional spot
- Socket: GU5.3
- Dimmable: No

## Bulb dimensions

- Height: 46 mm
- Width: 50 mm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 24 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 435 lm
- Warm-up time to 60% light: 1 s
- Correlated Color Temperature (Nom): 6500 K
- Luminous Flux: 435 lm
- Luminous Efficacy (rated) (Nom): 87.00 lm/W

## Other characteristics

- Efficacy: 87 lm/W
- EU RoHS compliant: Yes

## Power

- Power Factor (Fraction): 0.5

## Power consumption

- Power factor: >0.5
- Voltage: 12 V
- Wattage: 5 W
- Wattage equivalent: 50 W
- Power Consumption: 5 W

## Product dimensions and weight

- Length: 4.7 cm

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 1700 cd

#### Technical specifications

- Frequency: 50-60 Hz
- Line Frequency: - Hz
- Dimmable: No
- Cap-Base: GU5.3

#### Packaging dimensions and weight

- EAN/UPC - product: 8718696579572
- Net weight: 0.05 kg
- Gross weight: 0.06 kg
- Height: 5.2 cm
- Length: 4.5 cm
- Width: 4.5 cm



Issue date: 2025-03-07  
Version: 0.579

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)