

PHILIPS

Einstein Desk Light

Desk Lights

2800/4000/5100K

Dark grey

Dimmable



8719514396852



With EyeComfort, for light that's easy on your eyes

Desk light with professional light guide technology and built-in sensor provides an enhanced visibility and more convenience

Light effect

- SceneSwitch color change

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Step dimming

Highlights

SceneSwitch color change

SceneSwitch Color Change lets you set the overall mood of a living space at home. Stay focused with cool daylight, be more productive with cool white light or wind down and relax with warm white light. In essence, consumers can control the lights in their home according to their daily activities.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver

comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Step dimming

Select from different dimming levels to create the right mood for the moment.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Dark Grey
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 94

Miscellaneous

- Especially designed for: Bedroom, Living Room, Home Office
- Style: Contemporary
- Type: Desk Lights
- EyeComfort: Yes
- Extra Features: Dimmable

Other characteristics

- Lamp current: 180 mA
- Efficacy: 42 lm/W

Product dimensions and weight

- Net weight: 3.44 kg
- Height: 45.7 cm
- Length: 20 cm
- Width: 26.8 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 630
- Light color: 2800/4000/5100
- Mains power: 100-240
- Fixture dimmable: Step Dim - Do not use with dimmer
- LED: Yes
- Wattage bulb included: 15
- IP code: IP20
- Class of protection: Class II

8719514396852

Packaging dimensions and weight

- EAN/UPC - product: 8719514396852
- Net weight: 2.3 kg
- Gross weight: 3.45 kg
- Height: 51 cm
- Length: 23.2 cm
- Width: 26.6 cm
- Material number (12NC): 929003179507



Issue date: 2024-06-15
Version: 0.271

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com