

PHILIPS

Circular fluorescent

TL-E Super 80

40 W

G10q

Cool daylight

928027486574



Vibrant experience with extra brightness

Philips Color 80s offer higher light output for extra brightness and better ambiance. They are suitable for applications where light quality is important for a more vibrant experience.

Saves energy

- Saves energy

Gives you bright light

- Vibrant experience with extra brightness

Highlights

Saves energy Bright boost

High efficient fluorescent combined with BrightBoost technology for good color rendering and extra brightness

Specifications

Bulb characteristics

- Socket: G10q
- Dimmable: No

Durability

- Nominal lifetime: 8,000 hour(s)

Light characteristics

- Color rendering index (CRI): 80
- Light Color Category: Cool Daylight
- Correlated Color Temperature (Nom): 6500
- Luminous Flux: 3,070 lm
- Luminous Efficacy (rated) (Nom): 78 lm/W

Power consumption

- Wattage: 40 W
- Power Consumption: 40.0 W

Technical specifications

- Light output: 3,070 lm
- Shape: Circular fluorescent
- Dimmable: Yes
- Cap-Base: G10q

Packaging dimensions and weight

- EAN/UPC - product: 8711500286017
- Net weight: 0.24 kg
- Gross weight: 0.43 kg
- Height: 40.5 cm
- Length: 3.5 cm
- Width: 42 cm
- Material number (12NC): 928027486574



Issue date: 2024-06-15
Version: 0.433

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com