


		L1200			L1500	ı	
		LED25S LED41S LED64S			LED35S LED52S LED809		
		Electrical char			ics		
Inom (mA)	80	140	220	115	180	260	
Imax (A)	8.3	11.6	14.4	10	10.6	15.7	
Tref (µs)	332	499	579	508	527	678	
MCB		Luminaire Max.					
B-10 A	19	11	8	12	11	6	
B-16 A	25	13	9	16	13	8	
C-10 A	24	13	10	16	14	8	
C-16 A	38	22	16	25	23	14	

Optional


Installation Mode Suspension
12NC 911401776802
Description BN126Z SC
Short EOC 36574999



Signify Holding.


All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.







Туре	Energy efficiency class	P (W)	A (mm)	L (mm)	Q kg
BN126C LED25_41_64S/840 PSU L1200	E	19/30/48	798	1135	1.01
BN126C LED35_52_80S/840 PSU L1500	E	24.5/38/59	798	1450	1.27





Type	Lumen output	power	Factory setting
	2500lm	19W	
L1200	4100lm	30W	✓
	6400lm	48W	
	3500lm	24.5W	
L1500	5200lm	38W	✓
	8000lm	59W	

© 01/2023 Signify Holding. All rights reserved


Life time table				
L85 50k hrs	All			
L80 75K hrs	5200-6400lm			
L70 up to 100K hrs	2500-4100lm			

1/4





2/4



3/4