



CE	indoor	IP20	220V 240V	50Hz 60Hz	Life 50K hrs @L50	Max. 35°C Min. -10°C	GLOW WIRE 650°C	Energy efficiency class of light source	LxWxH (mm)	kg	Safety cable (SC) in the box
MAZDA G2 RC007B 32S/840 PSU W60L60 OC FR		3200	4000	32.0	02	E	595x595x35	1.52	Yes		



Available as accessory(Need to purchase separately)



The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material.

If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.

Luminaire must not be used or stored in corrosive environment where hazardous materials such as sulphur, chlorine, phthalates, etc. are present.

