


Daylight W60L60 driver Standalone





220 V 240 V 50Hz 60Hz



IP20













	Power (W)	Output current (A)	voltage (V)	Dimensions LxWxH (mm)	kg	
Daylight W60L60 driver Standalone	33	max. 2x 0.34	max. 60	585x114x72	1,5	









Electrical characteristics I max (A) 8 T ref (Us) 175 MCB Max n. of lumin. B-10 A 48 B-16 A 77 C-10 A 50 C-16 A 80





- If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer, his service agent or similar qualified person in order to avoid hazard.
- The product is IPXO & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Signify cannot guarantee safe failure & product warranty will become void.

ATTENTION OBSERVE PRECAUTIONS FOR HANDLING ELECTROSTATIC