

PHILIPS

Twirly Ceiling Light
12W

Ceiling Lights

4000K

White

31814/31/17



Decorate your home with light

Bring a natural feel to your room with this Philips myLiving Twirly LED ceiling light. It casts out a diffused cool light to illuminate every corner of your room and can be used on both ceilings and walls.

Sustainable light solutions

- Energy saving
- High quality LED light
- Long operating life up to 15 years
- Cool white light
- Philips offers 5 year warranty on the LED module and driver

Special characteristics

- Suitable for wall and ceiling installation

Designed for your living- and bedroom

- Perfect to relax and socialise
- Create a stylish and welcoming atmosphere

Highlights

Energy saving



This Philips energy saving lamp conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Long operating life



A light source you can trust. The integrated LEDs, used in this Philips LED lamp, will last up to 15.000 hours (which equals 15 years on basis of an average use of 3 hours / day with an amount of at least of 13.000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambiance in your home.

Cool white light




Light can have different color temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips light offers cool white light that keeps you energised.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

Wall and ceiling installation



Install this lamp as a wall light or ceiling light, just the way you like it.

Perfect to relax and socialise

The living room is the heart of any home - a place where families gather to relax and guests socialise. Lighting for your living- and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and to give the room a warm and welcoming feel.

Create a stylish atmosphere

This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Perfectly suited for wall and ceiling installation: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 100 mA
- Efficacy: 116 lm/W

Product dimensions and weight

- Net weight: 0.4 kg
- Height: 6.5 cm
- Length: 28.7 cm
- Width: 28.7 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Light source equivalent to traditional bulb of: 72 W
- Diameter: 287 mm
- Total lumen output fixture: 1400
- Bulb technology: LED, 240 V
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- Wattage bulb included: 12
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 5413987155857
- Net weight: 0.4 kg
- Gross weight: 0.68 kg
- Height: 6.7 cm
- Length: 33.4 cm
- Width: 33.4 cm
- Material number (12NC): 915004571601



Issue date: 2024-09-07
Version: 0.507

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com