

# PHILIPS

## Downlight

Recessed Lights

3000/4000/6500K

White

Dimmable; Water Resistant



8719514317253



## Less hassle, more savings. Tri-colour enabled downlight.

With its robust design and optimal performance, Philips LED Performance downlight is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

### Light effect

- Available in Warm White, Cool White or Cool Daylight

### Safety

- No harmful UV radiation
- IP54 seal rating. Ideal for balconies or moist areas. Direct spray of water to be avoided.

### Control

- Dimmable

### Durability

- Energy saving
- Long life span up to 20,000 hours

# Highlights

## Available in Warm White, Cool White or Cool Daylight

Different light colors can affect mood: warm white is perfect for relaxation, cool white for concentration and cool daylight for energizing you

## No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

## IP54 seal rating. Ideal for balconies or moist areas. Direct spray of water to be avoided.

This means the product can withstand moisture, so you can use it on balconies, porches and similar areas.

## Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow - just like traditional lamps.

## Energy saving

Saves energy - which is good for your bills, and the environment.

## Long life span up to 20,000 hours

Philips LED technology extends your product's lifetime up to 20,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 10,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Bathroom, Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Water Resistant

## Other characteristics

- Lamp current: 45 mA
- Efficacy: 111 lm/W

## Product dimensions and weight

- Net weight: 0.315 kg
- Cut out length: 12.0 cm
- Cut out width: 12.0 cm
- Height: 5.9 cm
- Length: 14 cm
- Recessed distance: 0 cm
- Width: 14 cm

## Service

- Warranty: 2 year(s)

#### Technical specifications

- Lifetime up to: 20,000 hour(s)
- Diameter: 140 mm
- Total lumen output fixture: 1000
- Light color: 3000/4000/6500
- Mains power: AC 220-240
- Fixture dimmable: Yes
- LED: Yes
- Wattage bulb included: 9
- IP code: IP20/54
- Class of protection: Class II

#### Packaging dimensions and weight

- EAN/UPC - product: 8719514317253
- Net weight: 0.32 kg
- Gross weight: 0.36 kg
- Height: 15 cm
- Length: 7.1 cm
- Width: 15 cm
- Material number (12NC):  
929002645701



Issue date: 2024-09-17  
Version: 0.84

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)