

PHILIPS

Filament Bulb Clear
60W G95 E27

LED


2700K

806lm

15000h

Dimming

8719514338746



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Dims to a warm glow

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light..

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off. "

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Type of glass: Clear
- Dimmable: Yes
- Bulb Finish: Clear

Bulb dimensions

- Height: 14.2 cm
- Width: 9.5 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 270 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: instant full light
- Color Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- Efficacy: 111 lm/W

Packaging information

- EAN: 8719514338746
- EOC: 871951433874600
- Product title: LED classic 7.2-60W G95 E27 WW CL D

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7.2 W
- Wattage equivalent: 60 W

Product dimensions and weight

- Length: 14.2 cm

Technical specifications

• Frequency: 50-60 Hz



Issue date: 2024-11-21
Version: 0.49

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com