

PHILIPS

Filament Bulb Clear
60W A60 B22

LED

2700K

806lm

15000h

Dimming

8719514377196



Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose for a sustainable solution

- Saves up to 90% Energy

Create the right light for your home

- Perfect for general room lighting

Highlights

Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Dimmable: Only with specific dimmers
- Bulb Finish: Clear
- Bulb Material: Glass

Bulb dimensions

- Height: 10.3 cm
- Width: 6 cm

Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 806 lm
- Luminous Efficacy (rated) (Nom): 134 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- Efficacy: 134 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514377196
- EOC: 871951437719600
- Product title: LEDclassic 60W A60 2700K B22 D CL AU

Power

- Power Factor (Fraction): 0.6

Power consumption

- Power factor: 0.6
- Voltage: 220–240 V
- Wattage: 6 W
- Wattage equivalent: 60 W
- Power Consumption: 6 W

Product dimensions and weight

- Length: 10.3 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 50–60 Hz
- Dimmable: Only with specific dimmers
- Cap-Base: B22

Packaging dimensions and weight

- EAN/UPC – product: 8719514377196
- Net weight: 0.03 kg
- Gross weight: 0.06 kg
- Height: 12 cm
- Length: 6.6 cm
- Width: 6.6 cm



Issue date: 2025-03-07
Version: 0.52

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com