

# PHILIPS

Filament Candle  
Clear 40W P45 B22

LED


2700K

470lm

15000h

Dimming

8719514377431



## Experience dimmable, warm white LED light

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

### Choose for a sustainable solution

- Better for your wallet and your planet

### Create the right light for your home

- Perfect for decorative fixtures

# Highlights

## Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

## Perfect for decorative fixture



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips, and post lights.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: B22
- Type of glass: Clear
- Dimmable: Only with specific dimmers
- Bulb Finish: Clear
- Bulb Material: Glass

## Bulb dimensions

- Height: 7.7 cm
- Width: 4.5 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 470 lm
- Luminous Efficacy (rated) (Nom): 134 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- Efficacy: 134 lm/W
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8719514377431
- EOC: 871951437743100
- Product title: LEDclassic 40W P45 2700K B22 D CL AU

## Power

- Power Factor (Fraction): 0.6

## Power consumption

- Power factor: 0.6
- Voltage: 220-240 V
- Wattage: 3.5 W
- Wattage equivalent: 40 W
- Power Consumption: 3.5 W

#### Product dimensions and weight

- Length: 7.7 cm

#### Rated values

- Rated lifetime: 15,000 hour(s)

#### Technical specifications

- Frequency: 50-60 Hz
- Dimmable: Only with specific dimmers
- Cap-Base: B22

#### Packaging dimensions and weight

- EAN/UPC - product: 8719514377431
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 10.1 cm
- Length: 5.5 cm
- Width: 5.5 cm



Issue date: 2024-11-21  
Version: 0.32

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)