

# PHILIPS

Reflector 120W  
PAR38 E27

LED

2700K

1200lm

15000h

8719514406933



## Smart lighting for you daily living

PAR38 with daylight and motion sensor to provide an easy smart lighting for you

### **Light beyond illumination**

- Instant on
- Built-in automatic on/off light sensor

# Highlights

## Instant on Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E27
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Bulb dimensions

- Height: 13.7 cm
- Width: 12.2 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 1200 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 1,200 lm
- Luminous Efficacy (rated) (Nom): 92.00 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Efficacy: 92 lm/W
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8719514406933
- EOC: 871951440693300
- Product title: 13PAR38/S/120W/927 40D E27 ND/G/110-277V

## Power

- Power Factor (Fraction): 0.7

## Power consumption

- Power factor: 0.7
- Voltage: 110-277 V
- Wattage: 13 W
- Wattage equivalent: 120 W
- Power Consumption: 13 W

#### Product dimensions and weight

- Length: 13.7 cm

#### Rated values

- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 2231 cd

#### Technical specifications

- Frequency: 50-60 Hz
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap-Base: E27

#### Packaging dimensions and weight

- EAN/UPC - product: 8719514406933
- Net weight: 0.31 kg
- Gross weight: 0.38 kg
- Height: 15.7 cm
- Length: 13 cm
- Width: 13 cm



Issue date: 2025-03-07  
Version: 0.53

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)