

# PHILIPS


Capsule 20W  
capsule G4

LED

2700K

200lm

15000h



8720169300491



## Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- True incandescent-like warm white light

### Choose for a sustainable solution

- Saves up to 80% Energy

### Create the right light for your home

- A simple LED for everyday use

# Highlights

## Incandescent-like warm white



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for

relaxing. This 2700K light is ideal for home lighting design

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional capsule
- Socket: G4
- Dimmable: No
- Bulb Finish: Clear
- Bulb Material: Clear Plastic

## Bulb dimensions

- Height: 3.75 cm
- Width: 0.95 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 200 lm

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Efficacy: 117 lm/W

## Packaging information

- EAN: 8720169300491
- EOC: 872016930049100
- Product title: LED 20W G4 WW 12V ND micro SRT6

## Power consumption

- Power factor: 0.5
- Voltage: AC Electronic 12 V
- Wattage: 1.7 W
- Wattage equivalent: 20 W
- Energy Efficiency Label (EEL): F

## Product dimensions and weight

- Length: 3.75 cm

#### Technical specifications

- Frequency: - Hz
- EPREL Registration Number: 1879160

#### Packaging dimensions and weight

- EAN/UPC - product: 8720169300491
- Net weight: 0 kg
- Gross weight: 0.01 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm
- Material number (12NC):  
929003779058



Issue date: 2024-07-25  
Version: 0.202

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)