

PHILIPS

Pomeron Recessed
Light

Recessed Lights

4000K

White

Dimmable



6947830439270



One fixture. Your switch. Three light settings

Create the right mood by changing brightness. Philips' SceneSwitch LED ceiling light lets you enjoy three brightness settings that are perfect for every moment. No dimmer or additional installation is required - all you need is your existing switch

Match your interior

- Decorative metallic finishing

Light effect

- Bright and focused beam

Safety

- No harmful UV radiation

Control

- Step dimming

Durability

- Long life span up to 15,000 hours

Highlights

Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

Step dimming

Select from different dimming levels to create the right mood for the moment.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 7,500

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 30 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable

Other characteristics

- Lamp current: 60 mA
- Efficacy: 57 lm/W

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.114 kg
- Cut out length: 7.0 cm
- Cut out width: 7.0 cm
- Height: 6.2 cm
- Length: 9 cm
- Recessed distance: 5.5 cm
- Width: 9 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 90 mm
- Total lumen output fixture: 450
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: Step Dim - Do not use with dimmer
- LED: Yes
- Wattage bulb included: 7
- IP code: IP20

- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 6947830439270
- Net weight: 0.11 kg
- Gross weight: 0.15 kg
- Height: 9 cm
- Length: 9.5 cm
- Width: 9.5 cm
- Material number (12NC): 915005738301



Issue date: 2024-09-17
Version: 0.87

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com