

PHILIPS

Weather Proof
Cover

Switches & Sockets

LeafStyle

Polycarbonate

Grey

8718699674601



High quality switch and socket designed to safely last for years

Philips LeafStyle provides modern design, high safety standard and easy to install switch & socket to your family.

Convenience

- IP55 Protection degree

Safety and Durability

- High quality PC
- IEC standard and Philips internal rule

Highlights

IP55 Protection degree

Meet IP55 protection degree -- protect the inner side from water and dust.

High quality PC

High quality PC for Cover and Base.

IEC standard and Philips internal rule

Pass IEC standard and follow more strict Philips internal design rule.

Specifications

Design and finishing

- Color: White
- Material: PC
- Module/Gang: 1 Module
- Product Range: LeafStyle
- Minimum Installation Box Depth: 34 cm

Product dimensions and weight

- Length: 13.7 cm
- Width: 10.15 cm
- Depth: 3.2 cm

Service

- Warranty: 2 year(s)

Packaging dimensions and weight

- EAN/UPC - product: 8718699674601
- Net weight: 0.16 kg
- Gross weight: 0.16 kg
- Height: 3.2 cm
- Length: 13.7 cm
- Width: 10.2 cm



Issue date: 2024-11-21
Version: 0.267

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.