

# PHILIPS

## Abrosa Recessed Light

Recessed Lights

2700K

White

Dimmable; Water Resistant



8719514254596



## Create the perfect ambience with high quality dimmable light.

Create the perfect mood with Philips LED Dimmable recessed spots, you can easily dim your lights from everyday bright light to cozy tones.

### Easy to experience

- Choose how and where light falls with these adjustable modular lights.

### Light effect

- Bright and focused beam

### Safety

- Moisture resistance

### Premium quality

- EyeComfort - light that's easy on the eyes

### Control

- Dimmable

### Durability

- Long life span up to 25,000 hours

# Highlights

## Adjustable modular light Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

## Moisture resistance

Moisture resistance means you can confidently use this product in bathrooms, kitchens, balconies and other spaces where moisture may be a consideration.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality,

output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow - just like traditional lamps.

## Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Aluminium

## Durability

- Number of switch cycles: 12,500

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 38 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Bathroom, Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Water Resistant

## Other characteristics

- Lamp current: 43 mA
- Efficacy: 72 lm/W

## Product dimensions and weight

- Net weight: 0.17 kg
- Cut out length: 6.8 cm
- Cut out width: 6.8 cm
- Height: 6.2 cm
- Length: 8.6 cm
- Recessed distance: 10 cm
- Width: 8.6 cm

## Service

- Warranty: 2 year(s)

#### Technical specifications

- Lifetime up to: 25,000 hour(s)
- Diameter: 86 mm
- Total lumen output fixture: 700
- Light color: 2700
- Mains power: AC 220-240
- Fixture dimmable: Yes
- LED: Yes
- Wattage bulb included: 9
- IP code: IP20/44

- Class of protection: Class II

#### Packaging dimensions and weight

- EAN/UPC - product: 8719514254596
- Net weight: 0.17 kg
- Gross weight: 0.21 kg
- Height: 8.5 cm
- Length: 10 cm
- Width: 10 cm



Issue date: 2025-02-16  
Version: 0.360

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)