

PHILIPS

Floor Socket

Switches & Sockets

LeafStyle

Metallica



8719514298972



High quality switch and socket designed to safely last for years

Philips LeafStyle provides modern design, high safety standard and easy to install switch & socket to your family.

Longer lifetime

- Long life cycles

Convenience

- Damping technology
- IP44 Protection degree

Safety and Durability

- High quality Aluminum Alloy

Highlights

Long life cycles

Could ensure 5000 times of operation.

Damping technology

Installed with damping technology, the panel opens softly and smoothly.

IP44 Protection degree

Meet IP44 protection degree -- protect the inner side from water and dust.

High quality Aluminum Alloy

High quality Aluminum Alloy for the whole product body.

Specifications

Design and finishing

- Color: White
- Material: PC
- Module/Gang: 1 Module
- Product Range: LeafStyle
- Minimum Installation Box Depth: 34 cm

Product dimensions and weight

- Length: 12 cm
- Width: 12 cm
- Depth: 5.97 cm

Service

- Warranty: 2 year(s)

Packaging dimensions and weight

- EAN/UPC - product: 8719514298972
- Net weight: 0.89 kg
- Gross weight: 0.92 kg
- Height: 6.5 cm
- Length: 12 cm
- Width: 12 cm
- Material number (12NC): 913713877701



Issue date: 2024-09-17
Version: 0.267

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com