

# PHILIPS

Downlight

Recessed Lights

3000K

White



8720169260894



## Twice the lifetime for long lasting performance

Designed with innovative thermal management for longer lifetime and reliable performance

### Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### Light effect

- Bright light with uniform distribution

### Safety

- No harmful UV radiation

### Durability

- Long life span up to 30,000 hours

# Highlights

## Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

## Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 30 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

## Other characteristics

- Lamp current: 75 mA
- Efficacy: 88 lm/W

## Power consumption

- Power factor: 0.5

## Product dimensions and weight

- Net weight: 0.21 kg
- Cut out length: 12.5 cm
- Height: 2.1 cm
- Length: 14.5 cm
- Recessed distance: 5 cm
- Width: 14.5 cm

## Service

- Warranty: 3 year(s)

## Technical specifications

- Lifetime up to: 30,000 hour(s)
- Total lumen output fixture: 800
- Light color: 3000
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- Wattage bulb included: 9
- IP code: IP20
- Class of protection: Class II

8720169260894

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169260894
- Net weight: 0.21 kg
- Gross weight: 0.25 kg
- Height: 17 cm
- Length: 3.8 cm
- Width: 17.8 cm



Issue date: 2025-02-16  
Version: 0.142

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)