

PHILIPS

Portable

Functional

Purepex

black

Dim



8720169293434

Touch key for tunable
white & dimming



Touch key for tunable
white & dimming



Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, Philips LED Performance desk light is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Tunable color temperature
- Brightness control with memory function

Highlights

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they

meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Tunable color temperature

Shift from crisp white light for focus to a warm yellow light for relaxation.

Brightness control with memory function

Memorizes the specific brightness levels you prefer.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Black
- Material: Plastic

Durability

- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Home office & Study
- Style: Contemporary
- Type: Desk Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Tunable White, Dimmable

Other characteristics

- Lamp current: 1500 mA
- Efficacy: 46 lm/W

Product dimensions and weight

- Net weight: 0.47 kg
- Height: 79 cm
- Length: 46 cm
- Width: 5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 350
- Light color: 3000/4000/5000
- Mains power: DC 5
- Fixture dimmable: Yes
- LED: Yes
- IP code: IP20
- Class of protection: Class III

8720169293434

Packaging dimensions and weight

- EAN/UPC - product: 8720169293434
- Net weight: 0.47 kg
- Gross weight: 0.71 kg
- Height: 47.5 cm
- Length: 6 cm
- Width: 16.3 cm



Issue date: 2024-11-21
Version: 0.118

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com