

# PHILIPS


Wavel Ceiling Light  
20W

Ceiling Lights

4000/6500/2700K

White

Dimmable;SceneSwitch



31822/31/P5



## Quality lighting for a cozy home

Philips myLiving WAWEL LED ceiling light comes with integrated LED to optimize light output and uniformity. Control its brightness according to your mood with step tunable and memory functions.

### Light effect

- Even light distribution

### Advanced LED light

- Tunable 2700-6500K

### Energy saving

- 80% energy saving, compared to traditional light sources

# Highlights

## Even light distribution



## 80% energy saving



## Tunable



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

This lamp is tunable. You can tune it to your preferred light color; from warm white (2700K) to cool daylight (6500K).

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, SceneSwitch

#### Other characteristics

- Lamp current: 160 mA
- Efficacy: 100 lm/W

#### Product dimensions and weight

- Net weight: 0.72 kg
- Height: 6.6 cm
- Length: 38 cm
- Width: 38 cm

#### Packaging dimensions and weight

- EAN/UPC - product: 8718696162781
- Net weight: 0.72 kg
- Gross weight: 1.18 kg
- Height: 42.6 cm
- Length: 7 cm
- Width: 42.6 cm
- Material number (12NC):  
915005315707

#### Service

- Warranty: 5 year(s)

#### Technical specifications

- Lifetime up to: 20,000 hour(s)
- Diameter: 380 mm
- Total lumen output fixture: 2000
- Light color: 4000/6500/2700
- Mains power: AC 220-240
- Fixture dimmable: Step Dim - Do not use with dimmer
- LED: Yes
- Wattage bulb included: 20
- IP code: IP20
- Class of protection: Class I



Issue date: 2024-06-14  
Version: 0.291

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)