

PHILIPS

Stick energy saving
bulb

Genie

8 W (40 W)

E27 cap

Warm white

8710163221762



Very compact size

Choose Philips Genie energy saving light bulbs for a compact, energy-efficient and affordable alternative.

Sustainable choice

- Carbon footprint
- Save energy from the moment you turn the switch

Beacon of trust

- You can trust what the Philips packaging is saying

Full lamp and light fixture compatibility

- Small, high-performance bulb

Highlights

Carbon footprint

Energy savers reduce the amount of energy in your home, which not only results in a lower energy bill, but also in less carbon (CO₂) output by your energy supplier. Together we make this a better world to live in.

Energy efficient

All Philips energy savers save energy from the moment you turn the switch. During their lifetime they use fewer kW and thus also result in a lower energy bill. The level of energy saving differs per lamp type and technology.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Compact size and high perform

Our smallest energy saving lamps are just as small as a traditional light bulb. You can now save energy and money in all your lights and lamps, without compromising on light quality.

Specifications

Bulb characteristics

- Shape: Stick
- Socket: E27
- Dimmable: No

Bulb dimensions

- Height: 108 mm
- Width: 44 mm

Durability

- Average life (at 2.7 hrs/day): 8 year(s)
- Nominal lifetime: 8,000 hour(s)

Light characteristics

- Color rendering index (CRI): 81
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 400 lm

Power consumption

- Voltage: 220-240 V
- Wattage: 8 W
- Wattage equivalent: 40 W

Packaging dimensions and weight

- EAN/UPC - product: 8710163221762
- Net weight: 0.07 kg
- Gross weight: 0.09 kg
- Height: 11.3 cm
- Length: 4.5 cm
- Width: 4.5 cm
- Material number (12NC): 929689238702



Issue date: 2024-06-14
Version: 0.410

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com