

PHILIPS

Halogen spot

Halogen

50 W

GU10

Warm white

925644344203



Superior halogen lighting

Provides bright, sparkling light with superior dimmability. An ideal accent for stylish homes, it doesn't require a transformer.

Personal scene setting

- Best dimmability to dims and create a cozy atmosphere

Create a cosy atmosphere

- Bright halogen light provides better contrast for more focus
- Bright, sparkling lighting to create your light scene at home

Create a decorative effect

- Accent light that can help create perfect focus on objects

Safe design

- Burner design ensures safety

Perfect for heat-sensitive light fixtures

- Alu reflector creates lower temperatures at the back of bulb

Highlights

Best dimmability

This Philips lamp can be used in combination with all dimmers and will not only turn down the dim light to 1% but also create a cozy atmosphere as you are used to with your incandescent.

Halogen contrast for focus

With bright halogen light, contrasts get richer, letters become sharper and visibility gets better. Bright light is more relaxing for your eyes for a better focus.

Bright, sparkling light

Clear halogen is a sparkling light, giving beautiful reflections where it shines, and sharp shadows where it doesn't. Philips halogen lamps give decorative light effect to your room, to bring your room to life.

Decorative accent light

This Philips lamp is perfect for home use in stylish rooms where accent lighting is required for a strong focus.

Safe burner design

Philips new super fuse design cuts off the light bulb within 2ms. This is so short that the arc can not build up. This results in a super safe light bulb, even at the end-of-life.

Aluminum reflector

90% of the heat is reflected towards the front of the light bulb, resulting in a lower temperature in the rear of the lamp. It is an ideal solution for heat-sensitive ceiling and other light fixtures.

Specifications

Bulb characteristics

- Socket: GU10
- Dimmable: Yes
- Bulb Finish: Clear

Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Number of switch cycles: 8,000
- Nominal lifetime: 2,000 hour(s)

Light characteristics

- Color rendering index (CRI): 100
- Light Color Category: Warm White
- Correlated Color Temperature (Nom): 2800

Power consumption

- Voltage: 230 V
- Wattage: 50 W
- Power Consumption: 50 W

Rated values

- Rated lifetime: 2,000 hour(s)

Technical specifications

- Shape: Spot light special
- Dimmable: Yes
- Cap-Base: GU10

Packaging dimensions and weight

- EAN/UPC - product: 8718291195177
- Net weight: 0.04 kg
- Gross weight: 0.05 kg
- Height: 6 cm
- Length: 5.1 cm
- Width: 5.1 cm
- Material number (12NC): 925644344203



Issue date: 2024-09-07
Version: 0.446

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com