

# PHILIPS

Non integrated  
compact fluorescent

PL-L

18 W

4 Pin

Cool white

927903008472



## Long life and sustainable light output

Philips' Bridge technology gives PLL sticks more light output than traditional PLLs. It also offers 15000hrs of life time, resulting in fewer replacements and lower maintenance costs.

### **Sustainable choice**

- Saves energy

### **Gives you bright light**

- Bridge technology gives PLL lamps more light output

# Highlights

## Saves energy

### Bridge technology

Philips Bridge technology gives PLL lamps more light output than

traditional PLL lamps. It also offers 12000hrs life time means Less replacements, lower maintenance costs.

# Specifications

## Bulb characteristics

- Socket: 4 Pin
- Dimmable: Yes

## Durability

- Nominal lifetime: 15,000 hour(s)

## Light characteristics

- Color rendering index (CRI): 82
- Light Color Category: Cool White
- Correlated Color Temperature (Nom): 4000
- Luminous Flux: 1,200 lm
- Luminous Efficacy (rated) (Nom): 67 lm/W

## Power consumption

- Wattage: 18 W
- Power Consumption: 18.0 W

## Technical specifications

- Light output: 1,200 lm
- Shape: Tube
- Dimmable: Yes
- Cap-Base: 2G11

## Packaging dimensions and weight

- EAN/UPC - product: 8711500706690
- Net weight: 60.9 g
- Gross weight: 75.91 g
- Height: 2.5 cm
- Length: 23 cm
- Width: 4.5 cm
- Material number (12NC): 927903008472



Issue date: 2024-06-14  
Version: 0.486

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)