

# PHILIPS

Tubular Fluorescent

15W

T12

Soft White

046677141462



## Energy savings and long life.

Philips Linear Fluorescent bulbs offer long life and energy savings in an environmentally responsible light bulb. They come in Soft and Cool white, Natural light and Daylight Deluxe colors to help create the mood you desire in the room.

### Light effect

- Provides a comfortable and relaxing environment

### Long lifespan

- Lasts at least 9000 hours

### Use in any room in your home

- Warm white light creates a comfortable, pleasant atmosphere

# Highlights

Soft white light

Lasts at least 9000 hours

Ideal for Kitchens and Baths

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Light characteristics

- Application: Comfortable light, Special application
- Color rendering index (CRI): 85
- Light Color Category: Soft White
- Correlated Color Temperature (Nom): 3000
- Luminous Flux: 800 lm

## Power consumption

- Wattage: 15 W
- Power Consumption: 15 W

## Technical specifications

- Lamp holder: T12
- Number of lamps: 1
- Placement: Ceiling
- Cap-Base: G13 | Medium Bi-Pin  
Fluorescent

## Packaging dimensions and weight

- EAN/UPC - product: 046677141462
- Net weight: 0 kg
- Gross weight: 0.16 kg
- Height: 3.8 cm
- Length: 3.8 cm
- Width: 45.2 cm



Issue date: 2024-11-21  
Version: 0.534

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)