

PHILIPS

Tubular Fluorescent

75W

T12

Daylight Deluxe

046677376635



Energy savings and long life.

Philips Linear Fluorescent bulbs offer long life and energy savings in an environmentally responsible light bulb. They come in Soft and Cool white, Natural light and Daylight Deluxe colors to help create the mood you desire in the room.

Long lifespan

- Lasts at least 12000 hours

Sustainable choice

- Reduced mercury for an environmentally friendly alternative

Use in any room in your home

- An arctic white light creates a cool, refreshing environment

Highlights

Lasts at least 12000 hours

ALTO Lamp Technology

For bath; laundry or any room

Specifications

Bulb characteristics

- Intended use: Indoor

Light characteristics

- Application: Extra brightness
- Color rendering index (CRI): 90
- Correlated Color Temperature (Nom): 6500
- Luminous Flux: 4,775 lm

Power consumption

- Wattage: 75 W
- Power Consumption: 75 W

Technical specifications

- Lamp holder: T12
- Number of lamps: 2
- Placement: Ceiling
- Cap-Base: FA8

Packaging dimensions and weight

- EAN/UPC - product: 046677376635
- Net weight: 0.88 kg
- Gross weight: 0.94 kg
- Height: 3.8 cm
- Length: 241 cm
- Width: 7.7 cm



Issue date: 2024-12-04
Version: 0.537

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com