

PHILIPS

Heat Lamp

250W

BR40

Medium Base



046677416744



Light for all of your specialized fixtures

Philips Specialty Incandescent and halogen bulbs provide the perfect light for accent and display lighting as well as general lighting in a variety of applications.

Use in any room in your home

- Provides a comfortable warmth using infrared technology

Perfect Shape

- Ideal for recessed cans and track light fixtures

Highlights

Ideal for Bathrooms

Use in indoor flood fixtures

Specifications

Bulb characteristics

- Intended use: Indoor
- Bulb Finish: Clear

Light characteristics

- Application: Special application

Power consumption

- Voltage: 120 V
- Wattage: 250 W
- Power Consumption: 250 W

Rated values

- Rated lifetime: 5,000 hour(s)

Technical specifications

- Lamp holder: BR40
- Number of lamps: 1
- Placement: Recessed cans, Track light
- Cap-Base: E26 | Single Contact
Medium Screw

Packaging dimensions and weight

- EAN/UPC - product: 046677416744
- Net weight: 0.33 kg
- Gross weight: 0.34 kg
- Height: 16.5 cm
- Length: 12 cm
- Width: 12 cm
- Material number (12NC):
925255136310



Issue date: 2024-09-17
Version: 0.537

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com