

PHILIPS

LEDtube Type A T8

LED

1200mm

4000K

G13

046677539153



Upgrade fluorescent to LED with confidence

Philips UniversalFit LED tubes replace T8 and T12 fluorescent tubes and work with electronic and magnetic ballasts. Simply plug and play. This 4' glass LED tube looks and feels like fluorescent, has a cool white light and long lifetime.

High quality light

- Cool, white light

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- Instant on

Highlights

Cool, white light



This bulb has a color temperature of 4000K providing you with an extra cool, fresh and crisp light.

Instant on

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Tube, double-ended
- Socket: G13
- Dimmable: No

Bulb dimensions

- Height: 121.23 cm
- Width: 2.78 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 36,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 240 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 1800 lm
- Warm-up time to 60% light: instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 112 lm/W

Packaging information

- Product family: UniversalFit
- EAN: 046677539153
- EOC: 542688
- Product title: 16T8/LED/48-840/UF18/G 24/2 FB WS

Power consumption

- Power factor: >0.9
- Voltage: 40-330 V
- Wattage: 16 W
- Wattage equivalent: 32-40 W

Product dimensions and weight

- Length: 121.23 cm

Technical specifications

- Frequency: 50-120000 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677539153
- Net weight: 0.68 kg
- Gross weight: 0.72 kg
- Height: 123.4 cm
- Length: 6.2 cm
- Width: 3.1 cm
- Material number (12NC): 929001965903



Issue date: 2024-09-17
Version: 0.225

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com