

PHILIPS

Bulb 150;100;50W
A21 E26d

LED

2700K

2150;1600;620lm

15000h

046677571528



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26d
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions

- Height: 13.31 cm
- Width: 7.06 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)
- Ambient temperature range: -4 to +113 °F

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 250 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 2150, 1600, 620 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 2,150, 1,600, 620 lm
- Luminous Efficacy (rated) (Nom): 116 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 116 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677571528
- EOC: 571521
- Product title: 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 18.5, 13, 6 W
- Wattage equivalent: 150;100;50 W
- Power Consumption: 18.5, 13, 6 W

Product dimensions and weight

- Length: 13.31 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 60 Hz
- Dimmable: No
- Cap-Base: E26D | 3 Contact Medium Screw
- UL Wet/ damp/ dry location: Damp location

Packaging dimensions and weight

- EAN/UPC - product: 046677571528
- Net weight: 0.15 kg
- Gross weight: 0.19 kg
- Height: 20.4 cm
- Length: 8 cm
- Width: 7.5 cm



Issue date: 2025-03-05
Version: 0.63

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com