

PHILIPS

Filament Bulb Amber
40W T20 E26

LED

2000K

400lm

15000h

Dimming

046677575243



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

Designed to be seen, looks good on and off

- Looks good on and off
- Vintage style LED

Highlights

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off. "

Vintage (2000K & 2200K)

Imagine the vintage look of traditional lighting with the benefits of LED. With Philips Vintage LED filament bulbs, you can have the classic look you love, with the energy-efficiency you need. Gives the traditional color and amber glow of old-fashioned incandescent lighting. The clear amber tinted glass bulb, brass finish base, and retro styling of the LED filament add a vintage flair to the decorative lighting in your home. The intricate swirling filament offers a cozy and warm ambience.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: T20
- Socket: E26
- Dimmable: Only with specific dimmers
- Bulb Finish: Amber
- Bulb Material: Glass

Bulb dimensions

- Height: 27.2 cm
- Width: 6.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)
- Ambient temperature range: -4 °F to 104 °F

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 330 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Nominal luminous flux: 400 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 820 | CCT of 2000K
- Correlated Color Temperature (Nom): 2000 K
- Luminous Flux: 400 lm
- Luminous Efficacy (rated) (Nom): 53 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, Decorative

Other characteristics

- Efficacy: 53 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677575243
- EOC: 575241
- Product title: 7.5T20/VIN/820/CL/G/E26/amber/SP/DIM 1CT

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 7.5 W
- Wattage equivalent: 40 W
- Power Consumption: 7.5 W

Product dimensions and weight

- Length: 27.2 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 50-60 Hz
- Line Frequency: 50 to 60 Hz
- Dimmable: Only with specific dimmers
- Cap-Base: E26 | Single Contact Medium Screw
- UL Wet/ damp/ dry location: Wet location

Packaging dimensions and weight

- EAN/UPC - product: 046677575243
- Net weight: 0.2 kg
- Gross weight: 0.29 kg
- Height: 32 cm
- Length: 10 cm
- Width: 10 cm
- Material number (12NC): 929001936513



Issue date: 2024-11-18
Version: 0.96

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com