

# PHILIPS

Filament Bulb Frosted  
300;200;100W A23 E26

LED

2700K

4000;3000;1600lm

15000h

046677576387



## A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- Designed for the comfort of your eyes

### Choose a simple replacement for your old bulbs

- Perfect fit and high-quality finishing

### Create the right light for your home

- Perfect for general room lighting

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Perfect fit

With a familiar shape, these bulbs are the perfect fit for your existing fixtures. They look just like the classic light bulb.

## Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Glass

## Bulb dimensions

- Height: 15.5 cm
- Width: 8.4 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 4000, 3000, 1600 lm
- Warm-up time to 60% light: instant full light
- Color Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Efficacy: 142 lm/W

## Packaging information

- EAN: 046677576387
- EOC: 576389
- Product title: 28A23/BrightD/827/FR/G/E26/ND 4/1PF T20

## Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 28, 20, 16 W
- Wattage equivalent: 300;200;100 W

## Product dimensions and weight

- Length: 15.5 cm

### Technical specifications

- Frequency: 60 Hz

### Packaging dimensions and weight

- EAN/UPC - product: 046677576387
- Net weight: 0.09 kg
- Gross weight: 0.14 kg
- Height: 20.9 cm
- Length: 10.2 cm
- Width: 13 cm
- Material number (12NC):  
929003127503



Issue date: 2024-05-31  
Version: 0.51

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)