

PHILIPS

Bulb 65W BR30 E26
x3

LED

2700K

650lm

11000h

Dimming

046677576578



Soft white light, no compromise on light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Light beyond illumination

- Dimmable

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: Only with specific dimmers
- Bulb Material: Plastic

Bulb dimensions

- Height: 13.2 cm
- Width: 9.5 cm

Design and finishing

- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 11,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 650 lm
- Warm-up time to 60% light: instant full light
- Color Code: 927 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- Efficacy: 90 lm/W

Packaging information

- EAN: 046677576578
- EOC: 576579
- Product title: 7.2BR30/LED/927/P/E26/DIM T20 4/3CT

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 7.2 W
- Wattage equivalent: 65 W

Product dimensions and weight

- Length: 13.2 cm

Technical specifications

- Frequency: 60 Hz

046677576578

Packaging dimensions and weight

- EAN/UPC - product: 046677576578
- Net weight: 0.17 kg
- Gross weight: 0.46 kg
- Height: 17.9 cm
- Length: 9.5 cm
- Width: 18.5 cm



Issue date: 2025-02-02
Version: 0.79

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com