

PHILIPS

Bulb 65W BR30 E26

UltraEfficient

3000K

650lm

50000h

Dimming

046677581671



UltraEfficient lamp, provide most sustainable and energy saving solution for you

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose for a sustainable solution

- Long life bulb - Lasts up to 50 years

Light beyond illumination

- Dimmable

Highlights

Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be

certain that your particular dimmer can be used with this bulb.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: Only with specific dimmers
- Bulb Material: Plastic

Bulb dimensions

- Height: 13 cm
- Width: 9.4 cm

Design and finishing

- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 650 lm
- Warm-up time to 60% light: instant full light
- Color Code: 930 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: UltraEfficient, EyeComfort
- Extra Features: Dimmable

Other characteristics

- Efficacy: 144 lm/W

Packaging information

- EAN: 046677581671
- EOC: 581678
- Product title: 4.5BR30/UE/930/P/E26/D/T20 1PF/3 SRP

Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 4.5 W
- Wattage equivalent: 65 W

Product dimensions and weight

- Length: 13 cm

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677581671
- Net weight: 0.07 kg
- Gross weight: 0.1 kg
- Height: 20.9 cm
- Length: 9.5 cm
- Width: 13 cm



Issue date: 2024-11-21
Version: 0.112

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com