

# PHILIPS

## Super Slim Ceiling Light 22W

Ceiling Lights

3000K

White

Dimmable



046677582876



# Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes

#### Match your interior

- Super slim design

#### Easy to experience

- Easy installation

#### Light effect

- Bright light with uniform distribution

#### Premium quality

- EyeComfort - light that's easy on the eyes

#### Control

- Dimmable

# Highlights

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a

decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow - just like traditional lamps.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 200 mA
- Efficacy: 81 lm/W

## Power consumption

- Power factor: 0.9

## Product dimensions and weight

- Net weight: 0.8 kg
- Height: 2.6 cm
- Length: 30 cm
- Width: 30 cm

## Service

- Warranty: 3 year(s)

#### Technical specifications

- Lifetime up to: 50,000 hour(s)
- Diameter: 300 mm
- Total lumen output fixture: 1800
- Light color: 3000
- Mains power: AC 120
- Fixture dimmable: Yes
- LED: Yes
- IP code: UL02 - Damp Location (North America)

- Class of protection: UL non-earthed

#### Packaging dimensions and weight

- EAN/UPC - product: 046677582876
- Net weight: 0.8 kg
- Gross weight: 1.06 kg
- Height: 31.7 cm
- Length: 5.5 cm
- Width: 31.7 cm



Issue date: 2025-02-02  
Version: 0.122

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)